



0 to 69dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 18GHz

RF Step Attenuators Technical Data Sheet

PE7444-69

Features

- 1 dB steps from 0 to 69 dB Attenuation
- Rotary Dial Control
- · SMA Female Connectors

- 0°C to +54°C Operating Temperature
- · ±1.5 dB Typical Attenuation Accuracy

Applications

Instrumentation

- · Prototyping and Characterization
- · Precision Measurements
- · Production Systems

Description

The PE7444-69 is a Step Attenuator that has 69 dB of total attenuation with 1 dB step size and rotary dial design across a frequency range from DC to 18 GHz. The design is tried and true technology that offers exceptional performance characteristics that include 1.5 dB maximum insertion loss, and a maximum VSWR of 1.75:1 at 18 GHz. The design also features excellent attenuation accuracy with ±1.5 dB typical at 18 GHz. The Aluminum package has SMA Female connectors, and operates within the temperature range of -0°C to 54°C.

Electrical Specifications

DC		18	GHz
			GHZ
	50		Ohms
		1.5	dB
	0 to 69		dB
	1		dB
	Rotary		
		2	Watts
		200	Watts
		1.75:1	
		1	0 to 69 1 Rotary 2 200

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 18					GHz
Attenuation Accuracy	1.5					dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 0 to 69dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 18GHz PE7444-69

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





0 to 69dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 18GHz

RF Step Attenuators Technical Data Sheet

PE7444-69

Mechanical Specifications

Size

 Length
 6.417 in [162.99 mm]

 Width
 1.772 in [45.01 mm]

 Height
 1.89 in [48.01 mm]

 Weight
 0.05 lbs [22.68 g]

Connectors

Description	Connector 1	Connector 2	
Туре	SMA Female	SMA Female	
Contact Material and Plating	Beryllium Copper, Gold		
Body Material and Plating	Stainless Steel	Aluminum	

Environmental Specifications

Temperature

Operating Range 0 to 54 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

0 to 69dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 18GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 0 to 69dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 18GHz PE7444-69

URL: https://www.pasternack.com/69db-step-sma-female-sma-female-2-watts-attenuator-pe7444-69-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE7444-69 CAD Drawing

0 to 69dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 18GHz

