


N-Channel 200V (D-S) MOSFET

PRODUCT SUMMARY					
V _{DS} (V)	$R_{DS(on)}(\Omega)$	I _D (A)			
200	0.056 at V _{GS} = 10 V	25			
200	0.070 at V _{GS} = 6 V	23			




FEATURES

- TrenchFET® Power MOSFET
- 175 °C Junction Temperature
- PWM Optimized
- 100 % R_g Tested
- Compliant to RoHS Directive 2002/95/EC



APPLICATIONS

· Primary Side Switch



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS (T _A = 25 °C, unless otherwise noted)						
Parameter		Symbol	Limit	Unit		
Drain-Source Voltage		V_{DS}	200	V		
Gate-Source Voltage		V_{GS}	± 20			
Continuous Dusin Comment /T 175 90\b	T _C = 25 °C	- I _D	25			
Continuous Drain Current (T _J = 175 °C) ^b	T _C = 125 °C		17			
Pulsed Drain Current	I _{DM}	60	Α			
Continuous Source Current (Diode Conduction)	I _S	19]			
Avalanche Current	I _{AS}	25				
Single Pulse Avalanche Energy	L = 0.1 mH	E _{AS}	18	mJ		
Maximum Dawar Dissination	T _C = 25 °C	P _D	145 ^b	W		
Maximum Power Dissipation	T _A = 25 °C	'D	3.5 ^a			
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 175	°C		

THERMAL RESISTANCE RATINGS							
Parameter		Symbol	Typical	Maximum	Unit		
Lucation to Ambient	t ≤ 10 s	R _{thJA}	15	18			
Junction-to-Ambient ^a	Steady State	□ thJA	40	50	°C/W		
Junction-to-Case (Drain)	•	R _{thJC}	0.85	1.1			

Notes:

- a. Surface mounted on 1" x 1" FR4 board.
- b. See SOA curve for voltage derating.

服务热线:400-655-8788

1



Parameter	Symbol	Test Conditions	Min.	Typ. ^a	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V_{DS}	V_{DS} $V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$ 200					
Gate Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_D = 250 \mu A$	2		4	V	
Gate-Body Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 100	nA	
		V _{DS} = 200 V, V _{GS} = 0 V	1		1		
Zero Gate Voltage Drain Current	I_{DSS}	V _{DS} = 200 V, V _{GS} = 0 V, T _J = 125 °C			50	μΑ	
		V _{DS} = 200 V, V _{GS} = 0 V, T _J = 175 °C			250		
On-State Drain Current ^b	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	40			Α	
		V _{GS} = 10 V, I _D = 5 A		0.056			
D : 0	D	V _{GS} = 10 V, I _D = 5 A, T _J = 125 °C		0.130			
Drain-Source On-State Resistance ^b	R _{DS(on)}	V _{GS} = 10 V, I _D = 5 A, T _J = 175 °C		0.260		Ω	
		V _{GS} = 6 V, I _D = 5 A		0.070			
Forward Transconductance ^b	9 _{fs}	V _{DS} = 15 V, I _D = 19 A		35		S	
Dynamic ^a							
Input Capacitance	C _{iss}			2400		pF	
Output Capacitance	C _{oss}	$V_{GS} = 0 \text{ V}, V_{DS} = 25 \text{ V}, F = 1 \text{ MHz}$		280			
Reverse Transfer Capacitance	C _{rss}			180			
Total Gate Charge ^c	Q_g			40			
Gate-Source Charge ^c	Q_{gs}	$V_{DS} = 100 \text{ V}, V_{GS} = 10 \text{ V}, I_D = 19 \text{ A}$		10		nC	
Gate-Drain Charge ^c	Q_{gd}			15			
Gate Resistance	R_{g}		0.5		2.9	Ω	
Turn-On Delay Time ^c	t _{d(on)}			15	25		
Rise Time ^c	t _r	$V_{DD} = 100 \text{ V}, R_L = 5.2 \Omega$		50	75	no	
Turn-Off Delay Time ^c	t _{d(off)}	$I_D \cong 19 \text{ A}, V_{GEN} = 10 \text{ V}, R_g = 2.5 \Omega$		30	45	ns	
Fall Time ^c	t _f			60	90		
Source-Drain Diode Ratings and Char	acteristics (7	_C = 25 °C)					
Pulsed Current	I _{SM}				50	Α	
Diode Forward Voltage ^b	V_{SD}	I _F = 19 A, V _{GS} = 0 V		0.9	1.5	V	
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 19 A, dI/dt = 100 A/μs		180	250	ns	


Notes:

- a. Guaranteed by design, not subject to production testing. b. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %. c. Independent of operating temperature.

服务热线:400-655-8788




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)






TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




On-Resistance vs. Junction Temperature




Source-Drain Diode Forward Voltage

THERMAL RATINGS

4




Maximum Avalanche Drain Current vs. Case Temperature



* V_{GS} > minimum V_{GS} at which R_{DS(on)} is specified

Safe Operating Area




Normalized Thermal Transient Impedance, Junction-to-Case

服务热线:400-655-8788



TO-251AA



	MILLIM	IETERS	INC	HES
Dim	Min	Max	Min	Max
Α	2.21	2.38	0.087	0.094
A1	0.89	1.14	0.035	0.045
b	0.71	0.89	0.028	0.035
b1	0.76	1.14	0.030	0.045
b2	5.23	5.43	0.206	0.214
С	0.46	0.58	0.018	0.023
с1	0.46	0.58	0.018	0.023
D	5.97	6.22	0.235	0.245
Е	6.48	6.73	0.255	0.265
е	2.28 BSC		0.090	BSC
L	3.89	9.53	0.153	0.375
L1	1.91	2.28	0.075	0.090
L2	0.89	1.27	0.035	0.050
L3	1.15	1.52	0.045	0.060

服务热线:400-655-8788



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.