


Surface-Mount TRANSZORB® Transient Voltage Suppressors

eSMP® Series


Top View

Bottom View

SlimSMA (DO-221AC)

Cathode Anode

DESIGN SUPPORT TOOLS AVAILABLE


| PRIMARY CHARACTERISTICS | |
|-----------------------------------|----------------------|
| V_{BR} | 6.4 V to 159 V |
| V_{WM} | 5.0 V to 130 V |
| P_{PPM} (10 x 1000 μ s) | 600 W |
| P_{PPM} (8 x 20 μ s) | 4000 W |
| P_D at $T_M = 55^\circ\text{C}$ | 8 W |
| T_J max. | 175 $^\circ\text{C}$ |
| Polarity | Unidirectional |
| Package | SlimSMA (DO-221AC) |

FEATURES

- Very low profile - typical height of 0.95 mm
- Ideal for automated placement
- Unidirectional only
- Excellent clamping capability
- Peak pulse power:
 - 600 W (10/1000 μ s)
 - 4 kW (8/20 μ s)
- ESD capability: IEC 61000-4-2 level 4
 - 15 kV (air)
 - 8 kV (contact)
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 $^\circ\text{C}$
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
 COMPLIANT
 HALOGEN
FREE
TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lighting on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, and telecommunication.

MECHANICAL DATA
Case: SlimSMA (DO-221AC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and industrial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD22-B102

M3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end


| MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$, unless otherwise noted) | | | | |
|--|---------------------------------|--------------------------|----------------|------------------|
| PARAMETER | | SYMBOL | VALUE | UNIT |
| Peak pulse power dissipation | with a 10/1000 μ s waveform | P_{PPM} ⁽¹⁾ | 600 | W |
| | with a 8/20 μ s waveform | | 4000 | |
| Peak pulse current | with a 10/1000 μ s waveform | I_{PPM} ⁽¹⁾ | See next table | A |
| | with a 8/20 μ s waveform | | | |
| Power dissipation | $T_M = 55^\circ\text{C}$ | P_D ⁽²⁾ | 8 | W |
| | $T_A = 25^\circ\text{C}$ | P_D ⁽³⁾ | 1.0 | |
| Storage temperature range | | T_{STG} | -65 to +175 | $^\circ\text{C}$ |
| Operating junction temperature range | | T_J | -55 to +175 | |

Notes

- (1) Non-repetitive current pulse, per fig. 3 and derated above $T_A = 25^\circ\text{C}$ per fig. 2.
- (2) Power dissipation mounted on infinite heatsink
- (3) Power dissipation mounted on FR4 PCB, 2 oz. standard footprint



| INDEX OF SYMBOLS | |
|------------------|---------------------------------|
| SYMBOL | PARAMETER |
| V_{WM} | Stand-off voltage |
| V_{BR} | Breakdown voltage |
| V_C | Clamping voltage |
| I_D | Leakage current at V_{WM} |
| I_{PP} | Peak pulse current |
| αT | Voltage temperature coefficient |
| V_F | Forward voltage drop |
| R_D | Dynamic resistance |



Zener Voltage Regulator

| ELECTRICAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted) | | | | | | | | | | | | | | | |
|---|---------------------|---|------|-----|----------------------------|---|-------------|-----|-----------------------------|------|----------|-----------------------------|------|----------|----------------|
| DEVICE TYPE | DEVICE MARKING CODE | BREAKDOWN VOLTAGE V_{BR} AT I_T (1) | | | STAND-OFF VOLTAGE V_{WM} | MAXIMUM REVERSE LEAKAGE I_D AT V_{WM} (3) | | | V_C AT I_{PP} R_D (2) | | | V_C AT I_{PP} R_D (2) | | | αT (3) |
| | | MIN. | MAX. | mA | | V | 25 °C 85 °C | | 10/1000 μ s | | | 8/20 μ s | | | |
| | | | | | V | | μ A | V | MAX. V | A | Ω | MAX. V | A | Ω | |
| SMA6F5.0A | 6AE | 6.40 | 7.07 | 10 | 5 | 150 | 375 | 5.0 | 9.2 | 68.0 | 0.031 | 13.4 | 298 | 0.021 | 5.7 |
| SMA6F6.0A | 6AG | 6.70 | 7.41 | 10 | 6 | 600 | 1500 | 6.0 | 9.5 | 63.2 | 0.033 | 13.7 | 290 | 0.022 | 5.9 |
| SMA6F6.5A | 6AK | 7.20 | 7.96 | 10 | 6.5 | 100 | 250 | 6.5 | 10.2 | 58.8 | 0.038 | 14.5 | 276 | 0.024 | 6.1 |
| SMA6F7.5A | 6AP | 8.33 | 9.21 | 1.0 | 7.5 | 50 | 125 | 7.5 | 11.8 | 50.8 | 0.051 | 17.0 | 235 | 0.033 | 6.5 |
| SMA6F8.0A | 6AR | 8.89 | 9.83 | 1.0 | 8.0 | 20 | 50 | 8.0 | 12.8 | 46.9 | 0.063 | 18.2 | 220 | 0.038 | 7.0 |
| SMA6F8.5A | 6AT | 9.4 | 10.4 | 1.0 | 8.5 | 20 | 50 | 8.5 | 13.3 | 45.1 | 0.064 | 18.7 | 205 | 0.040 | 7.3 |
| SMA6F10A | 6AX | 11.1 | 12.3 | 1.0 | 10 | 1.0 | 5.0 | 10 | 15.7 | 38.2 | 0.089 | 19.6 | 184 | 0.040 | 7.8 |
| SMA6F11A | 6AZ | 12.2 | 13.5 | 1.0 | 11 | 1.0 | 5.0 | 11 | 17.2 | 34.8 | 0.107 | 21.5 | 172 | 0.047 | 8.1 |
| SMA6F12A | 6BE | 13.3 | 14.7 | 1.0 | 12 | 0.2 | 1.0 | 12 | 18.8 | 31.9 | 0.128 | 23.5 | 157 | 0.056 | 8.3 |
| SMA6F12AHD | 6BF | 13.2 | 14.3 | 1.0 | 12 | 0.2 | 1.0 | 12 | 18.5 | 32.4 | 0.130 | 22.9 | 157 | 0.055 | 8.4 |
| SMA6F13A | 6BG | 14.4 | 15.9 | 1.0 | 13 | 0.2 | 1.0 | 13 | 20.4 | 29.4 | 0.153 | 23.9 | 147 | 0.064 | 8.4 |
| SMA6F15A | 6BM | 16.7 | 18.5 | 1.0 | 15 | 0.2 | 1.0 | 15 | 23.6 | 25.4 | 0.201 | 27.7 | 123 | 0.075 | 8.8 |
| SMA6F16A | 6BP | 17.8 | 19.7 | 1.0 | 16 | 0.2 | 1.0 | 16 | 25.2 | 23.8 | 0.229 | 29.5 | 119 | 0.082 | 8.8 |
| SMA6F17A | 6BR | 18.9 | 20.9 | 1.0 | 17 | 0.2 | 1.0 | 17 | 26.7 | 22.5 | 0.259 | 31.4 | 111 | 0.095 | 9.0 |
| SMA6F18A | 6BT | 20.0 | 22.1 | 1.0 | 18 | 0.2 | 1.0 | 18 | 28.3 | 21.2 | 0.292 | 33.2 | 102 | 0.109 | 9.2 |
| SMA6F20A | 6BV | 22.2 | 24.5 | 1.0 | 20 | 0.2 | 1.0 | 20 | 31.4 | 19.1 | 0.361 | 36.8 | 93 | 0.132 | 9.4 |
| SMA6F22A | 6BX | 24.4 | 26.9 | 1.0 | 22 | 0.2 | 1.0 | 22 | 35.5 | 16.9 | 0.509 | 48.2 | 83.0 | 0.257 | 9.6 |
| SMA6F24A | 6BZ | 26.7 | 29.5 | 1.0 | 24 | 0.2 | 1.0 | 24 | 39.0 | 15.4 | 0.617 | 50.0 | 80.0 | 0.256 | 9.6 |
| SMA6F26A | 6CE | 28.9 | 31.9 | 1.0 | 26 | 0.2 | 1.0 | 26 | 42.0 | 14.3 | 0.706 | 53.3 | 75.0 | 0.285 | 9.7 |
| SMA6F28A | 6CG | 31.1 | 34.4 | 1.0 | 28 | 0.2 | 1.0 | 28 | 45.5 | 13.2 | 0.841 | 58.8 | 68.0 | 0.359 | 9.8 |
| SMA6F30A | 6CK | 33.3 | 36.8 | 1.0 | 30 | 0.2 | 1.0 | 30 | 48.4 | 12.4 | 0.935 | 64.5 | 62.0 | 0.447 | 9.9 |
| SMA6F33A | 6CM | 36.7 | 40.6 | 1.0 | 33 | 0.2 | 1.0 | 33 | 53.1 | 11.3 | 1.11 | 70.2 | 57.0 | 0.519 | 10.0 |
| SMA6F36A | 6CP | 40.0 | 44.2 | 1.0 | 36 | 0.2 | 1.0 | 36 | 58.3 | 10.3 | 1.37 | 76.9 | 52.0 | 0.629 | 10.0 |
| SMA6F40A | 6CR | 44.4 | 49.1 | 1.0 | 40 | 0.2 | 1.0 | 40 | 64.5 | 9.3 | 1.66 | 83.3 | 48.0 | 0.713 | 10.1 |
| SMA6F43A | 6CT | 47.8 | 52.8 | 1.0 | 43 | 0.2 | 1.0 | 43 | 69.8 | 8.6 | 1.98 | 89.9 | 44.5 | 0.834 | 10.1 |
| SMA6F45A | 6CV | 50.0 | 55.3 | 1.0 | 45 | 0.2 | 1.0 | 45 | 72.3 | 8.3 | 2.05 | 93.9 | 42.6 | 0.906 | 10.2 |
| SMA6F48A | 6CX | 53.3 | 58.9 | 1.0 | 48 | 0.2 | 1.0 | 48 | 76.9 | 7.8 | 2.31 | 100 | 40.0 | 1.03 | 10.3 |
| SMA6F51A | 6CZ | 56.7 | 62.7 | 1.0 | 51 | 0.2 | 1.0 | 51 | 82.2 | 7.3 | 2.67 | 107 | 37.5 | 1.18 | 10.3 |
| SMA6F54A | 6RE | 60.0 | 66.3 | 1.0 | 54 | 0.2 | 1.0 | 54 | 87.0 | 6.9 | 3.00 | 113 | 35.5 | 1.32 | 10.4 |
| SMA6F58A | 6RG | 64.4 | 71.2 | 1.0 | 58 | 0.2 | 1.0 | 58 | 93.8 | 6.4 | 3.53 | 121 | 33.0 | 1.51 | 10.4 |



| ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | | | | | | | | | | | | |
|--|---------------------|--|------|-----|-----------------------------------|--|-------|-----|---|-----|------|---|------|------|-------------------|
| DEVICE TYPE | DEVICE MARKING CODE | BREAKDOWN VOLTAGE V _{BR} AT I _T ⁽¹⁾ | | | STAND-OFF VOLTAGE V _{WM} | MAXIMUM REVERSE LEAKAGE I _D AT V _{WM} ⁽³⁾ | | | V _C AT I _{PP} , R _D ⁽²⁾ | | | V _C AT I _{PP} , R _D ⁽²⁾ | | | αT ⁽³⁾ |
| | | MIN. | MAX. | mA | V | 25 °C | 85 °C | V | 10/1000 μs | | | 8/20 μs | | | |
| | | V | | | | μA | | | MAX. V | A | Ω | MAX. V | A | Ω | |
| SMA6F60A | 6RK | 66.7 | 73.7 | 1.0 | 60 | 0.2 | 1.0 | 60 | 96.8 | 6.2 | 3.73 | 125 | 31.9 | 1.61 | 10.5 |
| SMA6F64A | 6RM | 71.1 | 78.6 | 1.0 | 64 | 0.2 | 1.0 | 64 | 103 | 5.8 | 4.21 | 134 | 29.9 | 1.85 | 10.5 |
| SMA6F70A | 6RP | 77.8 | 86.0 | 1.0 | 70 | 0.2 | 1.0 | 70 | 113 | 5.3 | 5.09 | 148 | 27.0 | 2.30 | 10.5 |
| SMA6F75A | 6RR | 83.3 | 92.1 | 1.0 | 75 | 0.2 | 1.0 | 75 | 120 | 5.0 | 5.58 | 156 | 25.6 | 2.50 | 10.6 |
| SMA6F78A | 6RT | 86.7 | 95.8 | 1.0 | 78 | 0.2 | 1.0 | 78 | 125 | 4.8 | 6.08 | 163 | 24.6 | 2.73 | 10.6 |
| SMA6F85A | 6RV | 94.4 | 104 | 1.0 | 85 | 0.2 | 1.0 | 85 | 136 | 4.4 | 7.27 | 178 | 22.5 | 3.29 | 10.6 |
| SMA6F90A | 6RX | 100 | 111 | 1.0 | 90 | 0.2 | 1.0 | 90 | 146 | 4.1 | 8.54 | 189 | 21.2 | 3.68 | 10.7 |
| SMA6F100A | 6RZ | 111 | 123 | 1.0 | 100 | 0.2 | 1.0 | 100 | 162 | 3.7 | 10.5 | 211 | 19.0 | 4.63 | 10.7 |
| SMA6F110A | 6SE | 122 | 135 | 1.0 | 110 | 0.2 | 1.0 | 110 | 177 | 3.4 | 12.4 | 230 | 17.4 | 5.46 | 10.7 |
| SMA6F120A | 6VG | 133 | 147 | 1.0 | 120 | 0.2 | 1.0 | 120 | 194 | 3.1 | 15.2 | 250 | 16.0 | 6.44 | 10.7 |
| SMA6F130A | 6VK | 144 | 159 | 1.0 | 130 | 0.2 | 1.0 | 130 | 207 | 2.9 | 16.6 | 267 | 15.0 | 7.20 | 10.8 |

Notes

- (1) Pulse test: t_p ≤ 50 ms
- (2) To calculate maximum clamping voltage at other surge currents, use following formula: V_{CL} max. = R_D x I_{PP} + V_{BR} max.
- (3) To calculate V_{BR} vs. junction temperature, use following formula: V_{BR} at T_J = V_{BR} at 25 °C x (1 + αT x (T_J - 25))

| THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | |
|---|---------------------------------|------|------|------|
| PARAMETER | SYMBOL | TYP. | MAX. | UNIT |
| Typical thermal resistance | R _{θJA} ⁽¹⁾ | 120 | 150 | °C/W |
| | R _{θJM} ⁽²⁾ | 12 | 15 | |

Notes

- (4) Thermal resistance junction-to-ambient to follow JEDEC® 51-2A, device mounted on FR4 PCB, 2 oz. standard footprint
- (5) Thermal resistance junction-to-mount to follow JEDEC® 51-14, using TDIM (transient dual interface test method)

| IMMUNITY TO STATIC ELECTRICAL DISCHARGE TO THE FOLLOWING STANDARDS (T _A = 25 °C unless otherwise noted) | | | | | |
|--|---------------------------------------|-----------------------|----------------|-------|---------|
| STANDARD | TEST TYPE | TEST CONDITIONS | SYMBOL | CLASS | VALUE |
| IEC 61000-4-2 | Human body model (contact mode) | C = 150 pF, R = 330 Ω | V _C | 4 | > 8 kV |
| | Human body model (air discharge mode) | | | | > 15 kV |

| ORDERING INFORMATION (Example) | | | | |
|--------------------------------|-----------------|------------------------|---------------|------------------------------------|
| PREFERRED P/N | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE |
| SMA6F5.0A-M3/6A ⁽¹⁾ | 0.032 | 6A | 3500 | 7" diameter plastic tape and reel |
| SMA6F5.0A-M3/6B ⁽¹⁾ | 0.032 | 6B | 14 000 | 13" diameter plastic tape and reel |
| SMA6F22A-M3/H ⁽²⁾ | 0.032 | H | 3500 | 7" diameter plastic tape and reel |
| SMA6F22A-M3/I ⁽²⁾ | 0.032 | I | 14 000 | 13" diameter plastic tape and reel |

Notes

- (1) Package code "6A and 6B" apply for SMA6F5.0A thru SMA6F20A
- (2) Package code "H and I" apply for SMA6F22A thru SMA6F130A



RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^\circ\text{C}$ unless otherwise noted)




Fig. 1 - Peak Pulse Power Rating Curve




Fig. 4 - Typical Junction Capacitance




Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature




Fig. 5 - Power Dissipation Derating Curve




Fig. 3 - Pulse Waveform




Fig. 6 - Typical Transient Thermal Impedance



Notes

- Fig. 1 - Power calculation is based on I_{PPM} times defined maximum clamping voltage by pulse width
- Fig. 1 - 10 000 μs P_{PPM} is actual test for $V_{WM} \leq 60\text{ V}$ types, over 60 V types 10 000 μs P_{PPM} is curve extensional value




PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SlimSMA (DO-221AC)



Mounting Pad Layout





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.