




Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS
 Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Ordering Information

PM 200 - * - N - Z - * - **

| | | | | |
|---|------------------------|--------------------------------------|---------------------|--|
| No. of Rows 1=Single Row 2=Dual Row | No. of Pins 2-40Pin | Type Z-直针 H-弯针 S-弯脚 R-弯脚 | Length (Plastic) | Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin |
|---|------------------------|--------------------------------------|---------------------|--|

| | | | | | | | | | | |
|-----------|------------------------|-------------------|------------------|-------|------------------|--|---|--------------------|-------------|-----|
| | | | GENREL TOLERANCE | | 制图 DRAWING | | 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD | | | |
| | | | DIM | TOL | 审核 CHECK | | | | | |
| | | | X. X | ±0.30 | 批准 APPROVAL | | 产品名称 TITLE | 2.00双排 排母 直针 | 版本 REV. | A |
| | | | X. XX | ±0.20 | 比例 SCALE | | 产品料号 PART NO. | PM200-2-N-Z-4.3-XX | 单位 UNITS | mm |
| | | | X. XXX | ±0.10 | 投影 Projection | | 材料 MATERIAL | | 页次 SHEET | 1/1 |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | Angle | ±3.0° | | | | | | |