




SECTION A-A

SPECIFICATIONS

- 1、Current Rating: 0.5A AC, DC
- 2、Voltage Rating: 30V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contract Resistance: 30mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltage: 200V AC/minute
- 7、Material: Wafer LCP, UL94V-0
PIN Phosphoric bronze Tin-plated
Solder tad Phosphoric bronze Tin-plated



Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-0.8-2PWT	0.80	3.80
3	HC-0.8-3PWT	1.60	4.60
4	HC-0.8-4PWT	2.40	5.40
5	HC-0.8-5PWT	3.20	6.20
6	HC-0.8-6PWT	4.00	7.00
7	HC-0.8-7PWT	4.80	7.80
8	HC-0.8-8PWT	5.60	8.60
9	HC-0.8-9PWT	6.40	9.40
10	HC-0.8-10PWT	7.20	10.20
11	HC-0.8-11PWT	8.00	11.00
12	HC-0.8-12PWT	8.80	11.80
13	HC-0.8-13PWT	9.60	12.60
14	HC-0.8-14PWT	10.40	13.40
15	HC-0.8-15PWT	11.20	14.20
16	HC-0.8-16PWT	12.00	15.00

			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	0.8 卧贴	版本 REV.	A
1			初版发行				产品料号 PART NO.	HC-0.8-NPWT	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET	1/1