





SMA ATTENUATOR 20 DB 18 GHZ 2W

PAGE 1/2 ISSUE 10-06-15E SERIES PART NUMBER R411820121





Scale 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body Male center contact Female center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 2 OVER NICKEL 2 GOLD 1.3 OVER NICKEL2	
Outer contact Insulator	BERYLLIUM COPPER - PTFE	GOLD 1.3 OVER NICKEL2	
Gasket	SILICONE RUBBER ALUMINA		
Substrate Resistor	THIN FILM		
Others parts	-	-	





SMA ATTENUATOR 20 DB 18 GHZ 2W

PAGE 2/2	ISSUE 10-06-15E	SERIES ATTENUATOR	PART NUMBER R411820121
-----------------	-----------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4	12.4 - 18
V.S.W.R (≤)	1.15	1.20	1.25	1.35
Deviation(±dB)	0.50	0.50	0.60	1.00

Operating Frequency Range	DC - 18	GHz
Impedance	50	Ω
Nominal Attenuation	20	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	4,7300 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS