
Technical Data Sheet

BNC ATTENUATOR 10 DB 3 GHZ 1W





This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

Technical Data Sheet

BNC ATTENUATOR 10 DB 3 GHZ 1W



	ISSUE 19-12-14B	SERIES ATTENUATOR	PART NUMB	ER R412410124
		ELECT	RICAL CHARACTERISTICS	
Frequency (G V.S.W.R (≤)	GHz) DC -2 1.20	2 - 3 1.30		
Deviation(±dE	B) 0.50	0.50		
0	Operating Frequency Range Impedance Nominal Attenuation Peak power at 25°C (1µs, 1‰) Average power at 25°C		DC - 3 50	GHz
			10	Ω dB
Pe			100	W
A			1	W (Free Air Cooled) W (Conduction Cooled)
		MECHA	NICAL CHARACTERISTICS	
onnectors	BNC		Male Female	MIL-C 39012
/eight		12,8400 g		1
	510	Pov	ver derating Versus temperature	
			-7,5 25 55 85 Temperature (°C)	