SIEMENS

Data sheet

US2:14IUH320J



Non-reversing motor starter, Size 3 1/2, Three phase full voltage, Solidstate overload relay, OLR amp range 50-200A, 24VAC 50-60Hz coil, Noncombination type, Enclosure type 12, Dust/drip proof for indoors, Standard width enclosure

	Fi	gu	re	si	mi	lar
--	----	----	----	----	----	-----

product brand name	Class 14				
design of the product	Full-voltage non-reversing motor starter				
special product feature	ESP200 overload relay; Half-size starter				
General technical data					
weight [lb]	33 lb				
Height x Width x Depth [in]	26 × 13 × 8 in				
touch protection against electrical shock	(NA for enclosed products)				
installation altitude [ft] at height above sea level maximum	6560 ft				
ambient temperature [°F]					
 during storage 	-22 +149 °F				
during operation	-4 +104 °F				
ambient temperature					
during storage	-30 +65 °C				
during operation	-20 +40 °C				
country of origin	USA				
Horsepower ratings					
yielded mechanical performance [hp] for 3-phase AC motor					
• at 200/208 V rated value	30 hp				
• at 220/230 V rated value	40 hp				
• at 460/480 V rated value	75 hp				
• at 575/600 V rated value	75 hp				
Contactor					
size of contactor	Controller half size 3 1/2				
number of NO contacts for main contacts	3				
operating voltage for main current circuit at AC at 60 Hz maximum	600 V				
operational current at AC at 600 V rated value	115 A				
mechanical service life (switching cycles) of the main contacts typical	500000				
Auxiliary contact					
number of NC contacts at contactor for auxiliary contacts	0				
number of NO contacts at contactor for auxiliary contacts	1				
number of total auxiliary contacts maximum	7				
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)				
Coil					
type of voltage of the control supply voltage	AC				
control supply voltage					

a at AC at 50 Lie rated value	2414
at AC at 50 Hz rated value	24 V 24 V
at AC at 60 Hz rated value	24 V 14 W
holding power at AC minimum apparent pick-up power of magnet coil at AC	310 VA
apparent holding power of magnet coll at AC	26 VA
operating range factor control supply voltage rated value of magnet coil	0.85 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	26 41 ms
OFF-delay time	14 19 ms
Overload relay	
product function	
overload protection	Yes
phase failure detection	Yes
asymmetry detection	Yes
ground fault detection	Yes
test function	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	50 200 A
tripping time at phase-loss maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
 with single-phase operation at AC rated value 	600 V
 with multi-phase operation at AC rated value 	300 V
Enclosure	
degree of protection NEMA rating	12
design of the housing	Dust tight and drip proof for indoors
Mounting/wiring	
mounting position	Vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
tightening torque [lbf·in] for supply	120 120 lbf·in
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x(14 - 2/0 AWG)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Box lug
tightening torque [lbf·in] for load-side outgoing feeder	120 120 lbf·in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x(14 - 2/0 AWG)
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C
material of the conductor for load-side outgoing feeder	AL or CU
type of electrical connection of magnet coil	screw-type terminals
tightening torque [lbf·in] at magnet coil	5 12 lbf·in
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2 x (16 - 12 AWG)

temperature of the conductor at magnet coil maximum permissible	75 °C
material of the conductor at magnet coil	CU
type of electrical connection for auxiliary contacts	screw-type terminals
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1 x (12 AWG), 2 x (16 - 14 AWG), 2 x (18 - 16 AWG)
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C
material of the conductor at contactor for auxiliary contacts	CU
type of electrical connection at overload relay for auxiliary contacts	screw-type terminals
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2 x (20 - 14 AWG)
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C
material of the conductor at overload relay for auxiliary contacts	CU
Short-circuit current rating	
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)
design of the short-circuit trip	Thermal magnetic circuit breaker
breaking capacity maximum short-circuit current (Icu)	
• at 240 V	14 kA
• at 480 V	10 kA
• at 600 V	10 kA
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14
Further information	
Industrial Controls - Product Overview (Catalogs, Broch www.usa.siemens.com/iccatalog Industry Mall (Online ordering system)	ures,)

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:14IUH320J


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/US/en/ps/US2:14IUH320J

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:14IUH320J&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:14IUH320J/certificate



last modified:

11/29/2021 🖸