





.XXX ±0.10

THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ORIGINAL 1





NOTES:

MATERIAL:

HOUSING: BLACK THERMOPLASTIC POLYESTER, UL94V-0

SHELL: STEEL, TIN PLATED

CONTACT: COPPER ALLOY, 15μ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT

CONTACT RESISTANCE: $25m\Omega$ MAX. INSULATOR RESISTANCE: $5000M\Omega$ min.

DIELECTRIC

WITHSTANDING VOLTAGE: 1000V AC rms

F#HS T

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.





EDAC INC
TORONTO, ONTARIO
CANADA
COLIALITY & SERVICE

THESE DRAWIN
ARE THE PROPE
SHALL NOT BE IF
OR USED AS TH
MANUFACTURE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
SHALL NOT BE REPRODUCED,OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

| SCALE: 1:1 | SHEET 1 OF 1 |
|-----------------------|--------------------|
| CHECKED: | DATE: |
| DRAWN: C.B | DATE: AUG. 01/2018 |
| SW REFERENCE NO.: 628 | M ASSEMBLY |

 DRAWING NUMBER:
 628-M25-321-BT1
 ISSUE

 PART NUMBER:
 628-M25-321-BT1
 1