

**Customer Part:**



**Description**

- Temperature compensated crystal oscillator (TCXO)
- Model IQXT-210-2
- Model Issue number 3

**Frequency Parameters**

- Frequency 19.20MHz
- Frequency Tolerance  $\pm 0.50\text{ppm}$
- Tolerance Condition @ 25°C & 3.3V
- Frequency Stability  $\pm 0.14\text{ppm}$
- Operating Temperature Range -40.00 to 85.00°C
- Ageing  $\pm 0.02\text{ppm}$  max per day,  $\pm 1\text{ppm}$  max per year
- Frequency Tolerance (measurement referenced to frequency observed with TA=25°C, Vs=3.3V and within 30 days after ex-works)
- Frequency Stability: TA varied across the operating temperature range, measurement referenced to frequency observed with TA=25°C, Vs=3.3V, load=10kΩ//10pF and temperature variable speed less than 2°C per minute.
- Ageing: TA=25°C, Vs=3.3V and after 1hr of operation.
- Supply Voltage Variation (measurement referenced to frequency observed with TA=25°C, Vs varied from 3.13V to 3.47V and load=10kΩ//10pF):  $\pm 0.1\text{ppm}$  max
- Load Variation (5% load change measurement referenced to frequency observed with TA=25°C, Vs=3.3V and load=10kΩ//10pF):  $\pm 0.1\text{ppm}$  max
- Short Term Stability (@ 25°C after 10mins power on): 5E-10/s typ @ 10MHz

**Electrical Parameters**


- Supply Voltage 3.3V  $\pm 5\%$
- Current Draw 10.000mA
- Current: TA=25°C, Vs=3.3V and load=10kΩ//10pF

**Output Details**


- Output Compatibility Clipped Sine
- Drive Capability 10kΩ//10pF
- Output Levels: 0.8V pk-pk min

**Noise Parameters**


- Phase Noise (@ 10MHz typ):
  - 90dBc/Hz @ 10Hz
  - 115dBc/Hz @ 100Hz
  - 135dBc/Hz @ 1kHz
  - 145dBc/Hz @ 10kHz
  - 148dBc/Hz @ 100kHz
  - 150dBc/Hz @ 1MHz



**Outline (mm)**



**Recommended Solder Pad Layout**



**Sales Office Contact Details:**

UK: +44 (0)1460 270200

USA: +1.760 668 8935

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)

Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)

**Customer Part:****Environmental Parameters**

- Storage Temperature Range: -55 to 105°C
- ESD Level:  
HBM, Class 2: 2000V to 4000V, JEDEC JS-001-2010  
Machine Model, Class B: 200V to 400V, JEDEC JS-001-2010
- Shock: IEC 60068-2-27, Test Ea: 100G acceleration for 6ms, half sinewave, in 3 mutually perpendicular planes
- Vibration: IEC 60068-2-6, Test Fc: 10Hz-2000Hz, 0.75mm amplitude, 10G acceleration, 30mins per cycle, in 3 mutually perpendicular planes, test duration 2hrs

**Manufacturing Details**

- Moisture Sensitivity Level: 2
- Maximum Reflow Temperature: 260°C (30secs max)

**Compliance**

- RoHS Status (2015/863/EU)      Compliant
- REACH Status                      Compliant
- MSL Rating (JDEC-STD-033):    2

**Packaging Details**

- Pack Style: Bulk      Loose in bulk pack  
Pack Size: 1
- *Alternative packing option available*

---

**Sales Office Contact Details:**

UK: +44 (0)1460 270200

USA: +1.760 668 8935

Email: [info@iqdfrequencyproducts.com](mailto:info@iqdfrequencyproducts.com)Web: [www.iqdfrequencyproducts.com](http://www.iqdfrequencyproducts.com)