

1T12CW 1.5RP series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Regulated



- General SMD package
- 1.5kVDC isolation
- + High efficiency up to 75%
- 🕂 RoHS compliance
- Short circuit protection (SCP)



Common specifications Short circuit protection:

Operation temperature range:

Storage temperature range: Storage humidity range:

MTBF (MIL-HDBK-217F@25°C):

Case temperature:

Cooling:

Case material:

Radiated emissions:



Ŧ	Operating	temperature	range:

- -40°C ~ +85°C
- \bigoplus International standard pinout
- + 100% burn in
- MTBF >630,000
 hours

Continuous

+110°C MAX

-40°C~+85°C -55°C~+125°C

95% MAX

Free air convection

Non-conductive plastic

EN55032 Class A

>630,000 hours, ground benign

DC-DC Converter

1 Watt

The 1T12CW_1.5RP series is specially designed for applications where a wide range input voltage power supplies are isolated from the input power supply in a distributed power supply system on a circuit board.

These products apply to:

- Where the voltage of the input power supply is wide range (voltage range <2:1);
 Where isolation is necessary between input and output
- (Isolation Voltage ≤1500VDC);
- 3) Where the regulation of the output voltage and the output ripple noise are demanded.

Output specifications							
ltem	Test condition		Тур	Max	Units		
Voltage tolerance				±2	%		
Minimum load	of full load	10			%		
Line regulation	High line to low line			±0.5	%		
Load regulation output load current change from 10% to 100%			±0.5	%			
Temperature drift	100% full load			±0.05	%/°C		
Over load protection			150		%		
Ripple & Noise	20MHz Bandwidth			100	mVp-p		
Switching frequency	Full load, nominal input		100		KHz		

Example:

- 1T12CW_0515S1.5RP
- 1 = 1WaT; T12 = SMT12; C = Series; W= Wide input; 5Vin; 15Vout; S = Single output; 1.5 = 1.5kVDC; R = Regulated output;
- P = Short circuit protection (SCP)

Note:

- 1. Unless otherwise specified, data in this data sheet should be tested under the conditions of Ta = 25° C, nominal input voltage and rated output current;
- Output filtering is required for operation. A minimum of 10µF is needed. Output capacitance may be increased for additional filtering, not to exceed 470µF.
- 3. To meet the reflected ripple requirements of the converter, an input impedance
- of less than 0.5 ohm from DC to 250KHz is required. 4. A negative output voltage may be obtained by connecting the +OUT to circuit ground and connecting –OUT as the negative output.
- All index testing methods in this datasheet are based on our Company's corporate standards.

Weight:		1.4g				
Dimensions:		15.24x11	.1x7.1mn	n		
Input specifications						
Item	Test condition		Min	Тур	Max	Units
Input voltage range					2:1	
Input Filter	Capacitor					

Protection Fuse recommended

Isolation specifications

Item	Test condition	Min	Тур	Max	Units
Isolation voltage	for 10sec.	1500			VDC
Isolation resistance		10 ⁹			Ω
Isolation capacitance		80			pF

1T12CW_1.5RP series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Regulated

Part Number	Input Voltage Range [V]	Output Voltage [VDC]	Output current [mA]	Input cur Full load	rent [mA] No load	Efficiency [%; Typ]	Capacitive load [µF; Max]
1T12CW_1205S1.5RP	9-18	5	200	111	20	75	1500
1T12CW_1212S1.5RP	9-18	12	83	111	25	75	470
1T12CW_1215S1.5RP	9-18	15	67	112	25	75	470
1T12CW_2405S1.5RP	18-36	5	200	56	12	75	1500
1T12CW_2412S1.5RP	18-36	12	83	55	15	75	470
1T12CW_2415S1.5RP	18-36	15	67	56	15	75	470
1T12CW_4805S1.5RP	36-72	5	200	28	5	75	1500
1T12CW_4812S1.5RP	36-72	12	83	28	5	75	470
1T12CW_4815S1.5RP	36-72	15	67	28	5	75	470
1T12CW_4824S1.5RP	36-65	24	40	28	7	72	470

Typical characteristics



Reflow soldering curve



The curve applies only to the hot air reflow soldering.

1T12CW_1.5RP series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Regulated

Simplified schematic

Single output



Typical applications

Single output



Input fuse selection guide

9-18V	18-36V	36-72V		
INPUT VOLTAGE(VDC)	INPUT VOLTAGE(VDC)	INPUT VOLTAGE(VDC)		
300mA Slow-Blow Type	150mA Slow-Blow Type	100mA Slow-Blow Type		
INPUT		OUTPUT		
	+Vin +Vout			
F	use			
	DC-DC CONVERTER			
·	VinVout			

Certain applications may require the installation of external fuse in front of the input.

1T12CW_1.5RP series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Regulated

Simplified schematic

Single output



Typical applications

Single output



Mechanical dimensions & footprint





NOTE : All Dimensions are in mm [inches] 1. Pin Size is 0.50x0.30mm[0.02x0.01"] 2. Pin is Tolerance .XX= ±0.07mm 3. Tolerance .X or .XX= ±0.5mm

PIN	1	2, 3	5	6	7, 8	10, 11	12
SINGLE	-Vin	NC	-Vout	+Vout	NC	NC	+Vin