# PIN Diode Shunt Switch Element 50 MHz to 10 GHz



### **MASW-011164**

Rev. V2

### Features

- 3 Terminal LPF Broadband Shunt Structure
- 50 MHz 10 GHz Broadband Frequency
- >40 W Peak Power Handling
- <0.1 dB Shunt Insertion loss
- >27 dB Shunt Isolation
- RoHS\* Compliant

### Applications

 Wireless Telecommunications Infrastructure & Test Instrument Applications

### Description


The MASW-011164 is a broadband, high linearity, medium power shunt switch element in a lead free  $1.9 \times 1.1 \text{ mm}$  DFN surface mount plastic package.

This device is designed for wireless telecommunications infrastructure and test instrument applications. It is also suited for other applications in  $0.05 \sim 10$  GHz.

## **Ordering Information**

Part Number	Package
MASW-011164-20120T	500 Piece Reel

# Pin Out / Schematic



# **Pin Configuration<sup>3</sup>**

Pin #	Pin Name	Description	
1	RF <sub>iN</sub>	RF Input	
2	RF <sub>OUT</sub>	RF Output	
3	Paddle <sup>4</sup>	Ground	

MACOM recommends connecting unused package pins to ground.

4. The exposed pad centered on the package bottom must be connected to RF, DC and thermal ground.

## Electrical Specifications: T<sub>A</sub> = +25°C

Parameter	Test Conditions	Units	Min.	Тур.	Max.
Breakdown Voltage (V <sub>B</sub> )	I <sub>R</sub> = 10 μΑ	V	400	600	—
Insertion Loss (I <sub>L</sub> )	V <sub>R</sub> = 25 V, 512 MHz V <sub>R</sub> = 25 V, 2.7 GHz	dB	_	0.08 0.10	_
Isolation (I <sub>so</sub> )	I <sub>F</sub> = 10 mA, 512 MHz I <sub>F</sub> = 10 mA, 2.7 GHz	dB	_	28 27	_
Input / Output Return Loss	V <sub>R</sub> = 25 V, 512 MHz V <sub>R</sub> = 25 V, 2.7 GHz	dB	_	34 37	_
Minority Carrier Lifetime (T <sub>L</sub> )	I <sub>F</sub> = 10 mA, I <sub>R</sub> = 6 mA, @ 50%	ns	_	3000	_

<sup>1</sup> 

\* Restrictions on Hazardous Substances, compliant to current RoHS EU directive.

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit <u>www.macom.com</u> for additional data sheets and product information.

# PIN Diode Shunt Switch Element 50 MHz to 10 GHz




# MASW-011164

Rev. V2


# **Absolute Maximum Ratings**

Parameter	Absolute Maximum	
Breakdown Voltage	600 V	
Forward Current	200 mA	
Junction Temperature	+175°C	
Storage Temperature	-65°C to +150°C	
Assembly Temperature	+260°C Per JEDEC STD-J-20C	


# **Typical Performance Curves**



#### Input Return Loss



#### Isolation



MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit <u>www.macom.com</u> for additional data sheets and product information.


2

# PIN Diode Shunt Switch Element 50 MHz to 10 GHz



MASW-011164 Rev. V2

# **Printed Circuit Board Layout**




NOTE: If possible, use copper filled vias underneath pin 3 for better thermals; otherwise, use vias that are plated through, filled and plated over.

Solder mask should provide a 60 µm clearance between copper pad and soldermask. Rounded pkg pads should have matching rounded solder mask openings.

Use circles or squares for the thermal land stencil such that only get 50% to 80% solder paste coverage.

## **Outline (2012)**



NOTES

1. DIMENSIONS DO NOT INCLUDE MOLD FLASHING

2. BURRS AND DUMBAR SHALL NOT EXCEED 0.002" PER SURFACE

3. LEAD CO-PLANARITY IS 0.003" MAXIMUM

#### 3

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit <u>www.macom.com</u> for additional data sheets and product information.



MASW-011164 Rev. V2

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.

<sup>4</sup> 

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. Visit <u>www.macom.com</u> for additional data sheets and product information.