

# VC-TXO-39SMX Series

## VC-TCXO



The VC-TXO-39SMX is a VC (Voltage Controlled) TCXO (Temperature Compensated Crystal Oscillator) featuring very tight stability over a wide temperature range. The small SMD ceramic package measures 11.4 x 9.6 x 2.3 mm. The voltage control has a tuning range of  $\pm 12$  ppm typical. The low profile package is ideal for wireless communications applications.

[Request a Sample](#)

### OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS



- Highly stable output
- RoHS Compliant (Pb Free)
- Voltage control function
- Tape and Reel (500 pcs)

Parameters	Conditions	VC-TXO-39SMX (3V)			Units
		MIN	TYP	MAX	
Frequency Range		10.000		19.440	MHz
Operating Temperature		-30		+75	°C
Frequency Stability	Standard			$\pm 2.5$	PPM
Option A	-20 ~ +75°C			$\pm 1.5$	PPM
Supply Voltage Change	+3V $\pm 5\%$			$\pm 0.3$	PPM
Load Change	10k $\Omega$ $\pm 10\%$ // 10pF $\pm 10\%$			$\pm 0.3$	PPM
Aging	First year @ 25°C			$\pm 1$	PPM
Storage Temperature		-40		+85	°C
Supply Voltage	+3.0 V DC Nominal	+2.85	+3.0	+3.15	V DC
Current Consumption	10k $\Omega$ $\pm 10\%$ // 10pF $\pm 10\%$			1.5	mA
Output Voltage	Clipped since wave (DC-Cut)	0.8			Vp-p
Output Load	10k $\Omega$ $\pm 10\%$ // 10pF $\pm 10\%$				
Frequency Control Range	+1.5V DC $\pm 1$ V Positive Slope	$\pm 9$	$\pm 12$		PPM
Control Voltage		+0.5	+1.5	+2.5	V

### Part Numbering Guide: Example VC-TXO-39SMX-128-A-TR

Series - Frequency Abbreviations - Frequency Stability - Packaging




VC-TXO-39SMX

128 = 12.800 MHz

A =  $\pm 1.5$  ppm

TR = Tape & Reel  
500 pcs/Reel

**Package Dimensions (mm)**



**Figure 2) Test Circuit**

**Figure 1) Top, Side, and Bottom views**

Pin Connections	
#1	V Control
#2	Ground
#3	Output
#4	V <sub>CC</sub>