

Fusible Power Metal Film Leaded Resistors



A homogenous film of metal alloy is deposited on a high grade ceramic body. After a helical groove has been cut in the resistive layer, tinned electrolytic copper wires are welded to the end-caps. The resistors are coated with a red non-flammable lacquer, which provides electrical, mechanical, and climatic protection.

The encapsulation is resistant to all cleaning solvents in accordance with "MIL-STD 202E, method 215" and "IEC 60068-2-45".

FEATURES

- Metal film technology
- High power (upto 3 W) in small package
- Small standard sizes (0207/0414/0617)
- High stability, reliability and uniformity characteristics
- Defined interruption behaviour (fusing time)
- Various forming styles
- Non flammable
- Compatible with lead (Pb)-free and lead containing soldering processes
- Lead (Pb)-free and RoHS compliant



APPLICATIONS

- Audio
- Video

TECHNICAL SPECIFICATIONS			
DESCRIPTION	NFR01	NFR02	NFR03
Resistance Range ⁽¹⁾	0.47 Ω to 1 kΩ		
Resistance Tolerance	± 5 %; E24 series		
Temperature Coefficient	± 200 ppm/K		
Climatic Category (LCT/UCT/days)	55/155/56		
Rated Dissipation P_{70}	1 W	2 W	3 W
Maximum Permissible Voltage: DC or RMS	350 V	500 V	
Fusing Power	0.47 Ω to 10 Ω; ≥ 20 x Pn		
	10.1 Ω to 1 kΩ; ≥ 16 x Pn		
Fusing Time	≤ 60 s		
Maximum Resistance Change at P_{70} for Resistance Range, ΔR max., after:	Load	± (5 % R + 0.1 Ω)	
	Climatic Tests	± (3 % R + 0.1 Ω)	
	Resistance to Soldering Heat	± (1 % R + 0.05 Ω)	

Note

⁽¹⁾ Resistance values below 0.47 Ω with ± 10 % tolerance are available on request

NFR01, NFR02, NFR03



Vishay BCcomponents Fusible Power Metal Film Leaded Resistors

12NC INFORMATION FOR HISTORICAL CODING REFERENCE ONLY

- The resistors have a 12 digit ordering code starting with 2306
- The next 5 digits indicate the resistor type and packaging
- The last 3 digits indicate the resistance value:
 - The first 2 digits indicate the actual resistance value
 - The last digit indicates the resistance decade in accordance with table

Last Digit of 12NC Indicating Resistance Decade

RESISTANCE DECADE	LAST DIGIT
0.47 Ω to 0.91 Ω	7
1 Ω to 9.1 Ω	8
10 Ω to 91 Ω	9
100 Ω to 910 Ω	1
1 kΩ	2

12NC Example

NFR01, 1 Ω, ± 5 %, ammpack 1000 pieces is
2306 208 13108

12NC - resistor type and packaging						
DESCRIPTION			ORDERING CODE 2306			
			BANDOLIER IN AMMOPACK			BANDOLIER ON REEL
TYPE	TAPE WIDTH	TOL.	500 UNITS	1000 UNITS	5000 UNITS	5000 UNITS
NFR01	52.5	± 5 %	-	208 13...	208 53...	208 23...
NFR02	52.5	± 5 %	-	209 13...	-	209 23...
NFR03	63.0	± 5 %	210 13...	-	-	-

PART NUMBER AND PRODUCT DESCRIPTION

PART NUMBER (1): NFR0100001008JA100

N	F	R	0	1	0	0	0	0	1	0	0	8	J	A	1	0	0
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

MODEL/SIZE	SPECIAL CHARACTER	TCR/MATERIAL	VALUE	TOLERANCE	PACKAGING (2)	SPECIAL
NFR0100 NFR0200 NFR0300	0 = neutral	0 = standard	3 digit value 1 digit multiplier Multiplier: 7 = *10 ⁻³ 8 = *10 ⁻² 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² 3 = *10 ³ 4 = *10 ⁴	J = ± 5 %	A1 A5 R5 AC	up to 2 digits 00 = standard

PRODUCT DESCRIPTION: NFR01 5 % A1 1R0

NFR01	5 %	A1	1R0
MODEL	TOLERANCE	PACKAGING (2)	RESISTANCE VALUE
NFR01 NFR02 NFR03	± 5 %	A1 A5 R5 AC	1R0 = 1 Ω 470R = 470 Ω


Notes

- (1) The PART NUMBER is shown to facilitate the introduction of the unified part numbering system
 (2) Please refer to table PACKAGING, see next page



PACKAGING				
MODEL	REEL		BOX	
	PIECES	CODE	PIECES	CODE
NFR01	5000	R5	1000 5000	A1 A5
NFR02	5000	R5	1000	A1
NFR03	-	-	500	AC

DIMENSIONS




DIMENSIONS - resistor types, mass and relevant physical dimensions						
TYPE	L ₁ max. (mm)	L ₂ max. (mm)	D _{max.} (mm)	Ø d (mm)	A (mm)	MASS (g)/ 100 pieces
NFR01	6.5	8.5	2.5	0.58 ± 0.05	52.5 ± 1.5	22
NFR02	10	12	4	0.80 ± 0.03	52.5 ± 1.5	50
NFR03	16.7	19.5	5.3	0.80 ± 0.03	63.0 ± 1.5	120

MARKING

The nominal resistance and tolerance are marked on the resistor using four colored bands in accordance with IEC 60062 "Color code for fixed resistors". There is a fifth black band in order to indicate the type of resistor. Standard values of nominal resistance are taken from the E24 series for resistors with a tolerance of ± 5 %.

FUNCTIONAL PERFORMANCE




Derating - Standard Operation

Maximum dissipation ($P_{max.}$) in percentage of rated power as a function of ambient temperature (T_{amb})




APPLICATION INFORMATION

NFR01




Hot spot temperature rise (ΔT) as a function of dissipated power




Temperature rise (ΔT) at the lead end (soldering point) as a function of dissipated power at various leads lengths after mounting



NFR02



Hot spot temperature rise (ΔT) as a function of dissipated power



Temperature rise (ΔT) at the lead end (soldering point) as a function of dissipated power at various leads lengths after mounting

NFR03

 Hot spot temperature rise (ΔT) as a function of dissipated power

 Temperature rise (ΔT) at the lead end (soldering point) as a function of dissipated power at various leads lengths after mounting

FUSING CHARACTERISTIC

The resistors will fuse without the risk of fire and within an indicated range of overload. Fusing means that the resistive value of the resistor increases at least 100 times.

Resistance Range	Power Overload	Fusing Time
0.47 Ω - 10 Ω	≥ 20 x maximum dissipation at 70 °C (P_n)	≤ 60 s
10.1 Ω - 1 k Ω	≥ 16 x maximum dissipation at 70 °C (P_n)	

TESTS AND REQUIREMENTS

Essentially all tests are carried out in accordance with the schedule of IEC 60115-1, category 55/155/56 (rated temperature range - 55 to + 155 °C; damp heat, long term, 56 days) and along the lines of IEC 60068-2; "Recommended basic climatic and mechanical robustness testing procedure for electronic components" and under standard atmosphere conditions according to IEC 60068-1 subclause 5.3, unless otherwise specified. In some instances deviations from IEC applications were necessary for our specified method.

PERFORMANCE						
IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)		
				NFR01	NFR02	NFR03
4.8	-	Temperature coefficient	Between - 55 °C and + 155 °C	± 200 ppm/K		
4.25.1	-	Endurance at 70 °C	1000 h; loaded with P_n or V_{max} ; 1.5 h ON; 0.5 h OFF	$\pm (5\% R + 0.1 \Omega)$		
4.26	-	Accidental overload	Overload of 5, 10, 16, 25, 40, 63 and 100 times the rated power, but the applied voltage shall not exceed four times the limiting voltage.	Non-flammable		

PERFORMANCE						
IEC 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)		
				NFR01	NFR02	NFR03
4.24	3 (Ca)	Damp heat, steady state	56 days; 40 °C; 90 to 95 % RH loaded with 0.01 Pn	R_{ins} min. $10^3 M\Omega$ $\pm (3 \% R + 0.1 \Omega)$		
4.16 4.16.2 4.16.3 4.16.4	21 (U) 21 (Ua1) 21 (Ub) 21 (Uc)	Robustness of terminations: Tensile all samples Bending half number of samples Torsion other half of samples	Load 10 N; 10 s Load 5 N; 4 x 90° 3 x 360° in opposite direction	No damage $\pm (0.5 \% R + 0.05 \Omega)$		
4.19	14 (Na)	Rapid change of temperature	30 min at LCT; 30 min at UCT; LCT = - 55 °C; UCT = 155 °C; 5 cycles	$\pm (1 \% R + 0.05 \Omega)$	$\pm (1 \% R + 0.05 \Omega)$	$\pm (2 \% R + 0.05 \Omega)$
4.23 4.23.2 4.23.3 4.23.4 4.23.6	2 (Ba) 30 (Db) 1 (Aa) 30 (Db)	Climatic sequence Dry heat Damp heat (accelerated) Cold Damp heat, (accelerated) remaining cycles	16 h, 155 °C 24 h; 25 °C to 55 °C 90 % to 100 % RH; 1 cycle 2 h, - 55 °C 5 days; 25 °C to 55 °C 90 to 100 % RH	R_{ins} min. $10^3 M\Omega$ $\pm (3 \% R + 0.1 \Omega)$		
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 500 Hz; displacement 1.5 mm or acceleration 10 g; 6 h (3 x 2 h)	No visual damage $\pm (0.5 \% R + 0.05 \Omega)$		
4.17	20 (Ta)	Solderability (after ageing)	16 h at 155 °C; immersed in flux 600, leads immersed 2 mm in solder bath at (235 ± 5) °C for (2 ± 0.5) s	Good tinning (≥ 95% covered); no visible damage		
4.18	20 (Tb)	Resistance to soldering heat	Solder bath method; (350 ± 10) °C; 6 mm from body; for 3 s	$\pm (1 \% R + 0.05 \Omega)$		
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; MIL STD 202E	No visible damage		
4.7	-	Voltage proof on insulation	500 V _{RMS} during 1 min, V-block method	No flashover or breakdown		
4.6.1.1	-	Insulation resistance	500 V _{DC} during 1 min, V-block method	R_{ins} min. $10^4 M\Omega$		



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.