

(2.54 mm) .100"

SL, SDL SERIES

LOW-PROFILE MACHINED SOCKET STRIPS

FEATURES

- Achieve low-profile without sacrificing insertion depth!
- Choice of four precision screw machined lead styles.
- Exceptionally low-profile, down to (2.11 mm) .083" off of board.
- Mates with BBL or BDL for board stacking spaces down to (3.89 mm) .153"

SPECIFICATIONS

For complete specifications see www.samtec.com?SL or www.samtec.com?SDL

Insulator Material:
Black Glass Filled Polyester (SDL)
Black Liquid Crystal Polymer (SL)

Contact/Shell Materials:
BeCu/Brass
Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Operating Temp Range:
-55 °C to +125 °C with Gold
-55 °C to +105 °C with Tin

RoHS Compliant:


Yes
Lead-Free Solderable:
SL: Yes
SDL: No, Lead Wave only

RECOGNITIONS


For complete scope of recognitions see www.samtec.com/quality



Mates with:
TS, TD, HTS, BBS, BBD,
BBL, BDL, BHS



Low Insertion Force (LIF) Available



Note:
Some lengths, styles and options are non-standard, non-returnable.