

DATASHEET

Sidelooker Infrared LED IR908-7C-F



Features

- High reliability
- High radiant intensity
- Peak wavelength λp=940nm
- 2.54mm lead spacing
- Low forward voltage
- Pb free
- This product itself will remain within RoHS compliant version
- Compliance with EU REACH
- Compliance Halogen Free(Br < 900ppm, Cl < 900ppm, Br+Cl < 1500ppm)

Description

- EVERLIGHT's Infrared emitting diode IR908-7C-F is a high intensity diode, molded in a plastic package
- The miniature side-facing device has a chip, that emits radiation from the side of the clear package

Applications


- Mouse
- Optoelectronic switch
- Infrared applied system

Device Selection Guide

Part Category Chip Material		Lens Color
IR	GaAlAs	Water Clear



Package Dimension



Notes: 1. All dimensions are in millimeters

2. Tolerances unless dimensions ±0.3mm

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Rating	Unit
Continuous Forward Current	I _F	50	mA
Reverse Voltage	V_{R}	5	V
Operating Temperature	T_{opr}	-25 ~ +85	°C
Storage Temperature	T _{stg}	-40 ~ +85	°C
Soldering Temperature *1	T _{sol}	260	°C
Power Dissipation at (or below)	P _d	75	mW
25°C Free Air Temperature	Γd	73	IIIVV

Notes: *1 Soldering time ≤ 5 seconds

Electro-Optical Characteristics (Ta=25℃)

			_	_	_	
Parameter	Symbol	Condition	Min.	Тур.	Max.	Units
Light Current	I _{C(ON)}	I_F =4mA, V_{CE} =3.5V	143		1274	μA
Peak Wavelength	λр	I _F =20mA		940		nm
Spectral Bandwidth	Δλ	I _F =20mA		50		nm
Forward Voltage	V _F	I _F =20mA		1.25	1.60	V
Reverse Current	I _R	V _R =5V			10	μA
View Angle	201/2	I _F =20mA		40		deg

Rank

Condition: I_F =4mA, V_{CE} =3.5V

Symbol	Condition	Ranks	Min.	Max.	Unit
		E1	143	255	
		E2	214	343	
		E3	286	431	
		E4	357	519	
	I _F =4mA	E5	428	608	μΑ
$I_{C(ON)}$	V _{CE} =3.5V	E6	500	696	
		E7	571	784	
		E8	643	872	
		E9	714	960	
		E10	785	1049	
		E11	857	1137	

Rough Ranks


Symbol	Condition	Ranks	Min.	Max.	Unit	
I _{C(ON)} I _F =4mA V _{CE} =3.5V	7-2	306	441			
	I₅=4mA	7-1	347	550		
	V _{CE} =3.5V	6-2	465	750	μΑ	
		6-1	650	1274		



Test Method For $I_{C(ON)}$:

Condition: I_F=4mA, V_{CE}=3.5V

The intensity testing method for infrared emitting diode





Typical Electro-Optical Characteristics Curves

Fig.1 Forward Current vs.

Ambient Temperature




Fig.2 Spectral Distribution




Fig.3 Forward Current vs. Forward Voltage






Fig. 4 Relative Radiant Intensity vs. Angular Displacement







CPN: Customer Part Number

P/N: Part Number

QTY: Packing Quantity

CAT: Ranks

· REF: Reference

LOT No: Lot Number

Notes

Lead Forming

- 1. During lead frame bending, the lead frame should be bent at a distance more than 3mm from bottom of the epoxy.
 - Note: Must fix lead frame and do not touch epoxy before bending to avoid LEDs broken.
- 2. Lead forming should be done before soldering.
- 3. Avoid stressing the LED package during leads forming. The stress to the base may damage the LED's characteristics or it may break the LEDs.
- 4. Cut the LED lead frame at room temperature. Cutting the lead frames at high temperatures may cause failure of the LEDs.
- 5. When mounting the LEDs onto a PCB, the PCB holes must be aligned exactly with the lead position of the LED. If the LEDs are mounted with stress at the leads, it causes deterioration of the epoxy resin and this will degrade the LEDs.

Storage

- 1. The LEDs should be stored at 10~30°C and 70%RH or less after being shipped from Everlight and the storage life limits are 3 months. If the LEDs are stored for 3 months or more, they can be stored at 10°C~25°C and 20%RH~60%RH for a year in a sealed container with a nitrogen atmosphere. After opening the package, the devices must be stored at 10°C~25°C and 20%RH~60%RH, and suggested to be used within 24 hours or as soon as possible. Besides, suggest that the remaining devices seal in the package bag as soon as possible please.
- 2. Please avoid rapid transitions in ambient temperature, especially in high humidity environments where condensation can occur.




Soldering

1. Careful attention should be paid during soldering. When soldering, leave more than 3mm from solder joint to epoxy bulb, and soldering beyond the base of the tie bar is recommended.

2. Recommended soldering conditions:

Hand Soldering		DIP Soldering		
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	100°C Max. (60 sec Max.)	
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max	
Distance	3mm Min.(From solder joint to epoxy bulb)	Distance	3mm Min. (From solder joint to epoxy bulb)	

3. Recommended soldering profile



- 4. Avoiding applying any stress to the lead frame while the LEDs are at high temperature particularly when soldering.
- 5. Dip and hand soldering should not be done more than one time
- 6. After soldering the LEDs, the epoxy bulb should be protected from mechanical shock or vibration until the LEDs return to room temperature.
- 7. A rapid-rate process is not recommended for cooling the LEDs down from the peak temperature.
- 8. Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LEDs.
- 9. Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.

Cleaning

Do not clean the LEDs by the ultrasonic.

Heat Management

- Heat management of LEDs must be taken into consideration during the design stage of LED application. The current should be de-rated appropriately by referring to the de-rating curve found in each product specification.
- 2. The temperature surrounding the LED in the application should be controlled. Please refer to the data sheet de-rating curve.



ESD (Electrostatic Discharge)

- 1. The products are sensitive to static electricity or surge voltage. ESD can damage a die and its reliability.
- 2. When handling the products, the following measures against electrostatic discharge are strongly recommended:

Eliminating the charge

Grounded wrist strap, ESD footwear, clothes and floors

Grounded workstation equipment and tools

ESD table/shelf mat made of conductive materials

- 3. Proper grounding is required for all devices, equipment, and machinery used in product assembly. Surge protection should be considered when designing of commercial products
- 4. If tools or equipment contain insulating materials such as glass or plastic, the following measures against electrostatic discharge are strongly recommended:

Dissipating static charge with conductive materials

Preventing charge generation with moisture

Neutralizing the charge with ionizers

Directions for use

The LEDs should be operated with forward bias. The driving circuit must be designed so that the LEDs are not subjected to forward or reverse voltage while it is off. If reverse voltage is continuously applied to the LEDs, it may cause migration resulting in LED damage.

Other

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 3. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 4. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.
- 5. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.