

Ordering Information:

A2012WRA-F-XP - *** - ** - **
 1 2 3 4

1.Part NO.

2.Material:

(Blank):Nylon 66,UL94V-0

GWT: Nylon 66,UL94V-0(Beige),IEC 60335-1,5th Edition
 Glow Wire Capable.

3.Color:

(Blank):White

BK:Black

RD:Red

BL:Blue

GN:Green

OR:Orange

BR:Brown

PK:Pink






YL:Yellow

GY:Gray


4.Finish:

(Blank):Tin over Nickel


G:Gold over Nickel




2P~4P



5P~6P



7P~9P



10P~16P

SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 10mΩ Max.

Insulation Resistance: 1000MΩ Min.

Withstanding Voltage: 800V AC/minute

Pin Material:Brass/Tin over Nickel

Material: Nylon 66,UL94V-0(Ivory)

Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	2.00	6.00	10P	18.00	22.00
3P	4.00	8.00	11P	20.00	24.00
4P	6.00	10.00	12P	22.00	26.00
5P	8.00	12.00	13P	24.00	28.00
6P	10.00	14.00	14P	26.00	30.00
7P	12.00	16.00	15P	28.00	32.00
8P	14.00	18.00	16P	30.00	34.00
9P	16.00	20.00			

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE
mm	3:1	1 of 1	2.00mm Pitch Right angle Wafer
DRAWN	CHK'D	APPR	
Chengbiao Ye	Djankui Wan	Jack Yin	DRAWING NO.
General Tolerances	THIRD ANGLE PROJECTION		A2012WRA-F-XP
x,xx±0.25			REV
x,xxx±0.20			A3
x,xxxx±0.15			
ANGLES ±1°			

REV	DESCRIPTION	DATE
A3	CHANGE THE DRAWING	2023.02.14
A2	CHANGE THE DRAWING	2019.04.24
A1	CHANGE THE MATERIAL	2019.01.08
A0	NEW RELEASE	2014.06.06