



.XX ±0.13 .XXX ±0.10





NOTES:


MATERIAL:

HOUSING: BLACK THERMOPLASTIC POLYESTER, UL94V-0 STEEL, TIN PLATED SHELL: CONTACT: COPPER ALLOY, 30µ GOLD PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT CONTACT RESISTANCE: $25m\Omega$ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC rms

	628 SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 628M ASSEMBLY		
			DRAWN: C.B	DATE: AUG. 01/20	018
			CHECKED:	DATE:	
	EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1	SHEET 1 OF	1
	TORONTO, ONTARIO CANADA		DRAWING NUMBER: 628-M2	5-621-BT4	ISSUE
	YOUR CONNECTION TO QUALITY & SERVICE		PART NUMBER: 628-M2	5-621-BT4	1



COMPLIANT

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.