3RA2210-0AA15-2BB4

Data sheet



Fuseless motor starter Reversing operation 600VAC Size S00 0.11-0.16a 24V DC screw connection For screw mounting Or 35 mm rail-mounting Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NC (per contactor)

product brand name	SIRIUS		
product designation	non-fused motor starter 3RA2		
design of the product	reversing starter		
manufacturer's article number			
 of the supplied contactor 	3RT2015-1BB42		
 of the supplied circuit-breakers 	3RV2011-0AA10		
 of the supplied link module 	3RA1921-1DA00		
General technical data			
size of the circuit-breaker	S00		
size of load feeder	S00		
product extension auxiliary switch	Yes		
insulation voltage with degree of pollution 3 at AC rated value	690 V		
degree of pollution	3		
surge voltage resistance rated value	6 kV		
shock resistance according to IEC 60068-2-27	6g / 11 ms		
mechanical service life (switching cycles) of contactor typical	30 000 000		
type of assignment	2		
Substance Prohibitance (Date)	03/01/2017		
Ambient conditions			
ambient temperature			
 during operation 	-20 +60 °C		
during storage	-50 +80 °C		
 during transport 	-55 +80 °C		
Main circuit			
number of poles for main current circuit	3		
design of the switching contact	electromechanical		
adjustable current response value current of the current-dependent overload release	0.11 0.16 A		
operating voltage			
rated value	690 V		
 at AC-3 rated value maximum 	690 V		
operating frequency rated value	50 60 Hz		
operational current at AC-3 at 400 V rated value	0.16 A		
operating power at AC-3			
 at 400 V rated value 	40 W		
at 500 V rated value			
at 500 v fated value	40 W		
• at 690 V rated value	40 W 60 W		

control supply voltage at DC	0.4.14		
• rated value	24 V		
holding power of magnet coil at DC	4 W		
Auxiliary circuit	4		
number of NC contacts for auxiliary contacts	- 1		
number of NO contacts for auxiliary contacts	0		
Protective and monitoring functions	01.400.40		
trip class	CLASS 10		
design of the overload release	thermal (bimetallic)		
response value current of instantaneous short-circuit trip unit	2.08 A		
Short-circuit protection			
product function short circuit protection	Yes		
design of the short-circuit trip	magnetic		
conditional short-circuit current (Iq)			
 at 690 V according to IEC 60947-4-1 rated value 	100 000 A		
 at 400 V according to IEC 60947-4-1 rated value 	153 000 A		
at 500 V according to IEC 60947-4-1 rated value	100 000 A		
Installation/ mounting/ dimensions			
mounting position	vertical		
fastening method	Snap-mounted to DIN rail or	screw-mounted with ac	dditional push-in lug
height	170 mm		
width	90 mm		
depth	97.1 mm		
required spacing			
 for grounded parts 			
— forwards	0 mm		
— backwards	0 mm		
— upwards	20 mm		
— at the side	9 mm		
— downwards	10 mm		
for live parts			
— forwards	0 mm		
— backwards	0 mm		
— upwards	20 mm		
— downwards	10 mm		
— at the side	9 mm		
Connections/ Terminals			
type of electrical connection for main current circuit	screw-type terminals		
type of connectable conductor cross-sections	•		
for main contacts stranded	0.5 4 mm², 2x (0.75 2.5	5 mm²)	
 at AWG cables for main contacts 	2x (20 16), only for contactor 2x (18 14), 2x 12		
connectable conductor cross-section for main contacts finely stranded with core end processing	0.5 2.5 mm ²		
Safety related data			
B10 value with high demand rate according to SN 31920	1 000 000		
proportion of dangerous failures with high demand rate according to SN 31920	73 %		
protection class IP on the front according to IEC 60529	IP20		
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	ct from the front	
Certificates/ approvals			
		For use in hazard-	Declaration of
General Product Approval		ous locations	Conformity



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certificate

Type Test Certificates/Test Report







Marine / Shipping

other









Confirmation

Vibration and Shock

Railway

Dangerous Good

<u>Transport Information</u>

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-0AA15-2BB4

Cax online generator

 $\underline{\text{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RA2210-0AA15-2BB4}$

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0AA15-2BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2210-0AA15-2BB4&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0AA15-2BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-0AA15-2BB4&objecttype=14&gridview=view1

last modified: 12/15/2020 🖸