




Wirewound Resistors, Industrial Power, Tubular



FEATURES

- High temperature silicon coating
- Complete welded construction
- Excellent for intermittent power and pulsing applications
- Available in non-inductive styles (model NHLW) with Ayrton-Perry winding
- Axial or radial terminals for through hole or lead weld applications
- Excellent stability in operation (< 3 % change in resistance)
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS* Available

HALOGEN FREE Available

GREEN (5-2008) Available

Note

* This datasheet provides information about parts that are RoHS-compliant and/or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.


STANDARD ELECTRICAL SPECIFICATIONS					
GLOBAL MODEL	HISTORICAL MODEL	POWER RATING $P_{25^{\circ}\text{C}}$ W	RESISTANCE RANGE Ω $\pm 5\%$	RESISTANCE RANGE Ω $\pm 10\%$	WEIGHT (typical) g
HLW03 NHLW03	HLW-3 NHLW-3	3	1.0 to 6K 1.0 to 700	0.10 to 6K 1.0 to 700	1.16
HLW05 NHLW05	HLW-5 NHLW-5	5.25	1.0 to 15K 1.0 to 1.9K	0.10 to 15K 1.0 to 1.9K	2.12
HLW06 NHLW06	HLW-6 NHLW-6	8	1.0 to 20.5K 1.0 to 2.7K	0.10 to 20.5K 1.0 to 2.7K	4.60
HLW10 NHLW10	HLW-10 NHLW-10	10	1.0 to 29K 1.0 to 3.7K	0.10 to 29K 1.0 to 3.7K	6.24
HLW12 NHLW12	HLW-12 NHLW-12	12	1.0 to 58K 1.0 to 3.9K	0.10 to 58K 1.0 to 3.9K	6.60
HLW15 NHLW15	HLW-15 NHLW-15	15	1.0 to 60K 1.0 to 4.3K	0.10 to 60K 1.0 to 4.3K	8.82
HLW20 NHLW20	HLW-20 NHLW-20	20	1.0 to 95K 1.0 to 6.8K	0.10 to 95K 1.0 to 6.8K	11.36

TECHNICAL SPECIFICATIONS		
PARAMETER	UNIT	HLW RESISTOR CHARACTERISTICS
Temperature Coefficient	ppm/ $^{\circ}\text{C}$	± 30 for 10 Ω and above; ± 50 for 1 Ω to 9.9 Ω ; ± 90 for 0.1 Ω to 0.99 Ω
Short Time Overload	-	10 x rated power for 5 s
Dielectric Withstanding Voltage	V_{AC}	1000, from terminal to mounting hardware
Maximum Working Voltage	V	$(P \times R)^{1/2}$
Insulation Resistance	Ω	1000 M Ω minimum dry, 100 M Ω minimum after moisture test
Operating Temperature Range	$^{\circ}\text{C}$	-55 to +350

GLOBAL PART NUMBER INFORMATION																	
Global Part Numbering example: NHLW12A1Z10R00JF																	
N	H	L	W	1	2	A	1	Z	1	0	R	0	0	J	F		
GLOBAL MODEL	TERMINAL DESIGNATION	TERMINAL FINISH	RESISTANCE VALUE	TOLERANCE	PACKAGING CODE	SPECIAL											
NHLW12 (see "Standard Electrical Specifications" table above for additional P/N's)	A1 A2 R1 R2	E = lead (Pb)-free Z = tin / lead	R = decimal K = thousand 10R00 = 10.0 Ω 1K000 = 1 k Ω	J = $\pm 5.0\%$ K = $\pm 10.0\%$	E = lead (Pb)-free foam pack F = tin / lead foam pack (F01)	(dash number) (up to 2 digits) from 1 to 99 as applicable											
Historical Part Numbering example: NHLW-12-A1Z 10 Ω 5 % F01																	
NHLW-12	A1Z	10 Ω	5 %	F01													
HISTORICAL MODEL	TERMINAL/FINISH	RESISTANCE VALUE	TOLERANCE	PACKAGING													



DIMENSIONS in inches [millimeters]



GLOBAL MODEL	A (MAX.)	B TYP.	C ± 0.031 [0.79]	D TYP.	CORE DIMENSIONS			AXIAL TERMINAL DESIGNATION	RADIAL TERMINAL DESIGNATION	BRACKET TYPE ⁽¹⁾
					LENGTH ± 0.063 [1.59]	O.D.	I.D. ± 0.031 [0.79]			
HLW03 NHLW03	0.297 [7.54]	0.282 [7.16]	0.063 [1.59]	0.047 [1.19]	0.438 [11.11]	0.203 [5.16]	0.125 [3.18]	A2Z	R2Z	-
HLW05 NHLW05	0.344 [8.73]	0.469 [11.91]	0.063 [1.59]	0.047 [1.19]	0.625 [15.88]	0.250 [6.35]	0.125 [3.18]	A2Z	R2Z	-
HLW06 NHLW06	0.406 [10.32]	0.688 [17.48]	0.125 [3.18]	0.094 [2.38]	1.000 [25.40]	0.313 [7.94]	0.188 [4.76]	A1Z	R1Z	101, 204, 301
HLW10 NHLW10	0.563 [14.28]	0.688 [17.48]	0.125 [3.18]	0.094 [2.38]	1.000 [25.40]	0.438 [11.11]	0.313 [7.94]	A1Z	R1Z	101, 203, 301
HLW12 NHLW12	0.406 [10.32]	1.438 [36.53]	0.125 [3.18]	0.094 [2.38]	1.750 [44.45]	0.313 [7.94]	0.188 [4.76]	A1Z	R1Z	101, 204, 301
HLW15 NHLW15	0.563 [14.29]	1.188 [30.18]	0.125 [3.18]	0.094 [2.38]	1.500 [38.10]	0.438 [11.11]	0.313 [7.94]	A1Z	R1Z	101, 203, 301
HLW20 NHLW20	0.563 [14.29]	1.688 [42.88]	0.125 [3.18]	0.094 [2.38]	2.000 [50.80]	0.438 [11.11]	0.313 [7.94]	A1Z	R1Z	101, 203, 301

Note

⁽¹⁾ Brackets are available for mounting HLW series resistors - see "Mounting Hardware" section.

TERMINAL FINISH

Terminals are 20 AWG for HLW03 and HLW05 size and 18 AWG for all other sizes. "E" Finish - 100 % Sn, coated Copperweld®. "Z" Finish - 60/40 Sn/Pb coated Copperweld®.

MOUNTING HARDWARE

Mounting hardware is available for HLW resistors, see "HL Brackets and Sliders" datasheet for more information: www.vishay.com/doc?30279.

MATERIAL SPECIFICATIONS

Element: copper-nickel alloy of nickel-chrome alloy, depending on resistance value

Core: ceramic, steatite


Coating: special high temperature silicone

Standard Terminals: model "E" terminals are tinned Copperweld®

Terminal Bands: steel

Part Marking: Dale, model, wattage, value, tolerance, date code

DERATING





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.