SIEMENS

Data sheet

3RA2220-1BB23-0BB4



Combination Starter Reversing FLA Range 1.4-2A 3 Pole 24VDC Coil S0 Open Type 1NO <(>&<)> 1NC Aux

product brand name	SIRIUS
product designation	non-fused motor starter 3RA2
design of the product	reversing starter
manufacturer's article number	
of the supplied contactor	<u>3RT2023-1BB40</u>
of the supplied circuit-breakers	3RV2011-1BA10
 of the supplied RH assembly kit 	3RA2923-1BB1
 of the supplied busbar adapter 	3RA2922-1AA00
of the supplied link module	3RA2921-1BA00
of the supplied standard mounting rail adapter	3RA2922-1AA00
General technical data	
size of the circuit-breaker	S00
size of load feeder	S0
product extension auxiliary switch	Yes
insulation voltage with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	10 000 000
type of assignment	2
Ambient conditions	
ambient temperature	
during operation	-20 +60 °C
during storage	-50 +80 °C
during transport	-55 +80 °C
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	1.4 2 A
operating voltage	
rated value	690 V
at AC-3 rated value maximum	690 V
operating frequency rated value	50 60 Hz
operational current at AC-3 at 400 V rated value	1.9 A
operating power at AC-3	
at 400 V rated value	750 W
at 500 V rated value	750 W

• at 690 V rated value	1 100 W
Control circuit/ Control	1 100 11
control supply voltage at DC • rated value	24 V
holding power of magnet coil at DC	5.9 W
Auxiliary circuit	
number of NC contacts for auxiliary contacts	2
number of NO contacts for auxiliary contacts	2
Protective and monitoring functions	
trip class	CLASS 10
design of the overload release	thermal (bimetallic)
response value current of instantaneous short-circuit trip	26 A
unit	
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
• at 480 V rated value	1.63 A
at 600 V rated value	1.72 A
yielded mechanical performance [hp]	
for single-phase AC motor at 220 V rated value.	0.12 hp
— at 230 V rated value	0.13 hp
 for 3-phase AC motor at 460/480 V rated value 	0.75 hp
— at 460/480 V rated value — at 575/600 V rated value	0.75 hp 1 hp
Short-circuit protection	1 TIP
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
conditional short-circuit current (Iq)	ag.i.o.io
• at 400 V according to IEC 60947-4-1 rated value	153 000 A
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	snap-on fastening on 35 mm standard rail
height	265 mm
width	90 mm
depth	130 mm
required spacing	
 for grounded parts 	
— forwards	10 mm
— backwards	0 mm
— upwards	30 mm
— at the side	9 mm
— downwards	10 mm
• for live parts	
— forwards	10 mm
— backwards	0 mm
— upwards	30 mm
— downwards	10 mm
— at the side	9 mm
Connections/ Terminals	
type of electrical connection for main current circuit	screw-type terminals
type of connectable conductor cross-sections • for main contacts stranded	1 10 mm ² 2v (2.5 6 mm ²)
at AWG cables for main contacts	1 10 mm², 2x (2.5 6 mm²) 2x (16 12), 2x (14 8)
connectable conductor cross-section for main contacts	1 6 mm ²
finely stranded with core end processing	5
Safety related data	
B10 value with high demand rate according to SN 31920	1 000 000
proportion of dangerous failures with high demand rate according to SN 31920	73 %
protection class IP on the front according to IEC 60529	IP20

touch protection on the front according to IEC 60529

finger-safe, for vertical contact from the front

Certificates/ approvals

General Product Approval

For use in hazardous locations Declaration of Conformity

other

Dangerous Good

Confirmation







Confirmation

Transport Information

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2220-1BB23-0BB4

Cax online generator

 $\underline{\text{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RA2220-1BB23-0BB4}$

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2220-1BB23-0BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2220-1BB23-0BB4&lang=en


Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2220-1BB23-0BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2220-1BB23-0BB4&objecttype=14&gridview=view1





last modified: 12/15/2020 🖸