## **SIEMENS**

Data sheet 3RW5077-6TB15



SIRIUS soft starter 200-600 V 570 A, 110-250 V AC Screw terminals Thermistor input

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW50
manufacturer's article number	
<ul> <li>of standard HMI module usable</li> </ul>	<u>3RW5980-0HS01</u>
<ul> <li>of high feature HMI module usable</li> </ul>	3RW5980-0HF00
<ul> <li>of communication module PROFINET standard usable</li> </ul>	3RW5980-0CS00
<ul> <li>of communication module PROFIBUS usable</li> </ul>	3RW5980-0CP00
<ul> <li>of communication module Modbus TCP usable</li> </ul>	3RW5980-0CT00
<ul> <li>of communication module Modbus RTU usable</li> </ul>	3RW5980-0CR00
<ul> <li>of communication module Ethernet/IP</li> </ul>	3RW5980-0CE00
<ul> <li>of circuit breaker usable at 400 V</li> </ul>	3VA2580-6HN32-0AA0; Type of assignment 1, Iq = 65 kA
<ul> <li>of circuit breaker usable at 500 V</li> </ul>	3VA2580-6HN32-0AA0; Type of assignment 1, Iq = 65 kA
<ul> <li>of the gG fuse usable up to 690 V</li> </ul>	2x3NA3365-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of full range R fuse link for semiconductor protection usable up to 690 V</li> </ul>	3NE1 437-2; Type of coordination 2, Iq = 65 kA
<ul> <li>of back-up R fuse link for semiconductor protection usable up to 690 V</li> </ul>	3NE3 340-8; Type of coordination 2, Iq = 65 kA
<ul> <li>of line contactor usable up to 480 V</li> </ul>	3TF68
<ul> <li>of line contactor usable up to 690 V</li> </ul>	3TF68
General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
ramp-down time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
accuracy class according to IEC 61557-12	5 %
certificate of suitability	
CE marking	Yes
<ul> <li>UL approval</li> </ul>	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
<ul> <li>is supported HMI-Standard</li> </ul>	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	2
trip class	CLASS 10A / 10E (preset) / 20E; acc. to IEC 60947-4-2

buffering time in the event of power failure	
• for main current circuit	100 ms
for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC-53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	09/23/2019
product function	
<ul><li>ramp-up (soft starting)</li></ul>	Yes
<ul><li>ramp-down (soft stop)</li></ul>	Yes
Soft Torque	Yes
<ul> <li>adjustable current limitation</li> </ul>	Yes
<ul><li>pump ramp down</li></ul>	Yes
<ul> <li>intrinsic device protection</li> </ul>	Yes
motor overload protection	Yes; Full motor protection (thermistor motor protection and electronic motor overload protection)
<ul> <li>evaluation of thermistor motor protection</li> </ul>	Yes; Type A PTC or Klixon / Thermoclick
• auto-RESET	Yes
manual RESET	Yes
<ul> <li>remote reset</li> </ul>	Yes; By turning off the control supply voltage
<ul> <li>communication function</li> </ul>	Yes
<ul> <li>operating measured value display</li> </ul>	Yes; Only in conjunction with special accessories
<ul><li>error logbook</li></ul>	Yes; Only in conjunction with special accessories
<ul> <li>via software parameterizable</li> </ul>	No
<ul> <li>via software configurable</li> </ul>	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
<ul><li>voltage ramp</li></ul>	Yes
• torque control	No
analog output	No
Power Electronics	
operational current	
<ul> <li>at 40 °C rated value</li> </ul>	570 A
<ul> <li>at 50 °C rated value</li> </ul>	504 A
at 60 °C rated value	460 A
operating voltage	
rated value	200 600 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
operating power for 3-phase motors	
• at 230 V at 40 °C rated value	160 kW
<ul> <li>at 400 V at 40 °C rated value</li> </ul>	315 kW
• at 500 V at 40 °C rated value	355 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
<ul> <li>at rotary coding switch on switch position 1</li> </ul>	240 A
<ul> <li>at rotary coding switch on switch position 2</li> </ul>	262 A
<ul> <li>at rotary coding switch on switch position 3</li> </ul>	284 A

<ul> <li>at rotary coding switch on switch position 4</li> </ul>	306 A
<ul> <li>at rotary coding switch on switch position 5</li> </ul>	328 A
<ul> <li>at rotary coding switch on switch position 6</li> </ul>	350 A
at rotary coding switch on switch position 7	372 A
at rotary coding switch on switch position 8	394 A
at rotary coding switch on switch position 9	416 A
, ,	
<ul> <li>at rotary coding switch on switch position 10</li> </ul>	438 A
<ul> <li>at rotary coding switch on switch position 11</li> </ul>	460 A
<ul> <li>at rotary coding switch on switch position 12</li> </ul>	482 A
<ul> <li>at rotary coding switch on switch position 13</li> </ul>	504 A
<ul> <li>at rotary coding switch on switch position 14</li> </ul>	526 A
<ul> <li>at rotary coding switch on switch position 15</li> </ul>	548 A
<ul> <li>at rotary coding switch on switch position 16</li> </ul>	570 A
• minimum	240 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	
• at 40 °C after startup	73 W
at 50 °C after startup	57 W
at 60 °C after startup	47 W
power loss [W] at AC at current limitation 350 %	
• at 40 °C during startup	7 019 W
at 50 °C during startup     at 50 °C during startup	5 801 W
	5 048 W
at 60 °C during startup	
type of the motor protection	Electronic, tripping in the event of thermal overload of the motor
Control circuit/ Control	
type of voltage of the control supply voltage	AC
control supply voltage at AC	
● at 50 Hz	110 250 V
● at 60 Hz	110 250 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-15 %
relative positive tolerance of the control supply voltage at AC at 50 Hz	10 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-15 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	10 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply current in standby mode rated value	30 mA
holding current in bypass operation rated value	105 mA
locked-rotor current at close of bypass contact maximum	2.2 A
inrush current peak at application of control supply voltage maximum	12.2 A
duration of inrush current peak at application of control supply voltage	2.2 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature
	circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	0
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
action to act and a factor foliation	

• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting
factoring mathed	surface +/- 22.5° tiltable to the front and back
fastening method	screw fixing
height	230 mm
width	160 mm 282 mm
depth	202
required spacing with side-by-side mounting  • forwards	10 mm
backwards	0 mm
upwards	100 mm
downwards	75 mm
at the side	5 mm
weight without packaging	7.3 kg
Connections/ Terminals	7.5 kg
type of electrical connection  • for main current circuit	busbar connection
for control circuit	
width of connection bar maximum	screw-type terminals  35 mm; with connection cover 3RT1966-4EA1 maximum length 45 mm
	33 min, with connection cover 3KT 1900-4EAT maximum length 45 mm
<ul> <li>wire length for thermistor connection</li> <li>with conductor cross-section = 0.5 mm² maximum</li> </ul>	50 m
	150 m
<ul> <li>with conductor cross-section = 1.5 mm² maximum</li> <li>with conductor cross-section = 2.5 mm² maximum</li> </ul>	250 m
with conductor cross-section = 2.5 mm² maximum  type of connectable conductor cross-sections	200 111
for main contacts for box terminal using the front clamping point solid	95 300 mm²
<ul> <li>for main contacts for box terminal using the front clamping point finely stranded with core end processing</li> </ul>	70 240 mm²
<ul> <li>for main contacts for box terminal using the front clamping point finely stranded without core end processing</li> </ul>	70 240 mm²
<ul> <li>for main contacts for box terminal using the front clamping point stranded</li> </ul>	95 300 mm²
<ul> <li>at AWG cables for main contacts for box terminal using the front clamping point</li> </ul>	3/0 600 kcmil
<ul> <li>for main contacts for box terminal using the back clamping point solid</li> </ul>	120 240 mm²
<ul> <li>at AWG cables for main contacts for box terminal using the back clamping point</li> </ul>	250 500 kcmil
for main contacts for box terminal using both clamping points solid	min. 2x 70 mm², max. 2x 240 mm²
<ul> <li>for main contacts for box terminal using both clamping points finely stranded with core end processing</li> </ul>	min. 2x 50 mm², max. 2x 185 mm²
<ul> <li>for main contacts for box terminal using both clamping points finely stranded without core end processing</li> </ul>	min. 2x 50 mm², max. 2x 185 mm²
<ul> <li>for main contacts for box terminal using both clamping points stranded</li> </ul>	min. 2x 70 mm², max. 2x 240 mm²
<ul> <li>for main contacts for box terminal using the back clamping point finely stranded with core end processing</li> </ul>	120 185 mm²
<ul> <li>for main contacts for box terminal using the back clamping point finely stranded without core end processing</li> </ul>	120 185 mm²
<ul> <li>for main contacts for box terminal using the back clamping point stranded</li> </ul>	120 240 mm²
type of connectable conductor cross-sections	
<ul> <li>at AWG cables for main current circuit solid</li> </ul>	2/0 500 kcmil
<ul> <li>for DIN cable lug for main contacts stranded</li> </ul>	50 240 mm²
for DIN cable lug for main contacts finely stranded	70 240 mm²
type of connectable conductor cross-sections	
for control circuit solid	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)

for control circuit finely stranded with core end	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
processing	
at AWG cables for control circuit solid	1x (20 12), 2x (20 14)
wire length	
<ul> <li>between soft starter and motor maximum</li> </ul>	800 m
at the digital inputs at AC maximum	1 000 m
tightening torque	
<ul> <li>for main contacts with screw-type terminals</li> </ul>	14 24 N·m
for auxiliary and control contacts with screw-type terminals	0.8 1.2 N·m
tightening torque [lbf·in]	
<ul> <li>for main contacts with screw-type terminals</li> </ul>	124 210 lbf·in
<ul> <li>for auxiliary and control contacts with screw-type terminals</li> </ul>	7 10.3 lbf·in
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; derating as of 1000 m, see Manual
ambient temperature	
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
<ul> <li>during storage and transport</li> </ul>	-40 +80 °C
environmental category	
<ul> <li>during operation according to IEC 60721</li> </ul>	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
<ul> <li>during storage according to IEC 60721</li> </ul>	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of the fuse	
<ul> <li>usable for Standard Faults up to 575/600 V according to UL</li> </ul>	Type: Class L, max. 1600 A; Iq = 30 kA
<ul> <li>usable for High Faults up to 575/600 V according to UL</li> </ul>	Type: Class L, max. 1200 A; Iq = 100 kA
operating power [hp] for 3-phase motors	
<ul> <li>at 200/208 V at 50 °C rated value</li> </ul>	150 hp
<ul> <li>at 220/230 V at 50 °C rated value</li> </ul>	200 hp
<ul> <li>at 460/480 V at 50 °C rated value</li> </ul>	400 hp
• at 575/600 V at 50 °C rated value	500 hp
Safety related data	
protection class IP on the front according to IEC 60529	IP00; IP20 with cover
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with cover
ATEX	
certificate of suitability	
• ATEX	Yes
• IECEx	
	Yes
hardware fault tolerance according to IEC 61508 relating to ATEX	Yes 0
<u> </u>	
relating to ATEX PFDavg with low demand rate according to IEC 61508	0

3 y

Certificates/ approvals

## **General Product Approval**

For use in hazardous locations



Confirmation









For use in hazardous locations

**Declaration of** Conformity

**Test Certificates** 

Marine / Shipping





Type Test Certificates/Test Report







other

Confirmation

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5077-6TB15

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5077-6TB15

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5077-6TB15

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RW5077-6TB15&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5077-6TB15/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5077-6TB15&objecttype=14&gridview=view1

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified:

4/11/2022

