# SlimStack Board-to-Board Connectors, 0.635mm Pitch Series **molex**



SlimStack Board-to-Board Connectors 0.635mm Pitch Series offers a wide variety of circuit sizes and various stack heights for space savings and design flexibility in a diverse range of applications.

0.635mm Pitch Series has circuit sizes from 20 to 240. In addition, stack heights for this series is from 6.00mm to 16.00mm with same footprint. Molex Micro Solution design provides solutions for any market requirement.



## **Features and Advantages**

#### **Long Effective Mating Length**

Improves contact wipe and electrical reliability



**Lineup Combination** Receptacle 52885 55091 53625 53647 53649 53627 Series No. Circuits 20 to 240 20 to 200 20 to 240 20 to 160 30 to 140 20 to 200 Mated Height (mm) 6.00 to 10.00 6.00 7.00 8.00 9.00 10.00 Receptacle Plug 52901 55091 53625 53647 53649 53627 Series No. 20 to 200 Circuits 20 to 200 20 to 200 20 to 200 20 to 160 30 to 140 Mated Height (mm) 12.00 to 16.00 14.00 15.00 16.00 12.00 13.00

## **Applications**

Automotive	Medical		
Car Radar	Patient Monitors		
Car Infotainment	Ultrasound Monitors		
Datacom	Home Appliance		
<b>Datacom</b> Servers	Home Appliance Digital Electronics		

Industrial **Automation Machines** 



Car Infotainment





**Automation Machine** Servers

# SlimStack Board-to-Board Connectors, 0.635mm Pitch Series **molex**



# **Specifications**

#### REFERENCE INFORMATION

Packaging: Embossed Tape with Cover on Reel

Designed In: Millimeters

RoHS: Yes

Halogen Free: Low-Halogen (52885/52901/55091 series only)

#### **ELECTRICAL**

Voltage (max.): 100V

Current (max.): 0.5A per circuit

Contact Resistance (max.): 40 to 70 milliohms

(varied by each part)

Dielectric Withstanding Voltage: 250V AC Insulation Resistance (min.):1000 Megohms

#### **MECHANICAL**

Durability (max.): 50 cycles

#### **PHYSICAL**

Housing:

Receptacle: LCP, UL-94V-0, White Plug: LCP, UL-94V-0, Brown or Black

Contact: Copper Alloy

Fitting Nail: Copper Alloy

Plating:

Contact Area - Gold Solder Tail Area - Tin

Underplating - Nickel


Operating Temperature: -55 to +105°C

N: Circuit Size

#### **Dimensions**


\* Refer to drawing for detail dimension

## Receptacle





## Plug







# **Ordering Information**

Order No.				O'menths
Receptacle	Plug	Mated Height (mm)	Mated Width (mm)	Circuits
52885-**74	<u>55091-**74</u>	6.00	6.40	20 to 200
	<u>53625-**74</u>	7.00		20 to 240
	<u>53647-**74</u>	8.00		20 to 160
	<u>53649-**74</u>	9.00		30 to 140
	<u>53627-**74</u>	10.00		20 to 200
52901-**74	<u>55091-**74</u>	12.00		20 to 200
	<u>53625-**74</u>	13.00		20 to 200
	<u>53647-**74</u>	14.00		20 to 160
	<u>53649-**74</u>	15.00		30 to 140
	53627-**74	16.00		20 to 200

<sup>\*\*:</sup> circuit size

### www.molex.com/link/slimstack.html