

preliminary


Schottky [	Diode
------------	-------

$V_{\text{RRM}}$	=	45 V
I <sub>FAV</sub>	<i>=</i> 2x	10 A
V	=	0.61 V

High Performance Schottky Diode Low Loss and Soft Recovery Common Cathode


Part number

DSA20C45PB



Backside: cathode

20200127b



#### Features / Advantages:

- Very low Vf
- Extremely low switching losses
- Low Irm values
- Improved thermal behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching

### **Applications:**

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

#### Package: TO-220

- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0

#### **Disclaimer Notice**

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

IXYS reserves the right to change limits, conditions and dimensions.



preliminary

Schottky				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V <sub>RSM</sub>	max. non-repetitive reverse block	ng voltage	$T_{VJ} = 25^{\circ}C$			45	V
V <sub>RRM</sub>	max. repetitive reverse blocking v	oltage	$T_{vJ} = 25^{\circ}C$			45	V
I <sub>R</sub>	reverse current, drain current	$V_{R} = 45 V$	$T_{VJ} = 25^{\circ}C$			200	μA
		$V_{R} = 45 V$	$T_{vJ} = 125^{\circ}C$			2	mA
V <sub>F</sub>	forward voltage drop	$I_{F} = 10 \text{ A}$	$T_{vJ} = 25^{\circ}C$			0.72	V
		$I_{F} = 20 \text{ A}$				0.87	V
		$I_{F} = 10 \text{ A}$	T <sub>vJ</sub> = 125°C			0.61	V
		$I_{F} = 20 \text{ A}$				0.75	V
I FAV	average forward current	T <sub>c</sub> = 160°C	T <sub>vJ</sub> = 175°C			10	Α
		rectangular d = 0.5					
V <sub>F0</sub>	threshold voltage $T_{vJ} = 175^{\circ}C$					0.43	V
r <sub>F</sub>	slope resistance { for power loss calculation only					12.7	mΩ
<b>R</b> <sub>thJC</sub>	thermal resistance junction to case					2.4	K/W
R <sub>thCH</sub>	thermal resistance case to heatsir	nk			0.5		K/W
P <sub>tot</sub>	total power dissipation		$T_c = 25^{\circ}C$			65	W
	max. forward surge current	t = 10 ms; (50 Hz), sine; $V_{R} = 0 V$	$T_{vJ} = 45^{\circ}C$			260	A
C	junction capacitance	$V_{R} = 5V$ f = 1 MHz	$T_{VJ} = 25^{\circ}C$		326		pF


IXYS reserves the right to change limits, conditions and dimensions.


20200127b



preliminary

Package TO-220			Ratings			
Symbol	Definition	Conditions	min.	typ.	max.	Unit
	RMS current	per terminal <sup>1)</sup>			35	Α
T <sub>vj</sub>	virtual junction temperature		-55		175	°C
T <sub>op</sub>	operation temperature		-55		150	°C
T <sub>stg</sub>	storage temperature		-55		150	°C
Weight				2		g
M <sub>D</sub>	mounting torque		0.4		0.6	Nm
F <sub>c</sub>	mounting force with clip		20		60	Ν





### Part description

- D = Diode
- S = Schottky Diode A = low VF
- 20 = Current Rating [A]
- C = Common Cathode
- 45 = Reverse Voltage [V]
- PB = TO-220AB (3)


	Ordering	ering Ordering Number Marking on Product		Delivery Mode	Quantity	Code No.	
[	Standard	DSA20C45PB	DSA20C45PB	Tube	50	503675	


Equiva	alent Circuits for	Simulation	* on die level	$T_{VJ} = 175^{\circ}C$
	)[R]-	Schottky		
V <sub>0 max</sub>	threshold voltage	0.43		V
$\mathbf{R}_{0 \text{ max}}$	slope resistance *	9.6		mΩ

20200127b



preliminary





IXYS reserves the right to change limits, conditions and dimensions.

20200127b