



# HCH65R180


650V N-Channel Super Junction Power MOSFET

## ● Features:

- 20.0A, 650V,  $R_{DS(on)(Typ)} = 180m\Omega @ V_{GS}=10V$
- Low Gate Charge
- Low  $C_{rss}$
- 100% Avalanche Tested
- Fast Switching
- Improved dv/dt Capability

## ● Application:

- High Frequency Switching Mode Power Supply
- Active Power Factor Correction



## Absolute Maximum Ratings( $T_c=25^\circ C$ unless otherwise noted)

Symbol	Parameter	Value	Unit
$V_{DSS}$	Drain-Source Voltage	650	V
$I_D$	Drain Current - Continuous( $T_c=25^\circ C$ )	20.0*	A
	- Continuous( $T_c=100^\circ C$ )	12.6*	A
$I_{DM}$	Drain Current -Pulsed (Note1)	80*	A
$V_{GSS}$	Gate-Source Voltage	$\pm 30$	V
$E_{AS}$	Single Pulsed Avalanche Energy ( Limit Reference Value ) (Note2)	550	mJ
$I_{AR}$	Avalanche Current (Note1)	10.0	A
$E_{AR}$	Repetitive Avalanche Energy (Note1)	7.5	mJ
$dv/dt$	Peak Diode Recovery $dv/dt$ (Note3)	8.5	V/ns
$P_D$	Power Dissipation( $T_c = 25^\circ C$ ) -Derate above $25^\circ C$	185	W
		1.48	W/ $^\circ C$
$T_j$	Operating Junction Temperature	150	$^\circ C$
$T_{stg}$	Storage Temperature Range	-55 to+150	$^\circ C$

\* Drain Current Limited by Maximum Junction Temperature.

## Thermal Characteristics

Symbol	Parameter	Max	Unit
$R_{\theta JC}$	Thermal Resistance,Junction to Case	0.68	$^\circ C / W$
$R_{\theta JA}$	Thermal Resistance,Junction to Ambient	62.5	$^\circ C / W$

	<b>HCH65R180</b>
	650V N-Channel Super Junction Power MOSFET

### Electrical Characteristics(Tc=25°C unless otherwise noted)

Symbol	Parameter	Test Conditons	Min	Typ	Max	Unit
<b>Off Characteristics</b>						
$BV_{DSS}$	Drain-source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	650	--	--	V
$\Delta BV_{DSS} / \Delta T_J$	Breakdown Voltage Temperature Coefficient	$I_D=250\mu A$ (Referenced to 25°C)	--	0.62	--	V/°C
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=650V, V_{GS}=0V$	--	--	1	$\mu A$
		$V_{DS}=520V, T_c=125^{\circ}C$	--	--	10	$\mu A$
$I_{GSSF}$	Gate-Body Leakage Current,Forward	$V_{GS}=+30V, V_{DS}=0V$	--	--	100	nA
$I_{GSSR}$	Gate-Body Leakage Current,Reverse	$V_{GS}=-30V, V_{DS}=0V$	--	--	-100	nA
<b>On Characteristics</b>						
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	2.0	--	4.0	V
$R_{DS(on)}$	Static Drain-Source On-Resistance	$V_{GS}=10V, I_D=10A$	--	180	210	$m\Omega$
$g_{FS}$	Forward Transconductance	$V_{DS}=20V, I_D=10A$ (Note4)	--	13.5	--	S
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS}=100V, V_{GS}=0V, f=1.0MHz$	--	1170	--	pF
$C_{oss}$	Output Capacitance		--	67	--	pF
$C_{rss}$	Reverse Transfer Capacitance		--	4.0	--	pF
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 325V, I_D = 20A, R_G = 25\Omega$ (Note4,5)	--	20	--	ns
$t_r$	Turn-On Rise Time		--	59	--	ns
$t_{d(off)}$	Turn-Off Delay Time		--	105	--	ns
$t_f$	Turn-Off Fall Time		--	41	--	ns
$Q_g$	Total Gate Charge	$V_{DS} = 520V, I_D = 20A, V_{GS} = 10V$ (Note4,5)	--	39	--	nC
$Q_{gs}$	Gate-Source Charge		--	9.5	--	nC
$Q_{gd}$	Gate-Drain Charge		--	19	--	nC
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
$I_s$	Maximum Continuous Drain-Source Diode Forward Current	--	--	20	--	A
$I_{SM}$	Maximum Pulsed Drain-Source Diode Forward Current	--	--	80	--	A
$V_{SD}$	Drain-Source Diode Forward Voltage	$V_{GS} = 0V, I_s = 20.0A$	--	--	1.4	V
$t_{rr}$	Reverse Recovery Time	$V_{GS} = 0V, I_s = 20.0A, dI_F/dt = 100A/\mu s$ (Note4)	--	425	--	ns
$Q_{rr}$	Reverse Recovery Charge		--	6.2	--	$\mu C$

Notes:


- 1、Repetitive Rating:Pulse Width Limited by Maximum Junction Temperature.
- 2、 $L = 10mH, I_{AS} = 10.0A, V_{DD} = 100V, R_G = 25\Omega$ , Starting  $T_J = 25^{\circ}C$ .
- 3、 $I_{SD} \leq 20.0A$ ,  $dI/dt \leq 200A/\mu s$ ,  $V_{DD} \leq BV_{DSS}$ , Starting  $T_J = 25^{\circ}C$ .
- 4、Pulse Test : Pulse Width  $\leq 300\mu s$ , Duty Cycle  $\leq 2\%$ .
- 5、Essentially Independent of Operating Temperature.




HCH65R180

650V N-Channel Super Junction Power MOSFET


### On-Region Characteristics




### Transfer Characteristics




### On-Resistance Variation vs. Drain Current and Gate Voltage




### Body Diode Forward Voltage Variation vs. Source Current and Temperature



### Capacitance Characteristics



### Gate Charge Characteristics







HCH65R180

650V N-Channel Super Junction Power MOSFET


### Breakdown Voltage Variation vs. Temperature




### On-Resistance Variation vs. Temperature



### Maximum Safe Operating Area



### Maximum Drain Current Vs. Case Temperature






HCH65R180

650V N-Channel Super Junction Power MOSFET

### TO-262 MECHANICAL DATA

UNIT: mm

SYMBOL	min	nom	max	SYMBOL	min	nom	max
A	4.32	4.52	4.72	D1		7.40REF	
A1	2.44	2.64	2.84	E	9.88	10.13	10.38
b	0.70	0.80	0.90	E1	7.02	8.02	9.02
b1	0.28	0.38	0.48	e		2.54REF	
b2	0.90	1.00	1.10	L	12.60	13.10	13.60
b3	1.18	1.28	1.38	L1	1.30	1.50	1.70
c	0.30	0.38	0.46	L2	2.90	3.20	3.50
c1	1.17	1.27	1.37	H	1.08	1.28	1.48
D	8.70	9.05	9.40	θ1	2°	-	7°





**HCH65R180**

650V N-Channel Super Junction Power MOSFET

注意事项：

- 1、在电路设计时请不要超过器件的最大额定值，否则会影响整机的可靠性。
- 2、MOSFET产品为静电敏感型器件，使用时应注意采取防静电保护措施，如佩戴防静电手环、设备接地等。
- 3、如需安装散热片，请注意控制扭力大小及散热片的平整度。
- 4、该规格书由华科公司制作，并可能不定期更改，恕不另行通知。
- 5、如有疑问，请及时联系我司销售代表。

版本履历表：

序号	版本号	修改时间	修改记录
1	V1.0	2022-12-20	首次发行