


10.7 ±0.3 5.80 5.1 ±0.3

.XX ±0.13 .XXX ±0.10



NOTES:

MATERIAL:

HOUSING: BLACK THERMOPLASTIC POLYESTER, UL94V-0 STEEL, TIN PLATED SHELL: CONTACT: COPPER ALLOY, GOLD FLASH PLATED

OPERATING TEMPERATURE: -55°C ~ 125°C

CURRENT RATING: 5A PER CONTACT CONTACT RESISTANCE: $25m\Omega$ MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC rms

			SW REFERENCE NO.: 628M ASSEMBLY				
628 5	SERIES D-SUB (CONNECTOR	DRAWN: C.B		DATE: AU	G. 01/20	018
			CHECKED:		DATE:		
	EDAC INC TORONTO, ONTARIO CANADA O QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1		SHEET 1	OF	1
			DRAWING NUMBER: 628-M25-221-BT5			ISSUE	
YOUR CONNECTION TO			PART NUMBER:	628-M25-	221-BT5		1



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

SW REFERENCE NU.: 628M ASSEMBLY							
DRAWN: C.B		DATE: AUG. 01/2018					
CHECKED:		DATE:					
SCALE: 1:1		SHEET 1 OF	1				
DRAWING NUMBER: 628-M25-		221-BT5	ISSUE				
PART NUMBER:	628-M25-221-BT5		1				