



# **RF Adapters Technical Data Sheet**

# **PE906**

## Configuration

- SMA Male Connector 1
- SMA Female Connector 2

### Features

- Max VSWR of 1.23:1 up to 12.4 GHz
- SMA Interface compliant with MIL-STD-348A

### Applications

General Purpose Test

- 50 Ohms
- Right Angle Body Geometry
- Gold Plated Contact 50µ in min Gold Contact Plating

### Description

Pasternack's PE9068 SMA male to SMA female right angle adapter is part of our full line of RF components available for same-day shipping. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our SMA to SMA adapter has a male to female gender configuration. PE9068 SMA male to SMA female adapter operates to 12.4 GHz. The Pasternack RF adapter provides excellent VSWR of 1.23:1 maximum. This low profile right angle SMA adapter allows for easier connections in tight spaces.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/ disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

## **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR		1.13:1	1.23:1	
Insertion Loss		0.19	0.3	dB
Operating Voltage (AC)			500	Vrms
Inner Conductor DC Resistance			3	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms

## **Mechanical Specifications**

Size	
Length	0.65 in [16.51 mm]
Width	0.591 in [15.01 mm]
Height	0.315 in [8 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Right Angle Adapter PE9068

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# **RF Adapters Technical Data Sheet**

## **PE9068**

Weight	0.017 lbs [7.71 g]		
Description	Connector 1	Connector 2	
Туре	SMA Male	SMA Female	
Polarity	Standard	Standard	
Interface Specification	MIL-STD-348A	MIL-STD-348A	
Mating Cycles	500 500		
Hex Size	8 mm		
Mating Torque	3 to 5 in-lbs [0.34 to 0.57 Nm]		
Coupling Proof Torque, Min	5 in-lbs [0.57 Nm]		

#### **Material Specifications**

Connector		nector 1	Conne	ector 2
Description	Material	Plating	Material	Plating
Туре	SMA Male		SMA Female	
Contact	Brass	Gold	Beryllium Copper	Gold
		50 µin. minimum		50µ in. minimum
Insulation	PTFE		PTFE	
Outer Conductor			Brass	Nickel
				100µ in. minimum
Body	Brass	Nickel		
		100µ in. minimum		
Gasket	Silicone			
Coupling Nut	Brass	Nickel		
		100µ in. minimum		

#### **Environmental Specifications**

Temperature Operating Range

-65 to +165 deg C

Vibration Salt Spray MIL-STD-202, Method 204, Condition D MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Right Angle Adapter PE9068

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451


Sales@Pasternack.com • Techsupport@Pasternack.com





# **RF Adapters Technical Data Sheet**

**PE9068** 



Typical Performance Data

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Right Angle Adapter PE9068

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# **RF Adapters Technical Data Sheet**

## **PE9068**

SMA Male to SMA Female Right Angle Adapter from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to SMA Female Right Angle Adapter PE9068

URL: https://www.pasternack.com/sma-male-sma-female-right-angle-adapter-pe9068-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

## PE9068 CAD Drawing SMA Male to SMA Female Right Angle Adapter

