ignion™

Your innovation. Accelerated.

# COMPACT REACH Xtend<sup>TM</sup> (NN01-102)

DATASHEET

## COMPACT REACH Xtend<sup>™</sup> (NN01-102) <sup>-</sup> Bluetooth®, Zigbee®, 802.11 b/g/n WLAN (2.4 – 2.5 GHz)

Ignion specializes in enabling effective mobile communications. Using Ignion technology, we design and manufacture optimized antennas to make your wireless devices more competitive. Our mission is to help our clients develop innovative products and accelerate their time to market through our expertise in antenna design, testing and manufacturing.

The Compact Reach Xtend<sup>™</sup> chip antenna for Bluetooth® and 802.11 b /g WLAN is a rectangular 3D-shaped tiny antenna suitable for headset, compact flash (CF), secure digital (SD) and other small PCB devices operating at 2.4 GHz where high performance and low-cost are mandatory. The Compact Reach Xtend<sup>™</sup> antenna is built on glass epoxy substrate. Its broad bandwidth ensures high quality signal reception and transmission across wireless devices and different plastic housing designs.

Taking advantage of the space-filling properties, this small mono-pole antenna is ideal for use within indoor (highly scattered) environments. The Compact Reach Xtend<sup>™</sup> chip antenna speeds your time to market by allowing you to easily integrate it within your industrial design (SMD mounting).

### **Product Benefits**


- Small form factor
  Allows integration into space limited areas easily and efficiently with minimum clearance area.
- Broad bandwidth
  Ensures robust performance when
  considering different plastic housing
  and close body proximity.
- Omnidirectional pattern
  Optimizes device usage due to a uniform radiation pattern.
- Multi-mode support Works for Bluetooth, and Wi-Fi 802.11 b/g/n standards.

7.0 mm x 3.0 mm x 2.0 mm (image larger than real size)



PAT US 7,148,850, US 7,202,822

## VSWR and Total Efficiency (%) vs. Frequency (GHz)



| Technical Features     | 2.4 – 2.5 GHz            |
|------------------------|--------------------------|
| Average Efficiency     | 72.2 %                   |
| Peak Gain              | 1.7 dBi                  |
| VSWR                   | < 2:1                    |
| Radiation Pattern      | Omnidirectional          |
| Polarization           | Linear                   |
| Weight (approx.)       | 0.1 g                    |
| Temperature            | -40 to +125 °C           |
| Impedance              | 50 Ω                     |
| Dimensions (L x W x H) | 7.0 mm x 3.0 mm x 2.0 mm |

Measures from the evaluation board (47.0 mm x 23.0 mm x 1.0 mm)

See pictures of the evaluation boards and graphs of the specs in the User Manual.

For additional information, please visit <u>www.ignion.io</u> or contact <u>info@ignion.io</u>.

If you need assistance to design your matching network, please contact <u>support@ignion.io</u>, or try our free-of-charge<sup>1</sup> **NN Wireless Fast-Track** design service, you will get your chip antenna design including a custom matching network for your device in 24h<sup>1</sup>. Other related to NN's range of R&D services is available at: <u>https://www.ignion.io/rdservices/</u>

<sup>&</sup>lt;sup>1</sup> See terms and conditions for a free NN Wireless Fast-Track service in 24h at: <u>https://www.ignion.io/fast-track-project/</u>

## ignion<sup>™</sup>

## Your innovation. Accelerated.

## Contact: support@ignion.io +34 935 660 710

#### Barcelona

Av. Alcalde Barnils, 64-68 Modul C, 3a pl. Sant Cugat del Vallés 08174 Barcelona Spain

### Shanghai

Shanghai Bund Centre 18/F Bund Centre, 222 Yan'an Road East, Huangpu District Shanghai, 200002 China

#### **New Dehli**

New Delhi, Red Fort Capital Parsvnath Towers Bhai Veer Singh Marg, Gole Market, New Delhi, 110001 India

#### Tampa

8875 Hidden River Parkway Suite 300 Tampa, FL 33637 USA