

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

## **Technical Data Sheet**

N ATTENUATOR 10 DB 2 GHZ 80W



SERIES PAGE 2/2 ISSUE 13-04-16B PART NUMBER **R417710138** ATTENUATOR ELECTRICAL CHARACTERISTICS Frequency (GHz) DC - 1 1 - 2 V.S.W.R (≤) 1.10 1.25 Deviation(±dB) 1 1 **Operating Frequency Range** DC - 2 GHz Impedance 50 Ω Nominal Attenuation 10 dB Peak power at 25°C (1µs, 1%) 5000 W Average power at 25°C W (Free Air Cooled) 80 W (Conduction Cooled) For conduction cooling, a plate 1000 cm2 x 3 mm(156 sq.in\*1/8) min. is required MECHANICAL CHARACTERISTICS Connectors Ν **Male Female** MIL-C 39012 484,8300 Weight g ENVIRONMENTAL CHARACTERISTICS -55 /+125 °C Operating temperature range -55 /+125 °C Storage temperature range Power derating Versus temperature 100 90 80 70 60 50 40 30 20 10 -55 -15 125 25 Temperature (°C) SPECIFICATION **OTHER CHARACTERISTICS** 

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.