XMLP250MD21F

Electronic pressure sensors, Pressure sensors XM, transmitter 250mbar, 4...20 mA, G1/4 A male, FPM, M12





Main

Range of Product	OsiSense XM
Product or Component Type	Electronic pressure sensors
Pressure sensor type	Pressure transmitter
Pressure sensor name	XMLP
Electrical circuit type	Control circuit
Pressure Rating	250 mbar
Local display	Without
Controlled fluid	Fresh water 32257 °F (0125 °C)) Air 5257 °F (-15125 °C)) Gas 5257 °F (-15125 °C)) Hydraulic oil 5257 °F (-15125 °C))
Fluid connection type	G 1/4A (male) DIN 3852-E
Electrical connection	1 male connector M12 4 pins
[Us] rated supply voltage	1224 V DC SELV 733 V)
Current Consumption	< 23 mA
Type of output signal	Analogue
Analogue output function	420 mA, 2-wire
Quantity per Set	Set of 1
Type of Packing	Individual

Complementary

Pressure setting range	0.003.63 psi (00.25 bar)
Maximum permissible accidental pressure	43.51 psi (3 bar)
Destruction pressure	72.52 psi (5 bar)
Materials in contact with fluid	Fluorocarbon FPM Stainless steel AISI 316L Ceramic
Operating position	Any position
Protection Type	Reverse polarity Load short-circuit
Electromagnetic compatibility	Susceptibility to electromagnetic fields EN/IEC 61000-4-3 10 V/m 801000 MHz Radiated RF fields EN/IEC 61000-4-6 10 V 0.1580 MHz Electrostatic discharge immunity test EN/IEC 61000-4-2 8 kV air, 4 kV contact 1.2/50 µs shock waves immunity test EN/IEC 61000-4-5 1 kV 42 Ohm Immunity to magnetic fields EN/IEC 61000-4-8 100 A/m 50 Hz Electrical fast transient/burst immunity test EN/IEC 61000-4-4 4 kV
[Uimp] rated impulse withstand voltage	0.5 kV
Response time on output	<= 2 ms 92 % of full scale
Measurement accuracy	+/- 2 % of the measuring range
Drift of the sensitivity	+/- 0.02 % of measuring range/°K
Drift of the zero point	+/- 0.05 % of measuring range/°K
Long term stability	+/- 0.2 % of the measuring range
Mechanical durability	10000000 cycles
Net Weight	0.17 lb(US) (0.075 kg)
Diameter	1.02 in (26 mm)
Length	1.27 in (32.3 mm)

Environment

EN/IEC 61326-2-3
NSF ANSI 61
CULus
CE
RCM
EAC
-22185 °F (-3085 °C)
-58212 °F (-50100 °C)
20 gn 102000 Hz) EN/IEC 60068-2-6
100 gn 11 ms EN/IEC 60068-2-27
IP65 conforming to EN/IEC 60529
IP67 conforming to EN/IEC 60529
IP69K conforming to DIN 40050

Ordering and shipping details

Category	22661 - XMLA,B,C,D PRESSURE SWITCHES
Discount Schedule	DS2
GTIN	3389119625029
Nbr. of units in pkg.	1
Package weight(Lbs)	2.82 oz (80 g)
Returnability	No
Country of origin	СН

Packing Units


r doming office	
Unit Type of Package 1	PCE
Package 1 Height	1.65 in (4.2 cm)
Package 1 width	1.85 in (4.7 cm)
Package 1 Length	3.43 in (8.7 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Weight	4.85 lb(US) (2.199 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

5 11 5 1 5 1 5 1 5 1 5 1 5 1 5 1 5 1 5	
Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EV EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	€Yes
Environmental Disclosure	Product Environmental Profile

XMLP250MD21F

Dimensions



(1) SW24 tightening torque ≤ 25 N.m / 221 lb-in


Product data sheet Connections and Schema

XMLP250MD21F

Connection and Schema

Wiring Diagram

2-Wire Technique (4-20 mA)



XMLP250MD21F

Performance Curves

Curves

