

1T8F_4.2U series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Unregulated



← Small footprint

← Miniature SMD 8Pin package

High efficiency up to 75%

4200VDC isolation

Temperature range: -40°C ~ +105°C

Industry standard pinout

Low coupling capacity

Internal SMD construction

Qualified for lead-free reflow solder process according to IPC/JEDEC J-STD-020D.1

Tape & reel package option



1 Watt

The 1T8F_4.2U series is specially designed for applications where a group of polar power supplies are isolated from the input power supply in a distributed power supply system on a circuit board.

These products apply to:

- Where the voltage of the input power supply is fixed (voltage variation ≤ ±10%)
- 2) Where isolation is necessary between input and output (isolation voltage ≤4200VDC)
- 3) Where the regulation of the output voltage and the output ripple noise are not demanding. Such as: digit circuit condition; normal low-frequency artificial circuit condition; relay drive circuit condition, etc.







Common specifications	
Short circuit protection:	(automatic recovery) 0.5sec, max.
Temperature rise at full load:	25°C TYP (Ta= 25°C)
Cooling:	Free air convection
Operation temperature range:	-40°C~+105°C (see derating curve)
Storage temperature range:	-55°C ~+125°C
Lead-free reflow solder process:	IPC/JEDEC J-STD-020D.1
Reflow temperature:	245°C MAX, 1.5mm from case for 10 sec
Storage humidity range:	< 95%
Safety standard:	IEC60950-1
Vibration:	MIL-STD-810F
MTBF (MIL-HDBK-217F@25°C):	>8 Mhours
Base material:	Epoxy Resin [UL94-V0]
Weight:	1.52g
Dimensions:	0.5"x0.44"x0.27"

Input specifications					
Item	Test condition	Min	Тур	Max	Units
Input filter	Capacitor				
Input voltage range				±10	%
Input surge voltage	3.3V models5V models			5 9	VDC VDC
Input reflected ripple current*			20		mA pk-pk

* Measured with a simulated source inductance of 12 μ H and a source capacitor Cin (47 μ F, ESR<1.0 Ω at100kHz).

Isolation specifications								
Item	Test condition	Min	Тур	Max	Units			
Isolation voltage	Qualification: 60 sec. Production: 3 sec.	4200			VDC			
Isolation resistance	Test at 500VDC	1000			ΜΩ			
Isolation capacitance			25		pF			

Model selection/example:

1T8F_0505S4.2U

1 = 1Watt; T8 = SMT8; F = Pinning; 5Vin; 5Vout; S = Single output; 4.2 = 4.2kVDC; U = Unregulated output

Output specifications								
Item	Test condition	Min	Тур	Max	Units			
Output voltage accuracy	See tolerance envelope curve							
Line regulation	For Vin change of 1%			±1.2	%			
Load regulation	10% to 100% load • 3.3VDC output • 5VDC output			±15 ±12	% %			
Temperature drift	100% full load			±0.03	%/°C			
Ripple & Noise*	20MHz Bandwidth			150	mVp- p			
Switching frequency	Full load, nominal input		50~80		KHz			

EMC s	EMC specifications								
EMI	CE	EN55032	CLASS B						
EMI	RE	EN55032	CLASS B						
EMS	ESD	IEC/EN61000-4-2	perf. Criteria A						
EMS	RS	IEC/EN61000-4-3	perf. Criteria A						
EMS	EFT	IEC/EN61000-4-4	perf. Criteria A						
EMS	Surge	IEC/EN61000-4-5	perf. Criteria A						
EMS	CS	IEC/EN61000-4-6	perf. Criteria A						
EMS	PFMF	IEC/EN61000-4-8	perf. Criteria A						

* Input components (C1,D1) are used to help meet surge test requirement for the module. C1 and D1 recommended nichicon UHE and Littelfuse SMDJ series.

Note:


- Operation under minimum load will not damage the converter; However, they may not meet all specification listed.
- 2. Max. Capacitive Load tested at input voltage range and full load.
- 3. All specifications measured at Ta = 25°C, humidity <75%, nominal input voltage and rated output load unless otherwise specified.
- 4. In this datasheet, all the test methods of indications are based on our corporate standards.
- Operation under no-load conditions will not damage these devices, however they may not meet all listed specifications.
- 6. The 1T8F series of converters are not internally fused so to meet the requirements of UL; an anti-surge input line fuse should always be used with ratings as defined as follows: Input Voltage, 3.3V: 1.0A / Input Voltage, 5.0V: 1.0A All fuses should be UL recognized and rated to at least the maximum allowable DC input voltage.
- 7. It is not recommended to use water-washing process on SMT units.


1T8F 4.2U series

1W - Single Output DC-DC Converter - Fixed Input - Isolated & Unregulated

Part Number	Input Voltage [V]	Input Current [mA, typ.]	Output Voltage [VDC]	Output Current [mA]	Capacitive load [μF, max.]	Efficiency [%, typ]
1T8F_0303S4.2U	3.3	421	3.3	303	220	72
1T8F_0305S4.2U	3.3	410	5	200	220	74
1T8F_0503S4.2U	5	278	3.3	303	220	72
1T8F_0505S4.2U	5	267	5	200	220	75

Typical characteristics






Test configurations


Input reflected ripple current test step

Input reflected ripple current is measured through a source inductor Lin (12 μ H) and a source capacitor Cin (47 μ H, ESR<1.0 Ω at 100kHz) at nominal input and full load.




EFT & SURGE filter

Input components (C1, D1) are used to help meet surge test requirements for the module.




	C1	D1
1T8F_0303S4.2U	330μF/50V	SMDJ9.0A
1T8F_0305S4.2U	330μF/50V	SMDJ9.0A
1T8F_0503S4.2U	330μF/50V	SMDJ9.0A
1T8F_0505S4.2U	330μF/50V	SMDJ9.0A

Output ripple & noise measurement test Use a $10\mu F$ electrolytic capacitor and $0.1\mu F$ ceramic capacitor. The scope measurement is 0-20MHz.




EMI filter


Input filter components (C1, L) are used to help meet conducted emissions requirement fpr the module. These components should be mounted as close as possible to the module; and all leads should be minimized to decrease radiated noise.





	C1	L
1T8F_0303S4.2U	1206,22μF/10V	6.8µH
1T8F_0305S4.2U	1206,22μF/10V	6.8µH
1T8F_0503S4.2U	1206,22μF/10V	6.8µH
1T8F_0505S4.2U	1206,22μF/10V	6.8µH

Tolerance envelope curve













Efficiency











Mechanical dimensions




PIN	Single
1	-Vin
2	+Vin
4	-Vout
5	+Vout
8	NC




Note: Unit: mm[inch]

General tolerances: ±0.25mm[±0.010inch]

Tube outline dimensions




dimensions in [mm]





Packing informations

Optional packing - Tape & Reel

- Specifications shall conform with current EIA-481 standard
- ■1 Reel contains 500 converters
- ■Use appendix <<-R>> on order code







dimensions in [mm]

NOTE:

- 1. Material: Black Polystyrene.
- 2. Camber not to exceed 1mm in 100mm.
- 3. 10 sprocket hole pitch cumulative tolerance ±0.2
- 4. A0 and B0 measured on a plane 0.3mm above the bottom of the pocket.
- 5. K0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
- Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.

	Carrier Length: 26M / 22" reel, Q'ty= 500 pcs/13"reel											
ITEM	ITEM W A0 B0 K0 P1 F E1 D0 P0 P2 T D1							D1				
DIM	24.0 +0.30 -0.30	11.5 ^{+0.10} _{-0.10}	13.0 ^{+0.10}	7.50 ^{+0.15} _{-0.15}	16.0 ^{+0.10} _{-0.10}	11.50 ^{+0.10} _{-0.10}	1.75 ^{+0.10} _{-0.10}	1.50 +0.10 -0.00	4.00 +0.10 -0.10	2.00 +0.10 -0.10	0.50 +0.05 +0.05	1.50 MIN