### SURFACE MOUNT LED WHITE, 0402 PACKAGE






- **Industry Standard 0402 Package**
- **RoHS Compliant**
- **Small Package and Footprint**
- **Diffused Lens**
- Wide Viewing Angle
- Ideal for Status Indication, Display, and Backlighting





Bivar Surface Mount 0402 package LED can be used in nearly any indication application. It's ultraminiature packaging makes it ideal for smaller handheld devices, small back panel displays, and any other size constraint applications. Low power consumption and excellent long life reliability makes it excellent for battery powered equipment and applications. The SM0402 LED is packaged in standard tape and reels for pick and place assemblers.


Part Number	Material Emitted Color		Chromaticity Coordinates	Lens Appearance	Luminous Intensity (mcd) TYP.	Viewing Angle	
SM0402UWC	InGaN	WHITE	X = .30, Y = .30	Diffused	600	130°	

#### **Outline Dimensions**









- Outline Drawings Notes:
  1. All dimensions are in inches [millimeters].
- 2. Standard tolerance: ±0.006" unless otherwise noted.







# SURFACE MOUNT LED WHITE, 0402 PACKAGE



#### **Absolute Maximum Ratings**

 $T_A = 25$ °C unless otherwise noted

Power Dissipation	100 mW		
Continuous Forward Current	25 mA		
Peak Forward Current <sup>1</sup>	100 mA		
Reverse Voltage	5 V		
Derating Linear From 25°C	0.4 mA/°C		
Electrostatic Discharge (HBM)	2000 V		
Operating Temperature Range	-30 ~ +80°C		
Storage Temperature Range	-40 ~ +85°C		
Lead Soldering Temperature <sup>2</sup>	260°C		

Notes: 1. ≤ 10% Duty Cycle, Pulse Width ≤ 0.1 msec.

2. Solder time less than 5 seconds at temperature extreme.

#### **Electrical / Optical Characteristics**


 $T_A = 25^{\circ}C \& I_F = 20 \text{ mA}$  unless otherwise noted

Part Number	Forward Voltage (V)			Recommend Forward Current (mA)		Reverse Current (µA)	I Dominant		Luminous Intensity Iv (mcd)			Viewing Angle 2 Θ ½ (deg)		
	MIN	TYP	MAX	MIN	TYP	MAX	MAX	MIN	TYP	MAX	MIN	TYP	MAX	TYP
SM0402UWC	/	3.1	4.0	/	20	/	10	n/a	n/a	n/a	450	600	/	130

### SURFACE MOUNT LED WHITE, 0402 PACKAGE



# **Typical Electrical / Optical Characteristics**T<sub>A</sub> = 25°C unless otherwise noted







Fig. 1 Forward Current vs. Forward Voltage

Fig. 2 Relative Luminous Intensity vs. Forward Current







Fig. 3 Forward Current vs. Temperature


Fig. 4 Directivity Radiation Diagram



### SURFACE MOUNT LED WHITE, 0402 PACKAGE




#### **Recommended Soldering Conditions**



#### **Tape and Reel Dimensions**

Note: 5000 pcs / Reel




#### **Outline Drawings Notes:**

- All dimensions are in inches [millimeters].
   Standard tolerance: ±0.010" unless otherwise noted.

# SURFACE MOUNT LED WHITE, 0402 PACKAGE






#### **Outline Drawings Notes:**

- All dimensions are in inches [millimeters].
- 2. Standard tolerance unless otherwise noted: X.XXX ± 0.010"
  X X + 0.1"

### Packaging and Labeling Plan

Note: 1 Reel / Bag



Bivar reserves the right to make changes at any time without notice