۳ D D T	m		0	₩ >	
Z					
			LAYOUT SHOWN AS EXA	MPLE	
Ке	ying Shown as example				
CHARACTERISTICS	Connector dimension				
-Standard : Based on MIL-DTL-38999 Series III	Dim Nominal ØS 35.7 Max				
-Shell Material : Aluminium	Z 31 Max		SOURIAU shall not be liable for any r		
-Shell Plating : Nickel -Insulator : Thermoplastic	VV THREAD M25x1-6g		due to a use of the Products whic the Specifications issued by either of the		
-Contacts : Copper Alloy			(professional recommendatio		
-Seals & Grommet : Silicon Elastomer		L	Country	Jurisdiction & Control List] 1
-Contact Plating : Gold over copper Alloy 0.8µm minimum			FR	Not Listed	-
-Durability : 500 Mating cycles]
-Delivered without Souriau contacts			PN: 8D517F7	SPINL	
-Temperature Range65°C to +200°C		A 14-10-2016	First Release		
-Salt Spray : 48 hours					
-Mass : 26.31 g ± 10%		ISS DATE Designed By:	Latest modification - by Date:	CUSTOMER DRAWING	MOD N°
		TITLE	Aluminiı	ım Plug 8D series	
BASIC SERIES: 8D 5 - 17 F 75	P N L	SCALE	General linear Tolerances:	NPRDS / PROJECT	
SHELL TYPE : Plug with RFI Shielding	Delivered W/O Contacts	NA	↓Ψ <u>±-</u>	859 This document is the pro	nerty of
CONTACT TYPE : Standard Crimp Contact	ORIENTATION : N	SOURIAU	WWW.SOURIAU.CC	SOURIAU	
SHELL SIZE : 17	CONTACT TYPE : PIN(500 Matings)			it must not be reproduced of the communicated without periods of t	
PLATING : F = Nickel	CONTACT LAYOUT : 17-75		SOURIAU [DRG N°	SHEET
I		A3	8D517F75		1/2
	E	D	C		1

-	Ŧ	Q	н т	т		0
4		Contact Layout 75				
	Ctc A B	2#8 Triax 17-75 X Y 0 4.75 0 -4.75				
ω						
						SOURIAU shall not be liable for an due to a use of the Products wh the Specifications issued by either of (professional recommendat
N					A 14-10-20	Countr FR PN: 8D517F
					ISS DATE Designed By: TITLE	Latest modification - by Date: Alumin
					SCALE NA SOURIA	General linear Tolerances: ± U WWW.SOURIAU.C SOURIAU
	Н	G	F	E	A3	8D517F7

