



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
H3		REVISED PER ECN-22-153872	16MAY2022	RK	MF



RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 23-10-87	STE TE Connectivity Ltd.																			
DIMENSIONS: INCHES		CHK T. CLARK 23-10-87																				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. CLARK 29-10-87	NAME																			
<table border="1"> <tr><td>0 PLC</td><td>±</td><td>-</td></tr> <tr><td>1 PLC</td><td>±</td><td>-</td></tr> <tr><td>2 PLC</td><td>±</td><td>-</td></tr> <tr><td>3 PLC</td><td>±</td><td>.005</td></tr> <tr><td>4 PLC</td><td>±</td><td>-</td></tr> <tr><td>ANGLES</td><td>±</td><td>-</td></tr> </table>		0 PLC	±	-	1 PLC	±	-	2 PLC	±	-	3 PLC	±	.005	4 PLC	±	-	ANGLES	±	-	PRODUCT SPEC	HEADER ASSY, MOD II, B/A, DR, .100X.100 C/L, RA, WITH .025 SQ POSTS	
0 PLC	±	-																				
1 PLC	±	-																				
2 PLC	±	-																				
3 PLC	±	.005																				
4 PLC	±	-																				
ANGLES	±	-																				
MATERIAL: HOUSING: FLAME RETARDENT THERMOPLASTIC, COLOR: BLACK POSTS: COPPER ALLOY		FINISH SEE TABLE	WEIGHT -	SIZE A2																		
CUSTOMER DRAWING			CAGE CODE 00779	DRAWING NO C=103326																		
SCALE 4:1			SHEET 1 OF 2	REV H3																		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

- 1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
- 4 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 5 .000015 GOLD IN THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 6 .000015 GOLD IN THE CONTACT AREA, .000100-.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 7 HIGH TEMPERATURE CONFIGURATION
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 9 OBSOLETE

REMARKS	PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER		
7	7	6	6	3.984	3.900	39	80	9-103326-0	5	3.984	3.900	39	80	9-103326-0
7	7	6	6	3.884	3.800	38	78	8-103326-9	5	3.884	3.800	38	78	8-103326-9
7	7	6	6	3.784	3.700	37	76	8-103326-8	5	3.784	3.700	37	76	8-103326-8
7	7	6	6	3.684	3.600	36	74	8-103326-7	5	3.684	3.600	36	74	8-103326-7
7	7	6	6	3.584	3.500	35	72	8-103326-6	5	3.584	3.500	35	72	8-103326-6
7	7	6	6	3.484	3.400	34	70	8-103326-5	5	3.484	3.400	34	70	8-103326-5
7	7	6	6	3.384	3.300	33	68	8-103326-4	5	3.384	3.300	33	68	8-103326-4
7	7	6	6	3.284	3.200	32	66	8-103326-3	5	3.284	3.200	32	66	8-103326-3
7	7	6	6	3.184	3.100	31	64	8-103326-2	5	3.184	3.100	31	64	8-103326-2
7	7	6	6	3.084	3.000	30	62	8-103326-1	5	3.084	3.000	30	62	8-103326-1
7	7	6	6	2.984	2.900	29	60	8-103326-0	5	2.984	2.900	29	60	8-103326-0
7	7	6	6	2.884	2.800	28	58	7-103326-9	5	2.884	2.800	28	58	7-103326-9
7	7	6	6	2.784	2.700	27	56	7-103326-8	5	2.784	2.700	27	56	7-103326-8
7	7	6	6	2.684	2.600	26	54	7-103326-7	5	2.684	2.600	26	54	7-103326-7
7	7	6	6	2.584	2.500	25	52	7-103326-6	5	2.584	2.500	25	52	7-103326-6
7	7	6	6	2.484	2.400	24	50	7-103326-5	5	2.484	2.400	24	50	7-103326-5
7	7	6	6	2.384	2.300	23	48	7-103326-4	5	2.384	2.300	23	48	7-103326-4
7	7	6	6	2.284	2.200	22	46	7-103326-3	5	2.284	2.200	22	46	7-103326-3
7	7	6	6	2.184	2.100	21	44	7-103326-2	5	2.184	2.100	21	44	7-103326-2
7	7	6	6	2.084	2.000	20	42	7-103326-1	5	2.084	2.000	20	42	7-103326-1
7	7	6	6	1.984	1.900	19	40	7-103326-0	5	1.984	1.900	19	40	7-103326-0
7	7	6	6	1.884	1.800	18	38	6-103326-9	5	1.884	1.800	18	38	6-103326-9
7	7	6	6	1.784	1.700	17	36	6-103326-8	5	1.784	1.700	17	36	6-103326-8
7	7	6	6	1.684	1.600	16	34	6-103326-7	5	1.684	1.600	16	34	6-103326-7
7	7	6	6	1.584	1.500	15	32	6-103326-6	5	1.584	1.500	15	32	6-103326-6
7	7	6	6	1.484	1.400	14	30	6-103326-5	5	1.484	1.400	14	30	6-103326-5
7	7	6	6	1.384	1.300	13	28	6-103326-4	5	1.384	1.300	13	28	6-103326-4
7	7	6	6	1.284	1.200	12	26	6-103326-3	5	1.284	1.200	12	26	6-103326-3
7	7	6	6	1.184	1.100	11	24	6-103326-2	5	1.184	1.100	11	24	6-103326-2
7	7	6	6	1.084	1.000	10	22	6-103326-1	5	1.084	1.000	10	22	6-103326-1
7	7	6	6	.984	.900	9	20	6-103326-0	5	.984	.900	9	20	6-103326-0
7	7	6	6	.884	.800	8	18	5-103326-9	5	.884	.800	8	18	5-103326-9
7	7	6	6	.784	.700	7	16	5-103326-8	5	.784	.700	7	16	5-103326-8
7	7	6	6	.684	.600	6	14	5-103326-7	5	.684	.600	6	14	5-103326-7
7	7	6	6	.584	.500	5	12	5-103326-6	5	.584	.500	5	12	5-103326-6
7	7	6	6	.484	.400	4	10	5-103326-5	5	.484	.400	4	10	5-103326-5
7	7	6	6	.384	.300	3	8	5-103326-4	5	.384	.300	3	8	5-103326-4
7	7	6	6	.284	.200	2	6	5-103326-3	5	.284	.200	2	6	5-103326-3
7	7	6	6	.184	.100	1	4	5-103326-2	5	.184	.100	1	4	5-103326-2
7	7	6	6	.084			2	5-103326-1	5	.084			2	5-103326-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H MOLL 23-10-87
 CHK T. CLARK 23-10-87
 APVD T. CLARK 29-10-87

STE TE Connectivity Ltd.

NAME: HEADER ASSY, MOD II, BREAKAWAY, DR, .100X.100 C/L, RA, WITH .025 SQ POSTS

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=103326 RESTRICTED TO: -

MATERIAL: - FINISH: SEE TABLE WEIGHT: - SCALE: 1:1 SHEET: 2 OF 2 REV: H3

CUSTOMER DRAWING