

## SOT-23 Plastic-Encapsulate Transistors


### Features

- Complementary to MMBT2907A
- Power dissipation of 300mW
- High stability and high reliability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C

### Mechanical Data

- Case: SOT-23  
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

### Function Diagram




### Collector-Base Voltage

VCBO 75V

### Collector Current

-0.6 Ampere

### SOT-23



### Maximum Ratings (Ta=25°C Unless otherwise specified)

| PARAMETER                   | SYMBOL           | UNIT  | VALUE     |
|-----------------------------|------------------|-------|-----------|
| Collector-Base Voltage      | $V_{CBO}$        | V     | 75        |
| Collector-Emitter Voltage   | $V_{CEO}$        |       | 40        |
| Emitter-Base Voltage        | $V_{EBO}$        |       | 6.0       |
| Collector Current           | $I_C$            | A     | 0.6       |
| Collector Power Dissipation | $P_C$            | mW    | 300       |
| Storage temperature         | $T_{stg}$        | °C    | -55 ~+150 |
| Junction temperature        | $T_j$            | °C    | -55 ~+150 |
| Typical Thermal Resistance  | $R_{\theta J-A}$ | °C /W | 417       |

### Electrical Characteristics (Ta=25°C Unless otherwise noted)

| PARAMETER                            | SYMBOL         | UNIT    | Condition   | Min | Max  |
|--------------------------------------|----------------|---------|---|-----|------|
| Collector-Base Breakdown Voltage     | $V_{CBO}$      | V       | $I_C=10\mu A, I_E=0$  | 75  | —    |
| Collector-Emitter Breakdown Voltage  | $V_{CEO}$      |         | $I_C=10mA, I_B=0$   | 40  | —    |
| Emitter-Base Breakdown Voltage       | $V_{EBO}$      |         | $I_E=10\mu A, I_C=0$  | 6.0 | —    |
| Collector-Base cut-off current       | $I_{CBO}$      | $\mu A$ | $V_{CB}=60V, I_E=0$   | —   | 0.01 |
| Collector cut-off current            | $I_{CEX}$      |         | $V_{CE}=30V, V_{EB(off)}=3.0V$                              | —   | 0.01 |
| Emitter-Base cut-off current         | $I_{EBO}$      |         | $V_{EB}=3.0V, I_C=0$  | —   | 0.1  |
| DC Current Gain                      | $h_{FE}$       | —       | $I_C=0.1mA, V_{CE}=10V$                                     | 40  | —    |
|                                      |                |         | $I_C=150mA, V_{CE}=10V$                                     | 100 | 300  |
|                                      |                |         | $I_C=500mA, V_{CE}=10V$                                     | 42  | —    |
| Collector-Emitter Saturation Voltage | $V_{CE(sat)1}$ | V       | $I_C=500mA, I_B=50mA$                                       | —   | 1.0  |
| Collector-Emitter Saturation Voltage | $V_{CE(sat)2}$ |         | $I_C=150mA, I_B=15mA$                                       | —   | 0.3  |
| Base-Emitter Saturation Voltage      | $V_{BE(sat)1}$ |         | $I_C=500mA, I_B=50mA$                                       | —   | 2.0  |
| Base-Emitter Saturation Voltage      | $V_{BE(sat)2}$ |         | $I_C=150mA, I_B=15mA$                                       | —   | 1.2  |
| Delay time                           | $t_d$          | ns      | $V_{CC}=30V, V_{BE(off)}=-0.5V$<br>$I_C=150mA, I_{B1}=15mA$ | —   | 10   |
| Rise time                            | $t_r$          |         |   | —   | 25   |
| Storage time                         | $t_s$          |         | $V_{CC}=30V, I_C=150mA$<br>$I_{B1}=I_{B2}=15mA$             | —   | 225  |
| Fall time                            | $t_f$          |         |   | —   | 60   |

## ● Classification Of $h_{FE}$

| RANK  | L       | H       |
|-------|---------|---------|
| Range | 100-200 | 200-300 |





## ● Small-signal Characteristics

| ITEM                 | SYMBOL | Condition                        | UNIT | Min | Max |
|----------------------|--------|----------------------------------|------|-----|-----|
| Transition frequency | $f_T$  | $I_C=20mA, V_{CE}=20V, f=100MHz$ | MHz  | 300 | —   |



## ● Ordering Information

| PACKAGE | PACKAGE CODE | UNIT WEIGHT(g) | REEL(pcs) | BOX(pcs) | CARTON(pcs) | DELIVERY MODE |
|---------|--------------|----------------|-----------|----------|-------------|---------------|
| SOT-23  | R1           | 0.008          | 3000      | 30000    | 120000      | 7"            |


## ● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



### ● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




### ● Package Outline Dimensions (SOT-23)



| Symbol   | Dimensions  |      |          |       |
|----------|-------------|------|----------|-------|
|          | Millimeters |      | Inches   |       |
|          | Min.        | Max. | Min.     | Max.  |
| A        | 0.90        | 1.15 | 0.035    | 0.045 |
| A1       | -           | 0.10 | -        | 0.004 |
| A2       | 0.90        | 1.05 | 0.035    | 0.041 |
| b        | 0.30        | 0.50 | 0.012    | 0.020 |
| c        | 0.10        | 0.20 | 0.004    | 0.008 |
| D        | 2.80        | 3.00 | 0.110    | 0.118 |
| E        | 1.20        | 1.40 | 0.047    | 0.055 |
| E1       | 2.25        | 2.55 | 0.089    | 0.100 |
| e        | 0.950TYP    |      | 0.037TYP |       |
| e1       | 1.80        | 2.00 | 0.071    | 0.079 |
| L        | 0.550REF    |      | 0.022REF |       |
| L1       | 0.30        | 0.50 | 0.012    | 0.020 |
| $\theta$ | -           | 8°   | -        | 8°    |

### ● Suggested Pad Layout



| Symbol | Dimensions  |      |        |       |
|--------|-------------|------|--------|-------|
|        | Millimeters |      | Inches |       |
|        | Min.        | Max. | Min.   | Max.  |
| J      | 0.75        | 0.85 | 0.030  | 0.033 |
| K      | 0.85        | 0.95 | 0.033  | 0.037 |
| M      | 1.95        | 2.05 | 0.077  | 0.081 |
| N      | 1.85        | 1.95 | 0.073  | 0.077 |