

SOT-23 Plastic-Encapsulate Transistors


Features

- Complementary to MMBT5401
- Power dissipation of 300mW
- High stability and high reliability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C


Mechanical Data

- Case: SOT-23
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

Function Diagram



Collector-Base Voltage
VCBO 180V
Collector Current
0.6 Ampere



Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Collector-Base Voltage	V_{CBO}	V	180
Collector-Emitter Voltage	V_{CEO}		160
Emitter-Base Voltage	V_{EBO}		6.0
Collector Current	I_C	A	0.6
Collector Power Dissipation	P_C	mW	300
Storage temperature	T_{stg}	°C	-55 ~+150
Junction temperature	T_j	°C	-55 ~+150
Typical Thermal Resistance	$R_{\theta J-A}$	°C /W	417

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	SYMBOL	UNIT	Condition	Min	Max
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	V	$I_C=100\mu A, I_E=0$	180	—
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$		$I_C=1.0mA, I_B=0$	160	—
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$		$I_E=10\mu A, I_C=0$	6.0	—
Collector-Base cut-off current	I_{CBO}	nA	$V_{CB}=120V, I_B=0$	—	50
Emitter-Base cut-off current	I_{EBO}		$V_{EB}=4.0V, I_C=0$	—	50
DC Current Gain	h_{FE}	—	$I_C=1.0mA, V_{CE}=5.0V$	80	—
			$I_C=10mA, V_{CE}=5.0V$	100	300
			$I_C=50mA, V_{CE}=5.0V$	30	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)1}$	V	$I_C=10mA, I_B=1.0mA$	—	0.15
Collector-Emitter Saturation Voltage	$V_{CE(sat)2}$		$I_C=50mA, I_B=5.0mA$	—	0.2
Base-Emitter Saturation Voltage	$V_{BE(sat)1}$		$I_C=10mA, I_B=1.0mA$	—	1.0
Base-Emitter Saturation Voltage	$V_{BE(sat)2}$		$I_C=50mA, I_B=5.0mA$	—	1.0





● Small-signal Characteristics

ITEM	SYMBOL	Condition	UNIT	Min	Max
Transition frequency	f_T	$I_C=10\text{mA}, V_{CE}=10\text{V}, f=100\text{MHz}$	MHz	100	300



● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-23	R1	0.008	3000	30000	120000	7"


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (SOT-23)



● Suggested Pad Layout

