

Features

- 1.2kV Schottky Rectifier
- Zero Reverse Recovery Current
- High-Frequency Operation
- Temperature-Independent Switching
- Extremely Fast Switching
- Positive Temperature Coefficient on V_F
- Increased Creepage/Clearance Distance

Benefits

- Replace Bipolar with Unipolar Rectifiers
- Essentially No Switching Losses
- Higher Efficiency
- Reduction of Heat Sink Requirements
- Parallel Devices Without Thermal Runaway

Applications

- Switch Mode Power Supplies (SMPS)
- Boost diodes in PFC or DC/DC stages
- Free Wheeling Diodes in Inverter stages
- AC/DC converters



Part Number	Package	Marking
HC4D15120H	TO247-2L	HC4D15120H

Maximum Ratings (Tc=25°C unless otherwise specified)

Symbol	Parameter	Value	Unit	Test Conditions	Note
V _{RRM}	Repetitive Peak Reverse Voltage	1200	V		
V _{RSM}	Surge Peak Reverse Voltage	1300	V		
V _R	DC Peak Reverse Voltage	1200	v		
I _F	Continuous Forward Current	39 19 15	А	T _c =25°C T _c =135°C T _c =147°C	Fig. 3
I _{frm}	Repetitive Peak Forward Surge Current	64 42	А	$T_c=25$ °C, $t_p=10$ ms, Half Sine Pulse $T_c=110$ °C, $t_p=10$ ms, Half Sine Pulse	
I _{fsm}	Non-Repetitive Forward Surge Current	87 72	А	$T_c=25$ °C, $t_p=10$ ms, Half Sine Pulse $T_c=110$ °C, $t_p=10$ ms, Half Sine Pulse	
I _{F,Max}	Non-Repetitive Peak Forward Current	900 750	А	$T_c=25$ °C, $t_p=10 \ \mu$ s, Pulse $T_c=110$ °C, $t_p=10 \ \mu$ s, Pulse	Fig. 8
P _{tot}	Power Dissipation	174.5 75.5	w	T _c =25°C T _c =110°C	
dV/dt	Diode dV/dt ruggedness	200	V/ns	s V _R =0-960V	
∫i²dt	i²t value	38 26	A²s	$T_c=25$ °C, t_P=10 ms $T_c=110$ °C, t_P=10 ms	
T _J , T _{stg}	Operating Junction and Storage Temperature	-55 to +175	°C		
	TO-247 Mounting Torque	1 8.8	Nm Ibf-in	M3 Screw 6-32 Screw	



T0247-2L Package





Electrical Characteristics

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
V _F	Forward Voltage	1.5 2.3	1.8 3	V	$I_{F} = 15 \text{ A} T_{J} = 25^{\circ}\text{C}$ $I_{F} = 15 \text{ A} T_{J} = 175^{\circ}\text{C}$	Fig. 1
I _R	Reverse Current	35 120	200 300	μA	V _R = 1200 V T _J =25°C V _R = 1200 V T _J =175°C	Fig. 2
Q _c	Total Capacitive Charge	77.5		nC	V _R = 800 V, I _F = 15A d <i>i</i> /d <i>t</i> = 200 A/µs T _J = 25°C	Fig. 5
С	Total Capacitance	1200 70 50		pF	$V_{R} = 0 V, T_{J} = 25^{\circ}C, f = 1 MHz$ $V_{R} = 400 V, T_{J} = 25^{\circ}C, f = 1 MHz$ $V_{R} = 800 V, T_{J} = 25^{\circ}C, f = 1 MHz$	Fig. 6
E _c	Capacitance Stored Energy	22		μJ	V _R = 800 V	Fig. 7

Note: This is a majority carrier diode, so there is no reverse recovery charge.

Thermal Characteristics

Symbol	Parameter	Тур.	Unit	Note
$R_{_{ ext{ heta}JC}}$	JC Thermal Resistance from Junction to Case		°C/W	Fig. 9

Typical Performance






Figure 1. Forward Characteristics


Figure 2. Reverse Characteristics



Typical Performance










Figure 5. Recovery Charge vs. Reverse Voltage

Figure 6. Capacitance vs. Reverse Voltage



Typical Performance




Figure 7. Typical Capacitance Stored Energy







Figure 8. Non-repetitive peak forward surge current versus pulse duration (sinusoidal waveform)







Diode Model



$$Vf_T = V_T + If * R_T$$

$$V_T = 0.97 + (T_j * -2.12*10^{-3})$$


 $R_T = 0.031 + (T_j * 3.92*10^{-4})$

Note: T_j = Diode Junction Temperature In Degrees Celsius, valid from 25°C to 175°C




Package Dimensions

Package: TO247-2L All dimensions in mm.



SYM	MILLIMETERS		INCHES			
SIM	MIN	MAX	MIN	MAX		
A	4.83	5.21	.190	.205		
Al	2.29	2.54	.090	.100		
A2	1.91	2.16	.075	.085		
b'	1.07	1.28	.042	.050		
b	1.07	1.33	.042	.052		
b1	1.91	2.41	.075	.095		
b2	1.91	2.16	.075	.085		
c'	0.55	0.65	.022	.026		
с	0.55	0.68	.022	.027		
D	20.80	21.10	.819	.831		
D1	16.25	17.35	.640	.683		
D2	2.86	3.16	.112	.124		
Е	15.75	16.13	.620	.635		
E1	13.10	14.15	.516	.557		
E2	3.68	5.10	.145	.201		
E3	1.00	1.90	.039	.075		
E4	12.38	13.43	.487	.529		
e	10.88	BSC	.428 BSC			
L	19.81	20.32	.780	.800		
Ll	4.10	4.40	.161	.173		
ØP	3.51	3.65	.138	.144		
Q	5.49	6.00	.216	.236		
S	6.04	6.30	.238	.248		
Т	17.5° REF.					
W		3.5° REF.				
Х	4° REF.					
Y	0	0.50	0	0.020		

Recommended Solder Pad Layout



all units are in inches



Attention

Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

• HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

• Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ HUA XUAN YANG ELECTRONICS CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could

give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

In the event that any or all HUA XUAN YANG ELECTRONICS products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

• No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production.
HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.