

Vertical Cavity Surface Emitting Laser

OPV300, OPV310, OPV310Y, OPV314,
OPV314Y



Features:

- 850nm VCSEL Technology
- Data rates up to 2.5 Gbps
- High thermal stability
- Low drive current / high output density
- Narrow and concentric beam angle
- Recommended for multimode fiber applications
- Burned in for communication level reliability



Description:

The **OPV300 / OPV310 / OPV314** series are high performance 850nm Vertical Cavity Surface Emitting Laser (VCSEL). The **OPV300** and **OPV310** are designed to be utilized for sensing applications as well as air transmission of data. The **OPV314** is designed for high speed communication links. The **OPV310 / OPV314** combine all the performance advantages of a VCSEL with the addition of a power monitor diode for precise control of optical power. The **OPV310 and OPV314** have a back monitor photodiode used for optical power management or optical reception for data communication applications.

The **OPV300 / OPV310** have a flat lens while the **OPV314** has a microbead lens. Refer to mechanical drawings for details.

The high performance 850nm VCSEL is designed for applications where low current is required with high on-axis optical power. These product's combine features including high speed, high output optical power and concentric beam making it an ideal transmitter for integration into all types of data communications equipment as well as for reflective and transmissive switches.

Applications:

- Fiber Channel
- Gigabit Ethernet
- ATM
- VSR
- Intra-System links
- Optical backplane interconnects
- Reflective sensing
- Interruptive sensing
- Long distance spot illumination

NOTICE

This component is sensitive to electrostatic discharge (ESD). To prevent ESD-induced damage and/or degradation to equipment, take normal ESD precautions when handling this product.



RoHS



Additional laser safety information can be found on the Optek website. See application bulletin #221. Classification is not marked on the device due to space limitations. See package outline for centerline of optical radiance. Operating devices beyond maximum rating may result in hazardous radiation exposure.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

Vertical Cavity Surface Emitting Laser

OPV300, OPV310, OPV310Y, OPV314,
OPV314Y



Electrical Specifications

Absolute Maximum Ratings ($T_A = 25^\circ\text{C}$ unless otherwise noted)

| | |
|--|-------------------|
| Operating Temperature Range | 0°C to +70°C |
| Storage Temperature Range | -40°C to +100°C |
| Maximum Forward Peak Current, continuous | 12 mA |
| Maximum Reverse Voltage | 5 V |
| Max. Continuous Optical Power at 70° C | 1.1 mW |
| Lead Soldering Temperature | 260°C for 10 sec. |
| Maximum Forward Current, pulsed (1 μs P.W., 10% D.C.) | 48 mA |

Notes:

- (1) Threshold Current is based on the two line intersection method specified in Telcordia GR-468-Core. Line 1 from 4 mA to 6 mA. Line 2 from 0 mA to 0.5 mA.
- (2) Series Resistance is the slope of the Voltage-Current line from 5 to 8 mA.
- (3) Slope efficiency is the slope of the best fit LI line from 5 mA to 8 mA using no larger than .25 mA test interval points.
- (4) Using data points taken for slope efficiency above, $\Delta L/\Delta I$ shall be calculated for each adjacent pair of points.



Additional laser safety information can be found on the Optek website. See application bulletin #221. Classification is not marked on the device due to space limitations. See package outline for centerline of optical radiance. Operating devices beyond maximum rating may result in hazardous radiation exposure.

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

Vertical Cavity Surface Emitting Laser

OPV300, OPV310, OPV310Y, OPV314,
OPV314Y



Electrical Specifications

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted)

| SYMBOL | PARAMETER | MIN | TYP | MAX | UNITS | TEST CONDITIONS |
|---|--|--------------|-----------|------|----------------------|--|
| P_{OT} | Total Power Out OPV300 / OPV310 OPV314 | 1.50 1.40 | | | mW | $I_F = 7\text{ mA}$ |
| I_{TH} | Threshold Current | 0.80 | | 3.00 | mA | Note 1 |
| V_F | Forward Voltage | 1.60 | | 2.20 | V | $I_F = 7\text{ mA}$ |
| I_R | Reverse Current | | | 100 | nA | $V_R = 5\text{ V}$ |
| R_S | Series Resistance | 20 | | 55 | ohms | Note 2 |
| η | Slope Efficiency | 0.28 | | 0.60 | mW/mA | Note 3 |
| | Linearity | 0.00 | | | | Note 4 |
| λ | Wavelength | 840 | 850 | 860 | nm | |
| $\Delta\lambda$ | Optical Bandwidth | | | 0.85 | nm | |
| θ | Beam Divergence (OPV300 / OPV310 only) | | 24 | | Degree | $I_F = 7\text{ mA}$, FWHM |
| t_r/t_f | Rise and Fall Time | | 100 | | ps | 20% to 80% |
| N_{RI} | Relative Intensity Noise | | -123 | | dB/Hz | |
| ΔI_{TH} | Temp Variance of Threshold Current | | ± 1.0 | | mA | $0^\circ - 70^\circ\text{C}$, Note 1 |
| $\Delta\lambda/\Delta T$ | Temp Coefficient of Wavelength | | 0.06 | | nm/ $^\circ\text{C}$ | $0^\circ - 70^\circ\text{C}$, $I_F = 7\text{ mA}$ |
| $\Delta V_F/\Delta T$ | Temperature Coefficient for VF | | -2.5 | | mV/ $^\circ\text{C}$ | $0^\circ - 70^\circ\text{C}$, $I_F = 7\text{ mA}$ |
| $\Delta\eta/\Delta T$ | Temperature Coefficient for Efficiency | | -0.5 | | %/ $^\circ\text{C}$ | $0^\circ - 70^\circ\text{C}$, Note 3 |
| Photodiode Electrical Characteristics (OPV310/OPV314 series) | | | | | | |
| I_{RPD} | Reverse Current, photodiode | | | 30 | nA | $V_R = 5\text{ V}$ |
| I_{M1} | Monitor Current OPV310 OPV314 | 30 40 | | | μA | $I_F = 7\text{ mA}$, $V_R = 5\text{ V}$ |
| I_{M2} | Monitor Current OPV310 OPV314 | 40 45 | | | μA | $P_O = 2\text{ mW}$, $V_R = 5\text{ V}$ |

NOTES:

- Threshold Current is based on the two line intersection method specified in Telcordia GR-468-Core. Line 1 from 4 mA to 6 mA. Line 2 from 0 mA to 0.5 mA.
- Series Resistance is the slope of the Voltage-Current line from 5 to 8 mA.
- Slope efficiency, is the slope of the best fit LI line from 5 mA to 8 mA using no larger than .25 mA test interval points.
- Using data points taken for slope efficiency above, $\Delta L/\Delta I$ shall be calculated for each adjacent pair of points.
- ESD Class 1

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

Vertical Cavity Surface Emitting Laser

OPV300, OPV310, OPV310Y, OPV314,
OPV314Y



Performance



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com





Vertical Cavity Surface Emitting Laser

OPV300, OPV310, OPV310Y, OPV314, OPV314Y



Performance

OPV300 & OPV310



| OPV300 | |
|--------|---------------|
| Pin | Connection |
| 1 | VCSEL Anode |
| 2 | VCSEL Cathode |
| 3 | No Connection |

| OPV310 | |
|--------|------------------------|
| Pin | Connection |
| 1 | VCSEL Anode |
| 2 | VCSEL Cathode/PD Anode |
| 3 | PD Cathode |

| OPV310Y | |
|---------|------------------------|
| Pin | Connection |
| 1 | VCSEL Cathode |
| 2 | VCSEL Anode/PD Cathode |
| 3 | PD Anode |

General Note
 TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | OPTEK Technology
 2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com


Vertical Cavity Surface Emitting Laser

OPV300, OPV310, OPV310Y, OPV314, OPV314Y




OPV314


Invisible Light emits from this surface



Bottom View



| OPV314 | |
|--------|------------------------|
| Pin | Connection |
| 1 | VCSEL Anode |
| 2 | VCSEL Cathode/PD Anode |
| 3 | PD Cathode |



| OPV314Y | |
|---------|------------------------|
| Pin | Connection |
| 1 | VCSEL Cathode |
| 2 | VCSEL Anode/PD Cathode |
| 3 | PD Anode |

General Note
TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.