

FEATURES

- ※3-state setting
- ※Low profile for space saving

APPLICATION

- ※Remote control
- ※Home automation
- ※Telecommunication

SPECIFICATION

Contact Rating	25mA, 24V DC
Contact Resistance	100mΩ max.
Insulation Resistance	100MΩ min. 500V DC
Dielectric Strength	500V AC/1 minute
Operating Force	1,000gf max.
Travel	0.8mm
Operating Life	2,000 cycles
Operating Temp.	-20°C ~ +85°C
Storage Temp.	-40°C ~ +85°C

HOW TO ORDER






CIRCUIT




PACKAGE

- <Tube>
 TII(R)/TIM(R)-04: 41 pcs
 TII(R)/TIM(R)-05: 34 pcs
 TII(R)/TIM(R)-08: 22 pcs
 TII(R)/TIM(R)-09: 20 pcs
 TII(R)/TIM(R)-10: 18 pcs
- <Tape & Reel>
 TIM(R): 900 pcs

TII(R)




PART NO.	NO.OF POS.	DIM.A	DIM.B
TII(R)-04	4	11.32	7.62
TII(R)-05	5	13.86	10.16
TII(R)-08	8	21.48	17.78
TII(R)-09	9	24.02	20.32
TII(R)-10	10	26.56	22.86





P.C.B. LAYOUT

TIM(R)


DIP SWITCH



DATE CODE
 ex: MYY
 (1,2~9,X,Y,Z) L0,1,2~9



PART NO.	NO.OF POS.	DIM.A	DIM.B
TIM(R)-04	4	11.32	7.62
TIM(R)-05	5	13.86	10.16
TIM(R)-08	8	21.48	17.78
TIM(R)-09	9	24.02	20.32
TIM(R)-10	10	26.56	22.86



P.C.B. LAYOUT