



0.1MS4A 1.5UP series

0.1W - Single Output DC-DC Converter - Fixed Input - Isolated & Unregulated

DC-DC Converter

0.1 Watt

- ← Efficiency up to 62%
- 1500VDC isolation
- Operating temperature range: -40°C ~ +105°C
- Short circuit protection (SCP)
- Power density 0.36W/cm³
- + Industry standard pinout
- RoHS compliance
- MTBF >1,000,000 hours
- + UL 94V-0 package material

The 0.1MS4A_1.5UP series are miniature, isolated 0.1W DC-DC converters in a SIP package. They offer the ideal solution in many space critical applications for board level power distribution. The internal SMD construction makes it possible to offer a product with high performance at low cost. The series offers smaller size, improved efficiency.





Common specifications	
Short circuit protection:	continuous
Case temperature rise above ambient:	+35°C max. 0505 & 1205
Cooling:	Free air convection
Operation temperature range:	-40°C~+105°C
Storage temperature range:	-50°C ~+130°C
Lead temperature:	300°C MAX, 1.5mm from case for 10 sec
Storage humidity range:	< 95%
Case material:	Non-conductive plastic [UL94-V0]
MTBF (MIL-HDBK-217F @25°C):	>1,000,000 hours
Weight:	1.09g

Input specifications					
Item	Test condition	Min	Тур	Max	Units
Voltage range	• 3.3V input • 5V input • 12V input	2.9 4.5 11	3.3 5 12	3.6 5.5 13.3	V V V
input voltage Absolut max. rating 3.3V input 5V input 12V input		5.5 7 15	V V V		
Internal filter	Capacitor				
No load current				13mA	

Isolation specification	ons				
Item	Test condition	Min	Тур	Max	Units
Isolation voltage	Tested for 10sec.	1500			VDC
Isolation resistance	Test at 500VDC	1			GΩ

Output specification	S				
Item	Test condition	Min	Тур	Max	Units
Minimum load	10% of full load				
Voltage set point accuracy				±2	W
Line regulation	High to low Vin (±5%)			±1.2	%
Load regulation	10% to 100% load • 3.3V output & 0309 • 5V output • 9V output • 12V output • 15V output			15 15 10 10 9	% % % %
Output voltage accuracy	See tolerance envelope	graph			
Temperature drift	100% full load			±0.05	%/°C
Ripple & Noise*	20MHz Bandwidth		50	100	mVp-p
Switching frequency	Full load, nominal input		120		KHz

^{*} Measured with 1uF ceramic capacitor connect to the output pins.

Example:

0.1MS4A_0505S1.5UP

0.1 = 0.1 Watt; MS4 = Micro SIP4; A = Pinning; 05 = 5 Vin; 05 = 5Vout;

S = Single Output; 1.5 = 1.5kVDC Isolation; U = Unregulated;

P = Short circuit protection

Note:


- Operation under minimum load will not damage the converter; However, they
 may not meet all specification listed, and that will reduce the life of product.
- 2. All specifications measured at Ta = 25°C, humidity <75%, nominal input voltage and rated output load unless otherwise specified.
- 3. Only typical models listed, other models may be different, please contact our technical person for more details.
- In this datasheet, all the test methods of indications are based on corporate standards.

Typical characteristics


Part Number	Input Voltage [V]	Output Voltage [VDC]	Output Co	urrent [mA] max	Efficiency [%]
0.1MS4A_0303S1.5UP	3.3	3.3	3.03	30.3	58
0.1MS4A_0305S1.5UP	3.3	5	2	20	60
0.1MS4A_0309S1.5UP	3.3	9	1.11	11.1	60
0.1MS4A_0503S1.5UP	5	3.3	3.03	30.3	58
0.1MS4A_0505S1.5UP	5	5	2	20	59
0.1MS4A_0509S1.5UP	5	9	1.11	11.1	60
0.1MS4A_0512S1.5UP	5	12	0.83	8.3	61
0.1MS4A_0515S1.5UP	5	15	0.67	6.7	60
0.1MS4A_1205S1.5UP	12	5	2	20	62
0.1MS4A_1209S1.5UP	12	9	1.11	11.1	60
0.1MS4A_1212S1.5UP	12	12	0.83	8.3	59
0.1MS4A_1215S1.5UP	12	15	0.67	6.7	59


Typical characteristics

Temperature derating graph:




Tolerance envelope






Recommended footprint


Tube outline dimensions





Note: Tube length: 525mm ±2mm Tube quantity: 40Pcs

Mechanical dimensions



4 PIN SIP		
Pin	Function	
1	-Vin	
2	+Vin	
3	-Vout	
4	+Vout	

Note:

All dimensions are in mm $\pm 0.25 mm$ All pins on a 2.54mm pitch and within $\pm 0.25 mm$ of true position