



21.6 x 27.6 x 35.0 mm

#### **Features**

- Switching capacity up to 20A; small size and light weight
- Low coil power consumption; high contact load
- · Strong resistance to shock and vibration





### **Contact Data\***

Contact Arrangement	1A, 1B, 1C = SPST N.O., SPST N.C., SPDT
	2A, 2B, 2C = DPST N.O., DPST N.C., DPDT
Contact Rating	1 Pole: 20A@277VAC & 28VDC, General Purpose
	2 Pole: 12A@ 250VAC & 28VDC, General Purpose
	2 Pole: 10A @ 277VAC, General Purpose
	1/2hp @ 125VAC

Contact Resistance	< 50 milliohms initial
Contact Material	AgCdO
Max Switching Power	5540VA, 560W
Max Switching Voltage	300VAC
Max Switching Current	20A

### Coil Data DC Parameters\*

	Coil Voltage Coil Resistance VDC Ω +/- 10%		j -1 5 - j		Coil Power W	Operate Time ms	Release Time ms
Rated	Max		75% of rated voltage	voltage 10% of rated voltage			
12	15.6	160	9.0	1.2			
24	31.2	650	18.0	2.4			
36	46.8	1500	27.0	3.6	.9	25	25
48	62.4	2600	36.0	4.8	.9	25	25
110	143.0	11000	82.5	11.0			
220	286.0	53778	165.0	22.0			

### Coil Data AC Parameters\*

	Coil Voltage Coil Resistance VAC Ω +/- 10%		Pick Up Voltage VAC Release Voltage V (max) (min)		Coil Power VA	Operate Time ms	Release Time ms
Rated	Max		80% of rated voltage	30% of rated voltage			
12	15.6	46	9.6	3.6			
24	31.2	184	19.2	7.2			
36	46.8	370	28.8	10.8			
48	62.4	7335	38.4	14.4	1.2	25	25
110	143.0	3900	88.0	33.0			
220	286.0	14400	176.0	66.0			
240	312.0	19000	192.0	72.0			



### General Data\*

Electrical Life @ rated lo	oad	100K cycles, average				
Mechanical Life		20M cycles (1 & 2 pole), typical; 10M cycles (3 &4 pole), average				
Insulation Resistance		100M Ω min. @ 500VDC initial				
Dielectric Strength	Coil to Contact	1500V rms min. @ sea level initial				
	Contact to Contact	1500V rms min. @ sea level initial				
Shock Resistance		100m/s <sup>2</sup> for 11 ms				
Vibration Resistance		1.27mm double amplitude 10~40Hz				
Terminal (Copper Alloy)	Strength	10N				
Operating Temperature		-40°C to +85°C				
Storage Temperature		-40°C to +155°C				
Solderability		260°C for 5 s				
Weight		2C: 40g; 3C: 50g; 4C: 60g				

# **Ordering Information**


1. Series	J151	2C	Т	12VDC	.9		
J151							
2. Contact Arran 1A, 1B, 1C 2A, 2B, 2C	gement						
3. Termination T = Solder lug F = Solder lug P = PCB Term	s / Plug-in with	Flange					
4. Coil Voltage 12VDC 24VDC 36VDC 48VDC 110VDC 220VDC	12VAC 24VAC 36VAC 48VAC	110VAC 120VAC 220VAC 240VAC					
	use with DC coil o						
6. Option LED Blank = No inc D = With indic							
7. Gold Option Blank = Stand G = Gold over	lard contact r standard conta	icts					
	Option out push to test b to test button	outton					


<sup>\*</sup> Values can change due to the switching frequency, desired reliability levels, environmental conditions and in-rush load levels. It is recommended to test actual load conditions for the application. It is the user's responsibility to determine the performance suitability for their specific application. The use of any coil voltage less than the rated coil voltage may compromise the operation of the relay.




### **Dimensions**

#### Units = mm









[1.42]

1 & 2 Pole with Flange

2X 3.75 [.15]




1 & 2 Pole




Flange Mount Layouts



# **Termination Options**





## Schematics & PC Layouts

