


PART NO.		RFB-1133	
REV	DESCRIPTION	DWN	DATE
E	UPDATED DWG FORMAT	CZS	3/22/21
			APPROVED
			JDMc



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
 WORKING VOLTAGE: 500 VRMS @ SEA LEVEL
 FREQUENCY RANGE: 0-4 GHz
 INTERFACE PER MIL-STD-348A, SECTION 301.1

8	SHELL	2	BRASS	NICKEL
7	WASHER	2	BRASS	NICKEL
6	SPRING	2	SK-5	NICKEL
5	SPLIT LOCK WASHER	2	SK-5	NICKEL
4	GASKET	2	S.I. RUBBER	RED
3	DIELECTRIC	2	PTFE	NATURAL
2	PIN	1	BRASS	GOLD
1	BODY	1	BRASS	NICKEL
#	DESCRIPTION	QTY	MATERIAL	FINISH

CUSTOMER OUTLINE DRAWING ALL DIMENSIONS ARE REFERENCE ONLY UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES AND [MILLIMETERS]		DRAWN C. ZUNIGA CHECKED	03/22/21
DRW	C. JONES	8/27/91	

ROHS COMPLIANT

PROPRIETARY AND CONFIDENTIAL
 THIS DRAWING CONTAINS
 INFORMATION PROPRIETARY TO
 RF INDUSTRIES, ANY
 UNAUTHORIZED USE OF THIS
 DRAWING IS EXPRESSLY
 PROHIBITED WITHOUT WRITTEN
 PERMISSION FROM RF
 INDUSTRIES, ANY VIOLATION IS
 PUNISHABLE UNDER U.S.
 COPYRIGHT LAWS.

RF Industries
 DIVISION OF RF INDUSTRIES, LTD. (858) 549-6345 FAX

7610 MIRAMAR RD.
 SAN DIEGO, CA 92126
 (858) 549-6340

**BNC PLUG TO BNC PLUG
 ADAPTER \ UG491B/U**

CABLE GROUP | DWG # **RFB-1133** | REVISION **E**

FORMAT **A** | SCALE **NTS** | CONTROL # **000000** | SHEET **1 OF 1**