SIEMENS

Data sheet 3RW5244-2AC04



SIRIUS soft starter 200-480 V 250 A, 24 V AC/DC spring-type terminals Analog output

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
 of standard HMI module usable 	3RW5980-0HS00
 of high feature HMI module usable 	3RW5980-0HF00
 of communication module PROFINET standard usable 	3RW5980-0CS00
 of communication module PROFIBUS usable 	3RW5980-0CP00
 of communication module Modbus TCP usable 	3RW5980-0CT00
 of communication module Modbus RTU usable 	3RW5980-0CR00
 of communication module Ethernet/IP 	3RW5980-0CE00
 of circuit breaker usable at 400 V 	3VA2440-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V 	3VA2440-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2450-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V at inside-delta circuit 	3VA2450-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of the gG fuse usable up to 690 V 	2x3NA3354-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	2x3NA3354-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1331-0; Type of coordination 2, Iq = 65 kA
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE3336; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
UL approval	Yes
CSA approval	Yes
product component	
 HMI-High Feature 	No
 is supported HMI-Standard 	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	
for main current circuit	100 ms
for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	
ramp-up (soft starting)	Yes
ramp-down (soft stop)	Yes
Soft Torque	Yes
 adjustable current limitation 	Yes
pump ramp down	Yes
 intrinsic device protection 	Yes
 motor overload protection 	Yes; Electronic motor overload protection
 evaluation of thermistor motor protection 	No
• inside-delta circuit	Yes
• auto-RESET	Yes
manual RESET	Yes
 remote reset 	Yes; By turning off the control supply voltage
 communication function 	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
error logbook	Yes; Only in conjunction with special accessories
 via software parameterizable 	No
 via software configurable 	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
• firmware update	Yes
 removable terminal for control circuit 	Yes
• torque control	No
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)
Power Electronics	
operational current	
 at 40 °C rated value 	250 A
 at 50 °C rated value 	220 A
• at 60 °C rated value	200 A
operational current at inside-delta circuit	
at 40 °C rated value	433 A
• at 50 °C rated value	381 A
at 60 °C rated value	346 A
operating voltage	
• rated value	200 480 V
at inside-delta circuit rated value	200 480 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	

 at 230 V at 40 °C rated value 	75 kW
 at 230 V at inside-delta circuit at 40 °C rated value 	132 kW
 at 400 V at 40 °C rated value 	132 kW
at 400 V at inside-delta circuit at 40 °C rated value	250 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
 at rotary coding switch on switch position 1 	100 A
 at rotary coding switch on switch position 2 	110 A
 at rotary coding switch on switch position 3 	120 A
 at rotary coding switch on switch position 4 	130 A
 at rotary coding switch on switch position 5 	140 A
 at rotary coding switch on switch position 6 	150 A
 at rotary coding switch on switch position 7 	160 A
 at rotary coding switch on switch position 8 	170 A
 at rotary coding switch on switch position 9 	180 A
 at rotary coding switch on switch position 10 	190 A
 at rotary coding switch on switch position 11 	200 A
 at rotary coding switch on switch position 12 	210 A
 at rotary coding switch on switch position 13 	220 A
 at rotary coding switch on switch position 14 	230 A
 at rotary coding switch on switch position 15 	240 A
 at rotary coding switch on switch position 16 	250 A
• minimum	100 A
adjustable motor current	
 for inside-delta circuit at rotary coding switch on switch position 1 	173 A
 for inside-delta circuit at rotary coding switch on switch position 2 	191 A
 for inside-delta circuit at rotary coding switch on switch position 3 	208 A
 for inside-delta circuit at rotary coding switch on switch position 4 	225 A
 for inside-delta circuit at rotary coding switch on switch position 5 	242 A
 for inside-delta circuit at rotary coding switch on switch position 6 	260 A
 for inside-delta circuit at rotary coding switch on switch position 7 	277 A
 for inside-delta circuit at rotary coding switch on switch position 8 	294 A
 for inside-delta circuit at rotary coding switch on switch position 9 	312 A
 for inside-delta circuit at rotary coding switch on switch position 10 	329 A
 for inside-delta circuit at rotary coding switch on switch position 11 	346 A
 for inside-delta circuit at rotary coding switch on switch position 12 	364 A
 for inside-delta circuit at rotary coding switch on switch position 13 	381 A
 for inside-delta circuit at rotary coding switch on switch position 14 	398 A
 for inside-delta circuit at rotary coding switch on switch position 15 	416 A
 for inside-delta circuit at rotary coding switch on switch position 16 	433 A
at inside-delta circuit minimum	173 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	07 \\
• at 40 °C after startup	87 W
at 50 °C after startup	78 W

at 60 °C after startup	72 W
power loss [W] at AC at current limitation 350 %	
 at 40 °C during startup 	3 818 W
 at 50 °C during startup 	3 188 W
at 60 °C during startup	2 799 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
at 50 Hz rated value	24 V
at 60 Hz rated value	24 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
at DC rated value	24 V
relative negative tolerance of the control supply voltage at DC	-20 %
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	470 mA
locked-rotor current at close of bypass contact	7.6 A
maximum inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	1
switching capacity current of the relay outputs	
 at AC-15 at 250 V rated value 	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back
fastening method	screw fixing
height	393 mm
width	210 mm
depth	203 mm
required spacing with side-by-side mounting	
• forwards	10 mm
backwards	0 mm
• upwards	100 mm
• downwards	75 mm
at the side	5 mm

weight without packaging	9.9 kg
Connections/ Terminals	
type of electrical connection	
for main current circuit	busbar connection
for control circuit	spring-loaded terminals
width of connection bar maximum	45 mm
type of connectable conductor cross-sections	
for DIN cable lug for main contacts stranded	2x (50 240 mm²)
 for DIN cable lug for main contacts finely stranded 	2x (70 240 mm²)
type of connectable conductor cross-sections	
 for control circuit solid 	2x (0.25 1.5 mm²)
 for control circuit finely stranded with core end 	2x (0.25 1.5 mm²)
processing	
 at AWG cables for control circuit solid 	2x (24 16)
 at AWG cables for control circuit finely stranded with 	2x (24 16)
core end processing	
wire length	900 m
between soft starter and motor maximum	800 m
at the digital inputs at AC maximum	100 m
at the digital inputs at DC maximum	1 000 m
tightening torque	4.4 2.4 N m
for main contacts with screw-type terminals	14 24 N·m
 for auxiliary and control contacts with screw-type terminals 	0.8 1.2 N·m
tightening torque [lbf·in]	
for main contacts with screw-type terminals	124 210 lbf·in
for auxiliary and control contacts with screw-type	7 10.3 lbf·in
terminals	7 10.0 IDI III
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or
	above
during storage and transport	-40 +80 °C
environmental category	
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt
during storage apporting to IEC 60704	mist), 3S2 (sand must not get into the devices), 3M6
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
 during transport according to IEC 60721 	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
• EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of circuit breaker	
— usable for Standard Faults at 460/480 V	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; Iq = 18 kA
according to UL	
 usable for High Faults at 460/480 V according to UL 	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; Iq max = 65 kA
 usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3VA54, max. 600 A; Iq = 18 kA
 usable for High Faults at 460/480 V at insidedelta circuit according to UL 	Siemens type: 3VA54, max. 600 A; Iq max = 65 kA
 usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3VA53, max. 400 A or 3VA54, max. 600 A; Iq = 18 kA
 usable for Standard Faults at 575/600 V at inside-delta circuit according to UL 	Siemens type: 3VA54, max. 600 A; Iq = 18 kA

of the fuse

— usable for Standard Faults up to 575/600 V according to UL $\,$

— usable for High Faults up to 575/600 V according to UL

— usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL

— usable for High Faults at inside-delta circuit up to 575/600 V according to UL

Type: Class J / L, max. 800 A; Iq = 18 kA

Type: Class J / L, max. 800 A; Iq = 100 kA

Type: Class J / L, max. 800 A; Iq = 18 kA

Type: Class J / L, max. 800 A; Iq = 100 kA

operating power [hp] for 3-phase motors

at 200/208 V at 50 °C rated value
at 220/230 V at 50 °C rated value

at 460/480 V at 50 °C rated value

at 200/208 V at inside-delta circuit at 50 °C rated value

 at 220/230 V at inside-delta circuit at 50 °C rated value

 at 460/480 V at inside-delta circuit at 50 °C rated value 150 hp

60 hp

75 hp

150 hp

125 hp

300 hp

contact rating of auxiliary contacts according to UL

R300-B300

Safety related data

protection class IP on the front according to IEC 60529

touch protection on the front according to IEC 60529

electromagnetic compatibility

IP00; IP20 with cover

finger-safe, for vertical contact from the front with cover

in accordance with IEC 60947-4-2

Certificates/ approvals

General Product Approval

EMC





Confirmation







Declaration of Conformity

Test Certificates

Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5244-2AC04

Cax online generator

 $\underline{\text{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RW5244-2AC04}\\$

 $Service \& Support \ (Manuals, \ Certificates, \ Characteristics, \ FAQs, ...)$

https://support.industry.siemens.com/cs/ww/en/ps/3RW5244-2AC04

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5244-2AC04&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5244-2AC04/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5244-2AC04&objecttype=14&gridview=view1



last modified: 4/10/2022 🖸