## **SIEMENS**

Data sheet 3RW5246-2TC05



SIRIUS soft starter 200-600 V 370 A, 24 V AC/DC spring-type terminals Thermistor input

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
<ul> <li>of standard HMI module usable</li> </ul>	3RW5980-0HS00
<ul> <li>of high feature HMI module usable</li> </ul>	3RW5980-0HF00
<ul> <li>of communication module PROFINET standard usable</li> </ul>	3RW5980-0CS00
<ul> <li>of communication module PROFIBUS usable</li> </ul>	3RW5980-0CP00
<ul> <li>of communication module Modbus TCP usable</li> </ul>	3RW5980-0CT00
<ul> <li>of communication module Modbus RTU usable</li> </ul>	3RW5980-0CR00
<ul> <li>of communication module Ethernet/IP</li> </ul>	3RW5980-0CE00
<ul> <li>of circuit breaker usable at 400 V</li> </ul>	3VA2440-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 500 V</li> </ul>	3VA2440-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 400 V at inside-delta circuit</li> </ul>	3VA2580-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 500 V at inside-delta circuit</li> </ul>	3VA2580-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of the gG fuse usable up to 690 V</li> </ul>	2x3NA3365-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of the gG fuse usable at inside-delta circuit up to 500 V</li> </ul>	2x3NA3365-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of full range R fuse link for semiconductor protection usable up to 690 V</li> </ul>	3NE1334-2; Type of coordination 2, Iq = 65 kA
<ul> <li>of back-up R fuse link for semiconductor protection usable up to 690 V</li> </ul>	3NE3336; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
<ul> <li>UL approval</li> </ul>	Yes
CSA approval	Yes
product component	
<ul> <li>HMI-High Feature</li> </ul>	No
<ul> <li>is supported HMI-Standard</li> </ul>	Yes
<ul> <li>is supported HMI-High Feature</li> </ul>	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trin class	CLASS 10A (default) / 10E / 20E: 200 to IEC 60047 4.2
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	100 mg
for main current circuit     for control circuit	100 ms
for control circuit  inculation voltage rated value	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2 6 kV
impulse voltage rated value blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	O KV
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	32.020.0
• ramp-up (soft starting)	Yes
• ramp-down (soft stop)	Yes
• Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Full motor protection (thermistor motor protection and electronic
·	motor overload protection)
<ul> <li>evaluation of thermistor motor protection</li> </ul>	Yes; Type A PTC or Klixon / Thermoclick
inside-delta circuit	Yes
• auto-RESET	Yes
manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
communication function	Yes
<ul> <li>operating measured value display</li> </ul>	Yes; Only in conjunction with special accessories
error logbook	Yes; Only in conjunction with special accessories
<ul> <li>via software parameterizable</li> </ul>	No
• via software configurable	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
• firmware update	Yes
<ul> <li>removable terminal for control circuit</li> </ul>	Yes
torque control	No
analog output	No
Power Electronics	
operational current	
<ul> <li>at 40 °C rated value</li> </ul>	370 A
<ul> <li>at 50 °C rated value</li> </ul>	328 A
at 60 °C rated value	300 A
operational current at inside-delta circuit	
• at 40 °C rated value	641 A
at 50 °C rated value	568 A
at 60 °C rated value	519 A
operating voltage	
rated value	200 600 V
at inside-delta circuit rated value	200 600 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	

1000 1/ 140 00 1 1	440 100
• at 230 V at 40 °C rated value	110 kW
• at 230 V at inside-delta circuit at 40 °C rated value	200 kW
• at 400 V at 40 °C rated value	200 kW
<ul> <li>at 400 V at inside-delta circuit at 40 °C rated value</li> </ul>	355 kW
at 500 V at 40 °C rated value	250 kW
at 500 V at inside-delta circuit at 40 °C rated value	450 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
<ul> <li>at rotary coding switch on switch position 1</li> </ul>	160 A
<ul> <li>at rotary coding switch on switch position 2</li> </ul>	174 A
<ul> <li>at rotary coding switch on switch position 3</li> </ul>	188 A
<ul> <li>at rotary coding switch on switch position 4</li> </ul>	202 A
<ul> <li>at rotary coding switch on switch position 5</li> </ul>	216 A
<ul> <li>at rotary coding switch on switch position 6</li> </ul>	230 A
<ul> <li>at rotary coding switch on switch position 7</li> </ul>	244 A
<ul> <li>at rotary coding switch on switch position 8</li> </ul>	258 A
<ul> <li>at rotary coding switch on switch position 9</li> </ul>	272 A
<ul> <li>at rotary coding switch on switch position 10</li> </ul>	286 A
<ul> <li>at rotary coding switch on switch position 11</li> </ul>	300 A
<ul> <li>at rotary coding switch on switch position 12</li> </ul>	314 A
<ul> <li>at rotary coding switch on switch position 13</li> </ul>	328 A
<ul> <li>at rotary coding switch on switch position 14</li> </ul>	342 A
<ul> <li>at rotary coding switch on switch position 15</li> </ul>	356 A
<ul> <li>at rotary coding switch on switch position 16</li> </ul>	370 A
• minimum	160 A
adjustable motor current	
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 1</li> </ul>	277 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 2</li> </ul>	301 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 3</li> </ul>	326 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 4</li> </ul>	350 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 5</li> </ul>	374 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 6</li> </ul>	398 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 7</li> </ul>	423 A
for inside-delta circuit at rotary coding switch on switch position 8      for inside delta circuit at rotary coding switch on	447 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 9</li> <li>for inside-delta circuit at rotary coding switch on</li> </ul>	471 A 495 A
ior inside-delta circuit at rotary coding switch on switch position 10     for inside-delta circuit at rotary coding switch on	520 A
switch position 11  • for inside-delta circuit at rotary coding switch on	544 A
switch position 12  • for inside-delta circuit at rotary coding switch on	568 A
switch position 13  • for inside-delta circuit at rotary coding switch on	592 A
switch position 14  • for inside-delta circuit at rotary coding switch on	617 A
switch position 15  • for inside-delta circuit at rotary coding switch on	641 A
switch position 16  • at inside-delta circuit minimum	277 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	
posses i coo jui jui latea talae el tile callelle at Ae	

<ul> <li>at 40 °C after startup</li> </ul>	123 W
<ul> <li>at 50 °C after startup</li> </ul>	110 W
• at 60 °C after startup	102 W
power loss [W] at AC at current limitation 350 %	
at 40 °C during startup	5 575 W
at 50 °C during startup     at 50 °C during startup	4 706 W
at 60 °C during startup	4 157 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	AO/DC
• at 50 Hz rated value	24 V
at 60 Hz rated value     at 60 Hz rated value	24 V
	-20 %
relative negative tolerance of the control supply voltage at AC at 50 Hz	
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
at DC rated value	24 V
relative negative tolerance of the control supply	-20 %
voltage at DC relative positive tolerance of the control supply	20 %
voltage at DC	160 mA
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	470 mA
locked-rotor current at close of bypass contact maximum	7.6 A
inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	0
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting
	surface +/- 22.5° tiltable to the front and back
fastening method	screw fixing
height	393 mm
width	210 mm
depth	203 mm
required spacing with side-by-side mounting	
<ul><li>forwards</li></ul>	10 mm
<ul><li>backwards</li></ul>	0 mm
• upwards	100 mm

<ul><li>downwards</li></ul>	75 mm
at the side	5 mm
weight without packaging	9.9 kg
Connections/ Terminals	
type of electrical connection	
<ul> <li>for main current circuit</li> </ul>	busbar connection
for control circuit	spring-loaded terminals
width of connection bar maximum	45 mm
wire length for thermistor connection	
<ul> <li>with conductor cross-section = 0.5 mm² maximum</li> </ul>	50 m
<ul> <li>with conductor cross-section = 1.5 mm² maximum</li> </ul>	150 m
• with conductor cross-section = 2.5 mm² maximum	250 m
type of connectable conductor cross-sections	
<ul> <li>for DIN cable lug for main contacts stranded</li> </ul>	2x (50 240 mm²)
for DIN cable lug for main contacts finely stranded	2x (70 240 mm²)
type of connectable conductor cross-sections	
<ul> <li>for control circuit solid</li> </ul>	2x (0.25 1.5 mm²)
<ul> <li>for control circuit finely stranded with core end processing</li> </ul>	2x (0.25 1.5 mm²)
<ul> <li>at AWG cables for control circuit solid</li> </ul>	2x (24 16)
at AWG cables for control circuit finely stranded with core end processing	2x (24 16)
wire length	
<ul> <li>between soft starter and motor maximum</li> </ul>	800 m
<ul> <li>at the digital inputs at AC maximum</li> </ul>	100 m
at the digital inputs at DC maximum	1 000 m
tightening torque	
<ul> <li>for main contacts with screw-type terminals</li> </ul>	14 24 N·m
<ul> <li>for auxiliary and control contacts with screw-type terminals</li> </ul>	0.8 1.2 N·m
tightening torque [lbf·in]	
<ul> <li>for main contacts with screw-type terminals</li> </ul>	124 210 lbf·in
<ul> <li>for auxiliary and control contacts with screw-type terminals</li> </ul>	7 10.3 lbf·in
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
during storage and transport	-40 +80 °C
environmental category	
<ul> <li>during operation according to IEC 60721</li> </ul>	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
<ul> <li>during storage according to IEC 60721</li> </ul>	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
<ul> <li>PROFINET standard</li> </ul>	Yes
• EtherNet/IP	Yes
<ul> <li>Modbus RTU</li> </ul>	Yes
<ul> <li>Modbus TCP</li> </ul>	Yes
• PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of the fuse	
<ul> <li>usable for Standard Faults up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 1200 A; Iq = 18 kA
<ul> <li>usable for High Faults up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 1200 A; Iq = 100 kA
usable for Standard Faults at inside-delta	Type: Class J / L, max. 1200 A; Iq = 18 kA

circuit up to 575/600 V according to UL	
<ul> <li>usable for High Faults at inside-delta circuit up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 1200 A; Iq = 100 kA
operating power [hp] for 3-phase motors	
<ul> <li>at 200/208 V at 50 °C rated value</li> </ul>	100 hp
<ul> <li>at 220/230 V at 50 °C rated value</li> </ul>	125 hp
<ul> <li>at 460/480 V at 50 °C rated value</li> </ul>	250 hp
<ul> <li>at 575/600 V at 50 °C rated value</li> </ul>	300 hp
<ul> <li>at 200/208 V at inside-delta circuit at 50 °C rated value</li> </ul>	200 hp
<ul> <li>at 220/230 V at inside-delta circuit at 50 °C rated value</li> </ul>	200 hp
<ul> <li>at 460/480 V at inside-delta circuit at 50 °C rated value</li> </ul>	450 hp
<ul> <li>at 575/600 V at inside-delta circuit at 50 °C rated value</li> </ul>	600 hp
contact rating of auxiliary contacts according to UL	R300-B300
Safety related data	
protection class IP on the front according to IEC 60529	IP00; IP20 with cover
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with cover
electromagnetic compatibility	in accordance with IEC 60947-4-2
Certificates/ approvals	

Confirmation









**EMC** 

**Declaration of Conformity** 

**General Product Approval** 

**Test Certificates** 

Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

## Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5246-2TC05

Cax online generator

 $\underline{\text{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RW5246-2TC05}$ 

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5246-2TC05

 $Image\ database\ (product\ images, 2D\ dimension\ drawings, 3D\ models, device\ circuit\ diagrams,\ EPLAN\ macros,\ ...)$ 

 $\underline{\text{http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RW5246-2TC05\&lang=en}$ 

Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5246-2TC05/char

Characteristic: Installation altitude

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified: 4/10/2022 🖸