SIEMENS

Data sheet

3RW5248-6TC05



SIRIUS soft starter 200-600 V 570 A, 24 V AC/DC Screw terminals Thermistor input

product brand name	SIRIUS
product stategory	Hybrid switching devices
product designation	Soft starter
product designation	3RW52
manufacturer's article number	5111152
of standard HMI module usable	3RW5980-0HS00
of high feature HMI module usable	<u>3RW5980-0HF00</u>
 of night leader in induce deable of communication module PROFINET standard usable 	<u>3RW5980-0CS00</u>
 of communication module PROFIBUS usable 	<u>3RW5980-0CP00</u>
 of communication module Modbus TCP usable 	<u>3RW5980-0CT00</u>
 of communication module Modbus RTU usable 	<u>3RW5980-0CR00</u>
 of communication module Ethernet/IP 	<u>3RW5980-0CE00</u>
 of circuit breaker usable at 400 V 	3VA2580-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V 	3VA2580-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2510-6HN32-0AA0: Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V at inside-delta circuit 	3VA2510-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of the gG fuse usable up to 690 V 	2x3NA3365-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	2x3NA3365-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	<u>3NE1437-2: Type of coordination 2. Iq = 65 kA</u>
 of back-up R fuse link for semiconductor protection usable up to 690 V 	<u>3NE3340-8; Type of coordination 2, Iq = 65 kA</u>
eneral technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
 UL approval 	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
• is supported HMI-Standard	Yes
 is supported HMI-High Feature 	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	
 for main current circuit 	100 ms
for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
 between main and auxiliary circuit 	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	
 ramp-up (soft starting) 	Yes
• ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
• pump ramp down	Yes
intrinsic device protection	Yes
 motor overload protection 	Yes; Full motor protection (thermistor motor protection and electronic motor overload protection)
 evaluation of thermistor motor protection 	Yes; Type A PTC or Klixon / Thermoclick
inside-delta circuit	Yes
• auto-RESET	Yes
manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
communication function	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
• error logbook	Yes; Only in conjunction with special accessories
via software parameterizable	No
 via software configurable 	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
 firmware update 	Yes
 removable terminal for control circuit 	Yes
torque control	No
analog output	No
Power Electronics	
operational current	
at 40 °C rated value	570 A
• at 50 °C rated value	504 A
at 60 °C rated value	460 A
operational current at inside-delta circuit	
at 40 °C rated value	987 A
• at 50 °C rated value	873 A
at 60 °C rated value	796 A
operating voltage	
rated value	200 600 V
at inside-delta circuit rated value	200 600 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	

• at 230 V at 40 °C rated value	160 kW
 at 230 V at inside-delta circuit at 40 °C rated value 	315 kW
 at 400 V at 40 °C rated value 	315 kW
 at 400 V at inside-delta circuit at 40 °C rated value 	560 kW
 at 500 V at 40 °C rated value 	355 kW
 at 500 V at inside-delta circuit at 40 °C rated value 	630 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
 at rotary coding switch on switch position 1 	240 A
 at rotary coding switch on switch position 2 	262 A
 at rotary coding switch on switch position 3 	284 A
 at rotary coding switch on switch position 4 	306 A
 at rotary coding switch on switch position 5 	328 A
 at rotary coding switch on switch position 6 	350 A
 at rotary coding switch on switch position 7 	372 A
 at rotary coding switch on switch position 8 	394 A
 at rotary coding switch on switch position 9 	416 A
 at rotary coding switch on switch position 10 	438 A
 at rotary coding switch on switch position 11 	460 A
 at rotary coding switch on switch position 12 	482 A
 at rotary coding switch on switch position 13 	504 A
 at rotary coding switch on switch position 14 	526 A
 at rotary coding switch on switch position 15 	548 A
 at rotary coding switch on switch position 16 	570 A
• minimum	240 A
adjustable motor current	
 for inside-delta circuit at rotary coding switch on switch position 1 	416 A
 for inside-delta circuit at rotary coding switch on switch position 2 	454 A
• for inside-delta circuit at rotary coding switch on switch position 3	492 A
• for inside-delta circuit at rotary coding switch on switch position 4	530 A
 for inside-delta circuit at rotary coding switch on switch position 5 	568 A
 for inside-delta circuit at rotary coding switch on switch position 6 for inside delta circuit at rotary coding switch on 	606 A
 for inside-delta circuit at rotary coding switch on switch position 7 for inside delta circuit at rotary coding switch on 	644 A
 for inside-delta circuit at rotary coding switch on switch position 8 for inside-delta circuit at rotary coding switch on 	682 A 721 A
 for inside-delta circuit at rotary coding switch on switch position 9 for inside-delta circuit at rotary coding switch on 	759 A
 for inside-delta circuit at rotary coding switch on switch position 10 for inside-delta circuit at rotary coding switch on 	797 A
 for inside-delta circuit at rotary coding switch on switch position 11 for inside-delta circuit at rotary coding switch on 	835 A
 for inside delta circuit at rotary coding switch on for inside-delta circuit at rotary coding switch on 	873 A
 for inside-delta circuit at rotary coding switch on for inside-delta circuit at rotary coding switch on 	911 A
 for inside delta circuit at rotary coding switch on switch position 14 for inside-delta circuit at rotary coding switch on 	949 A
 switch position 15 for inside-delta circuit at rotary coding switch on 	987 A
 switch position 16 at inside-delta circuit minimum 	416 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	

 at 40 °C after startup 	183 W
• at 50 °C after startup	163 W
• at 60 °C after startup	153 W
power loss [W] at AC at current limitation 350 %	
• at 40 °C during startup	10 241 W
 at 50 °C during startup 	8 500 W
• at 60 °C during startup	7 663 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
• at 50 Hz rated value	24 V
• at 60 Hz rated value	24 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
 at DC rated value 	24 V
relative negative tolerance of the control supply voltage at DC	-20 %
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	470 mA
locked-rotor current at close of bypass contact maximum	7.6 A
inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	0
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back
fastening method	screw fixing
height	393 mm
width	210 mm
depth	203 mm
required spacing with side-by-side mounting	10
• forwards	10 mm
backwards	0 mm
 upwards 	100 mm

downwards	75 mm
at the side	5 mm
weight without packaging	10.6 kg
Connections/ Terminals	
type of electrical connection	
for main current circuit	busbar connection
for control circuit	screw-type terminals
width of connection bar maximum	45 mm
wire length for thermistor connection	
 with conductor cross-section = 0.5 mm² maximum 	50 m
 with conductor cross-section = 1.5 mm² maximum 	150 m
 with conductor cross-section = 2.5 mm² maximum 	250 m
type of connectable conductor cross-sections	
 for DIN cable lug for main contacts stranded 	2x (50 240 mm²)
 for DIN cable lug for main contacts finely stranded 	2x (70 240 mm²)
type of connectable conductor cross-sections	
for control circuit solid	1x (0.5 4.0 mm ²), 2x (0.5 2.5 mm ²)
 for control circuit finely stranded with core end processing 	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
at AWG cables for control circuit solid	1x (20 12), 2x (20 14)
wire length	
 between soft starter and motor maximum 	800 m
at the digital inputs at AC maximum	100 m
at the digital inputs at DC maximum	1 000 m
tightening torque	14 04 N m
for main contacts with screw-type terminals	14 24 N·m
 for auxiliary and control contacts with screw-type terminals 	0.8 1.2 N·m
tightening torque [lbf·in]	
 for main contacts with screw-type terminals 	124 210 lbf·in
 for auxiliary and control contacts with screw-type terminals 	7 10.3 lbf·in
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
 during operation 	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
 during storage and transport 	-40 +80 °C
environmental category	
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
 during transport according to IEC 60721 	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
 of the fuse 	
 — usable for Standard Faults up to 575/600 V according to UL 	Type: Class J / L, max. 1600 A; Iq = 30 kA
 — usable for High Faults up to 575/600 V according to UL 	Type: Class J / L, max. 1200 A; Iq = 100 kA
 usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL 	Type: Class J / L, max. 1600 A; Iq = 30 kA
circuit up to 373/000 v according to DE	

to 575/600 V a						
			_			
operating power [hp]	-	5	4 5 0 1			
 at 200/208 V at 5 			150 hp			
• at 220/230 V at 5			200 hp			
• at 460/480 V at 5			400 hp			
• at 575/600 V at 5		50 °0 1 1	500 hp			
at 200/208 V at inside-delta circuit at 50 °C rated value		300 hp				
value	iside-delta circuit at		350 hp			
value	iside-delta circuit at		750 hp			
value	iside-delta circuit at		950 hp)		
contact rating of auxil	iary contacts acco	rding to UL	R300-E	B300		
Safety related data						
protection class IP on 60529	the front accordin	g to IEC	IP00; II	P20 with cover		
touch protection on the		to IEC 60529	-	safe, for vertical contac		over
electromagnetic comp	patibility		in acco	ordance with IEC 60947	7-4-2	
Certificates/ approvals						
General Product App	roval					EMC
		<u>Confirmation</u>	<u>on</u>		EHC	RCM
Declaration of Confo	mity	Test Certifica	ates	Marine / Shipping		
Declaration of Confor	UK CA	Test Certifica Type Test Ce ates/Test Re	ertific-	Marine / Shipping	BUREAU VERITAS	Llovets Register uis
CE		Type Test Ce	ertific-		BUREAU VERITAS	Lloyd's Register Lits
C E EG-Konf.		<u>Type Test Ce</u> ates/Test Re	ertific- eport		BUREAU VERITAS	Llovets Register uis
C E EG-Konf.		Type Test Ce ates/Test Re other <u>Confirmation</u>	on		BUREAU VERITAS	Lis

last modified: