SIEMENS

Data sheet

3RA2110-1JA16-1AK6




FUSELESS LOAD FEEDER DIRECT START, AC 400V, SZ. S00 7. . .10A, AC 110/120V 50/60HZ SCREW TERMINAL FOR RAIL MOUNTING, TYPE OF ASSIGNMENT 1,IQ = 150KA 1NO (CONTACTOR)

product brand name	SIRIUS			
product designation	_ non-fused load feeders 3RA2			
design of the product	direct starter			
manufacturer's article number				
of the supplied contactor	<u>3RT2016-1AK61</u>			
 of the supplied circuit-breakers 	3RV2011-1JA10			
 of the supplied link module 	3RA1921-1DA00			
General technical data				
size of the circuit-breaker	S00			
size of load feeder	S00			
product extension auxiliary switch	Yes			
insulation voltage with degree of pollution 3 at AC rated value	690 V			
degree of pollution	3			
surge voltage resistance rated value	6 kV			
shock resistance according to IEC 60068-2-27	6g / 11 ms			
mechanical service life (switching cycles) of contactor typical	30 000 000			
type of assignment	1			
Substance Prohibitance (Date)	10/01/2009			
Ambient conditions				
ambient temperature				
 during operation 	-20 +60 °C			
 during storage 	-50 +80 °C			
 during transport 	-50 +80 °C			
Main circuit				
number of poles for main current circuit	3			
design of the switching contact	electromechanical			
adjustable current response value current of the current-dependent overload release	7 10 A			
operating voltage				
rated value	690 V			
 at AC-3 rated value maximum 	690 V			
operating frequency rated value	50 60 Hz			
operational current at AC-3 at 400 V rated value	8.5 A			
operating power at AC-3				
• at 400 V rated value	4 000 W			
a at EQO V rated value	5 500 W			
 at 500 V rated value 				
at 500 V rated value at 690 V rated value	7 500 W			

control supply voltage at AC			
• at 50 Hz rated value	110 V		
at 60 Hz rated value	120 V		
apparent holding power of magnet coil at AC	4.2 VA		
Protective and monitoring functions			
trip class	CLASS 10		
design of the overload release	thermal (bimetallic)		
response value current of instantaneous short-circuit trip	130 A		
unit			
UL/CSA ratings			
full-load current (FLA) for 3-phase AC motor			
 at 480 V rated value 	7.6 A		
at 600 V rated value	9 A		
yielded mechanical performance [hp]			
 for 3-phase AC motor 			
— at 200/208 V rated value	2 hp		
— at 220/230 V rated value	3 hp		
— at 460/480 V rated value	5 hp		
— at 575/600 V rated value	7.5 hp		
Short-circuit protection			
product function short circuit protection	Yes		
design of the short-circuit trip	magnetic		
conditional short-circuit current (Iq)			
 at 690 V according to IEC 60947-4-1 rated value 	4 000 A		
 at 400 V according to IEC 60947-4-1 rated value 	153 000 A		
 at 500 V according to IEC 60947-4-1 rated value 	42 000 A		
Installation/ mounting/ dimensions			
mounting position	vertical		
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail		
height	167.2 mm		
width	45 mm		
depth	97.1 mm		
required spacing			
 for grounded parts 			
— forwards	0 mm		
— backwards	0 mm		
— upwards	20 mm		
— at the side	9 mm		
— downwards	10 mm		
• for live parts			
— forwards	0 mm		
— backwards	0 mm		
— upwards	20 mm		
— downwards	10 mm		
— at the side	9 mm		
Connections/ Terminals			
type of electrical connection for main current circuit	screw-type terminals		
type of connectable conductor cross-sections			
for main contacts stranded	0.5 4 mm², 2x (0.75 2.5 mm²)		
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12		
connectable conductor cross-section for main contacts	0.5 2.5 mm ²		
finely stranded with core end processing	0.0 2.0 mm		
Safety related data			
B10 value with high demand rate according to SN 31920	1 000 000		
proportion of dangerous failures with high demand rate according to SN 31920	73 %		
protection class IP on the front according to IEC 60529	IP20		
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front		
Certificates/ approvals			

General Product A	pproval			For use in hazard- ous locations	Declaration of Conformity	
SP EM	<u>Confirmation</u>	(UL)	EHC	KEX ATEX	CE EG-Konf.	
Declaration of Conformity	Test Certificates		Marine / Shipping			
UK CA	Special Test Certific- ate	<u>Type Test Certific-</u> ates/Test Report	ABS	BUREAU VERITAS	Lloyd's Register Lits	
Marine / Shipping				other	Railway	
PRS	RINA	RMRS	CINV-GL EXYSLEDIELE	<u>Confirmation</u>	Vibration and Shock	
Further information Information- and Downloadcenter (Catalogs, Brochures,) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-1JA16-1AK6 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-1JA16-1AK6 Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-1JA16-1AK6 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-1JA16-1AK6⟨=en						

Characteristic: Tripping characteristics, I²t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-1JA16-1AK6/char Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-1JA16-1AK6&objecttype=14&gridview=view1



last modified:

12/15/2020 🖸