Data sheet

3RA2210-0BA15-2AP6



FUSELESS MOTOR STARTER REVERSING OPERATION 600V AC SZ S00 0.14-0.2A 220/240V AC 50/60HZ SCREW CONNECTION FOR SCREW MOUNTING OR 35 MM RAIL-MOUNTING TYPE OF COORDINATION 2 IQ = 150 KA ALSO FULFILLS TYPE OF COORDINATION 1 1NC (PER CONTACTOR)

product brand name	SIRIUS	
product designation	non-fused motor starter 3RA2	
design of the product	reversing starter	
manufacturer's article number		
 of the supplied contactor 	3RT2015-1AP62	
 of the supplied circuit-breakers 	3RV2011-0BA10	
 of the supplied link module 	3RA1921-1DA00	
General technical data		
size of the circuit-breaker	S00	
size of load feeder	S00	
product extension auxiliary switch	Yes	
insulation voltage with degree of pollution 3 at AC rated value	690 V	
degree of pollution	3	
surge voltage resistance rated value	6 kV	
shock resistance according to IEC 60068-2-27	6g / 11 ms	
mechanical service life (switching cycles) of contactor typical	30 000 000	
type of assignment	2	
Substance Prohibitance (Date)	03/01/2017	
Ambient conditions		
ambient temperature		
 during operation 	-20 +60 °C	
 during storage 	-50 +80 °C	
 during transport 	-55 +80 °C	
Main circuit		
number of poles for main current circuit	3	
design of the switching contact	electromechanical	
adjustable current response value current of the current-dependent overload release	0.14 0.2 A	
operating voltage		
rated value	690 V	
at AC-3 rated value maximum	690 V	
operating frequency rated value	50 60 Hz	
operational current at AC-3 at 400 V rated value	0.2 A	
operating power at AC-3		
at 400 V rated value	60 W	
● at 500 V rated value	60 W	
at 690 V rated value	90 W	
Control circuit/ Control		

touch protection on the front according to IEC 60529 Certificates/ approvals General Product Approval	finger-safe, for vertical conta	act from the front For use in hazard- Declaration of
touch protection on the front according to IEC 60529		act from the front
		act from the front
protection class IP on the front according to IEC 60529	IP/U	
according to SN 31920	IP20	
proportion of dangerous failures with high demand rate	73 %	
B10 value with high demand rate according to SN 31920	1 000 000	
Safety related data		
connectable conductor cross-section for main contacts finely stranded with core end processing	0.5 2.5 mm ²	
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12	
 for main contacts stranded 	0.5 4 mm², 2x (0.75 2.5 mm²)	
type of connectable conductor cross-sections		
type of electrical connection for main current circuit	screw-type terminals	
Connections/ Terminals		
— at the side	9 mm	
— downwards	10 mm	
— upwards	20 mm	
— backwards	0 mm	
— forwards	0 mm	
• for live parts		
— downwards	10 mm	
— at the side	9 mm	
— upwards	20 mm	
— backwards	0 mm	
— forwards	0 mm	
for grounded parts		
required spacing		
depth	97.1 mm	
width	90 mm	
height	170 mm	, , , , , , , , , , , , , , , , , , , ,
fastening method	_	r screw-mounted with additional push-in lug
mounting position	vertical	
Installation/ mounting/ dimensions		
at 500 V according to IEC 60947-4-1 rated value	100 000 A	
• at 400 V according to IEC 60947-4-1 rated value	153 000 A	
at 690 V according to IEC 60947-4-1 rated value	100 000 A	
conditional short-circuit current (Iq)		
design of the short-circuit trip	magnetic	
product function short circuit protection	Yes	
Short-circuit protection		
unit	2.0 A	
design of the overload release response value current of instantaneous short-circuit trip	thermal (bimetallic) 2.6 A	
trip class	CLASS 10	
Protective and monitoring functions	01.400.40	
number of NO contacts for auxiliary contacts	U	
number of NC contacts for auxiliary contacts	_ 1 0	
Auxiliary circuit	1	
coil		
inductive power factor with the holding power of the	0.25	
apparent holding power of magnet coil at AC	4.8 VA	
at 60 Hz rated value	192 264 V	
 at 60 Hz rated value 	240 V	
• at 50 Hz rated value	187 242 V	
at 50 Hz rated value	220 V	
control supply voltage at AC		



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certific-<u>ate</u>

Type Test Certificates/Test Report







Marine / Shipping

other









Confirmation

Vibration and Shock

Railway

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-0BA15-2AP6

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2210-0BA15-2AP6

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0BA15-2AP6

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2210-0BA15-2AP6&lang=en


Characteristic: Tripping characteristics, I2t, Let-through current


https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0BA15-2AP6/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-0BA15-2AP6&objecttype=14&gridview=view1







last modified: 12/15/2020 🖸