SIEMENS

Data sheet 3RW5227-3AC04



SIRIUS soft starter 200-480 V 93 A, 24 V AC/DC spring-type terminals Analog output

product brand name	SIRIUS	
product category	Hybrid switching devices	
product designation	Soft starter	
product type designation	3RW52	
manufacturer's article number		
 of standard HMI module usable 	3RW5980-0HS00	
 of high feature HMI module usable 	3RW5980-0HF00	
 of communication module PROFINET standard usable 	3RW5980-0CS00	
 of communication module PROFIBUS usable 	3RW5980-0CP00	
 of communication module Modbus TCP usable 	3RW5980-0CT00	
 of communication module Modbus RTU usable 	3RW5980-0CR00	
 of communication module Ethernet/IP 	3RW5980-0CE00	
 of circuit breaker usable at 400 V 	3VA2216-7MN32-0AA0; Type of coordination 1, Iq = 15 kA, CLASS 10	
 of circuit breaker usable at 500 V 	3VA2216-7MN32-0AA0; Type of coordination 1, Iq = 10 kA, CLASS 10	
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2220-7MN32-0AA0; Type of coordination 1, Iq = 15 kA, CLASS 10	
 of circuit breaker usable at 500 V at inside-delta circuit 	3VA2220-7MN32-0AA0; Type of coordination 1, Iq = 10 kA, CLASS 10	
 of the gG fuse usable up to 690 V 	3NA3136-6; Type of coordination 1, Iq = 65 kA	
 of the gG fuse usable at inside-delta circuit up to 500 V 	3NA3136-6; Type of coordination 1, Iq = 65 kA	
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1224-0: Type of coordination 2, Iq = 65 kA	
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE4124; Type of coordination 2, Iq = 65 kA	

General technical data		
starting voltage [%]	30 100 %	
stopping voltage [%]	50 %; non-adjustable	
start-up ramp time of soft starter	0 20 s	
current limiting value [%] adjustable	130 700 %	
certificate of suitability		
 CE marking 	Yes	
UL approval	Yes	
CSA approval	Yes	
product component		
HMI-High Feature	No	
 is supported HMI-Standard 	Yes	
is supported HMI-High Feature	Yes	
product feature integrated bypass contact system	Yes	
number of controlled phases	3	

trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2		
buffering time in the event of power failure			
for main current circuit	100 ms		
for control circuit	100 ms		
insulation voltage rated value	600 V		
degree of pollution	3, acc. to IEC 60947-4-2		
impulse voltage rated value	6 kV		
blocking voltage of the thyristor maximum	1 400 V		
service factor	1		
surge voltage resistance rated value	6 kV		
maximum permissible voltage for safe isolation			
 between main and auxiliary circuit 	600 V		
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting		
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz		
utilization category according to IEC 60947-4-2	AC 53a		
reference code according to IEC 81346-2	Q		
Substance Prohibitance (Date)	02/15/2018		
product function			
ramp-up (soft starting)	Yes		
ramp-down (soft stop)	Yes		
Soft Torque	Yes		
 adjustable current limitation 	Yes		
 pump ramp down 	Yes		
 intrinsic device protection 	Yes		
motor overload protection	Yes; Electronic motor overload protection		
 evaluation of thermistor motor protection 	No		
inside-delta circuit	Yes		
auto-RESET	Yes		
manual RESET	Yes		
remote reset	Yes; By turning off the control supply voltage		
communication function	Yes		
 operating measured value display 	Yes; Only in conjunction with special accessories		
error logbook	Yes; Only in conjunction with special accessories		
via software parameterizable	No		
via software configurable	Yes		
PROFlenergy	Yes; in connection with the PROFINET Standard communication module		
firmware update	Yes		
 removable terminal for control circuit 	Yes		
• torque control	No		
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)		
Power Electronics			
operational current			
at 40 °C rated value	93 A		
at 50 °C rated value	83 A		
at 60 °C rated value	76 A		
operational current at inside-delta circuit			
at 40 °C rated value	161 A		
at 50 °C rated value	143 A		
at 60 °C rated value	131 A		
operating voltage			
rated value	200 480 V		
at inside-delta circuit rated value	200 480 V		
relative negative tolerance of the operating voltage	-15 %		
relative positive tolerance of the operating voltage	10 %		
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %		
relative positive tolerance of the operating voltage at inside-delta circuit	10 %		
operating power for 3-phase motors			

-1 000 1/ -1 40 00	00 1144
at 230 V at 40 °C rated value t 200 V at inside delta signality at 40 °C rated value.	22 kW
at 230 V at inside-delta circuit at 40 °C rated value at 400 V at 40 °C rated value	45 kW
at 400 V at 40 °C rated value at 400 V at inside delta circuit at 40 °C rated value.	45 kW
at 400 V at inside-delta circuit at 40 °C rated value Operating frequency 1 rated value	90 kW 50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	10 /0
at rotary coding switch on switch position 1	40.5 A
at rotary coding switch on switch position 2	44 A
at rotary coding switch on switch position 3	47.5 A
at rotary coding switch on switch position 4	51 A
at rotary coding switch on switch position 5	54.5 A
at rotary coding switch on switch position 6	58 A
at rotary coding switch on switch position 7	61.5 A
at rotary coding switch on switch position 8	65 A
at rotary coding switch on switch position 9	68.5 A
at rotary coding switch on switch position 10	72 A
at rotary coding switch on switch position 11	75.5 A
at rotary coding switch on switch position 12	79 A
at rotary coding switch on switch position 13	82.5 A
at rotary coding switch on switch position 14	86 A
at rotary coding switch on switch position 15	89.5 A
at rotary coding switch on switch position 16	93 A
• minimum	40.5 A
adjustable motor current	
 for inside-delta circuit at rotary coding switch on switch position 1 	70.1 A
 for inside-delta circuit at rotary coding switch on switch position 2 	76.2 A
 for inside-delta circuit at rotary coding switch on switch position 3 	82.3 A
 for inside-delta circuit at rotary coding switch on switch position 4 	88.3 A
 for inside-delta circuit at rotary coding switch on switch position 5 	94.4 A
 for inside-delta circuit at rotary coding switch on switch position 6 	100 A
 for inside-delta circuit at rotary coding switch on switch position 7 	107 A
 for inside-delta circuit at rotary coding switch on switch position 8 	113 A
 for inside-delta circuit at rotary coding switch on switch position 9 	119 A
 for inside-delta circuit at rotary coding switch on switch position 10 	125 A
for inside-delta circuit at rotary coding switch on switch position 11	131 A
for inside-delta circuit at rotary coding switch on switch position 12	137 A
 for inside-delta circuit at rotary coding switch on switch position 13 	143 A
 for inside-delta circuit at rotary coding switch on switch position 14 	149 A
 for inside-delta circuit at rotary coding switch on switch position 15 	155 A
 for inside-delta circuit at rotary coding switch on switch position 16 	161 A
at inside-delta circuit minimum	70.1 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	40.14
• at 40 °C after startup	40 W
at 50 °C after startup	37 W

10000 %	0514	
• at 60 °C after startup	35 W	
power loss [W] at AC at current limitation 350 %	4.0=0.14	
• at 40 °C during startup	1 270 W	
• at 50 °C during startup	1 077 W	
at 60 °C during startup	959 W	
Control circuit/ Control		
type of voltage of the control supply voltage	AC/DC	
control supply voltage at AC		
at 50 Hz rated value	24 V	
at 60 Hz rated value	24 V	
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %	
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %	
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %	
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %	
control supply voltage frequency	50 60 Hz	
relative negative tolerance of the control supply voltage frequency	-10 %	
relative positive tolerance of the control supply voltage frequency	10 %	
control supply voltage		
at DC rated value	24 V	
relative negative tolerance of the control supply voltage at DC	-20 %	
relative positive tolerance of the control supply voltage at DC	20 %	
control supply current in standby mode rated value	160 mA	
holding current in bypass operation rated value	380 mA	
locked-rotor current at close of bypass contact maximum	7.6 A	
inrush current peak at application of control supply voltage maximum	3.3 A	
duration of inrush current peak at application of control supply voltage	12.1 ms	
design of the overvoltage protection	Varistor	
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply	
Inputs/ Outputs		
number of digital inputs	1	
number of digital outputs	3	
not parameterizable	2	
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)	
number of analog outputs	1	
switching capacity current of the relay outputs		
at AC-15 at 250 V rated value	3 A	
• at DC-13 at 24 V rated value	1 A	
Installation/ mounting/ dimensions		
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back	
factoning method	surface +/- 22.5° tiltable to the front and back screw fixing	
fastening method	306 mm	
height width	185 mm	
depth	203 mm	
required spacing with side-by-side mounting	200 11111	
• forwards	10 mm	
backwards	0 mm	
upwards	100 mm	
downwards	75 mm	
at the side	5 mm	
♥ at the side	O THILL	

weight without packaging	6.9 kg		
Connections/ Terminals			
type of electrical connection			
for main current circuit	box terminal		
for control circuit	spring-loaded terminals		
width of connection bar maximum	25 mm		
type of connectable conductor cross-sections			
 for main contacts for box terminal using the front clamping point solid 	1x (2.5 16 mm²)		
 for main contacts for box terminal using the front clamping point finely stranded with core end processing 	1x (2.5 50 mm²)		
 for main contacts for box terminal using the front clamping point stranded 	1x (10 70 mm²)		
 at AWG cables for main contacts for box terminal using the front clamping point 	1x (10 2/0)		
 for main contacts for box terminal using the back clamping point solid 	1x (2.5 16 mm²)		
 at AWG cables for main contacts for box terminal using the back clamping point 	1x (10 2/0)		
 for main contacts for box terminal using both clamping points solid 	2x (2.5 16 mm²)		
 for main contacts for box terminal using both clamping points finely stranded with core end processing 	2x (2.5 35 mm²)		
 for main contacts for box terminal using both clamping points stranded 	2x (6 16 mm²), 2x (10 50 mm²)		
 for main contacts for box terminal using the back clamping point finely stranded with core end processing 	1x (2.5 50 mm²)		
 for main contacts for box terminal using the back clamping point stranded 	1x (10 70 mm²)		
type of connectable conductor cross-sections			
 for control circuit solid 	2x (0.25 1.5 mm²)		
 for control circuit finely stranded with core end processing 	2x (0.25 1.5 mm²)		
 at AWG cables for control circuit solid 	2x (24 16)		
 at AWG cables for control circuit finely stranded with core end processing 	2x (24 16)		
wire length			
 between soft starter and motor maximum 	800 m		
 at the digital inputs at AC maximum 	100 m		
 at the digital inputs at DC maximum 	1 000 m		
tightening torque			
 for main contacts with screw-type terminals 	4.5 6 N⋅m		
 for auxiliary and control contacts with screw-type terminals 	0.8 1.2 N·m		
tightening torque [lbf·in]			
 for main contacts with screw-type terminals 	40 53 lbf·in		
 for auxiliary and control contacts with screw-type terminals 	7 10.3 lbf·in		
Ambient conditions			
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog		
ambient temperature			
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above		
during storage and transport	-40 +80 °C		
environmental category			
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6		
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4		
 during transport according to IEC 60721 	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)		
EMC emitted interference	acc. to IEC 60947-4-2: Class A		
Communication/ Protocol			

communication module is supported			
PROFINET standard	Voc		
EtherNet/IP	Yes		
	Yes		
Modbus RTU Madhus TOP	Yes		
Modbus TCP Document	Yes		
PROFIBUS	Yes		
UL/CSA ratings			
manufacturer's article number			
of circuit breaker			
 usable for Standard Faults at 460/480 V according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
 usable for High Faults at 460/480 V according to UL 	Siemens type: 3VA51, max. 125 A; Iq max = 65 kA		
 usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
 usable for High Faults at 460/480 V at inside- delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq max = 65 kA		
 usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
 usable for Standard Faults at 575/600 V at inside-delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA		
of the fuse			
 usable for Standard Faults up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 300 A; Iq = 10 kA		
 usable for High Faults up to 575/600 V according to UL 	Type: Class J / L, max. 250 A; Iq = 100 kA		
 usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 300 A; Iq = 10 kA		
 usable for High Faults at inside-delta circuit up to 575/600 V according to UL 	Type: Class J / L, max. 250 A; Iq = 100 kA		
operating power [hp] for 3-phase motors			
 at 200/208 V at 50 °C rated value 	25 hp		
 at 220/230 V at 50 °C rated value 	30 hp		
 at 460/480 V at 50 °C rated value 	60 hp		
 at 200/208 V at inside-delta circuit at 50 °C rated value 	40 hp		
 at 220/230 V at inside-delta circuit at 50 °C rated value 	50 hp		
• at 460/480 V at inside-delta circuit at 50 °C rated value	100 hp		
contact rating of auxiliary contacts according to UL	R300-B300		
Safety related data			
protection class IP on the front according to IEC 60529	IP00; IP20 with cover		
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with cover		
electromagnetic compatibility	in accordance with IEC 60947-4-2		
Certificates/ approvals			
General Product Approval		EMC	



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping





Type Test Certificates/Test Report











Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5227-3AC04

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5227-3AC04

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5227-3AC04

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5227-3AC04&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current


https://support.industry.siemens.com/cs/ww/en/ps/3RW5227-3AC04/char


Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5227-3AC04&objecttype=14&gridview=view1

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917





last modified: 4/10/2022 🖸