SIEMENS

Data sheet

6GK5795-1TR10-0AA6

product type designation



IWLAN terminating resistor TI795-1R RSMA Male

R-SMA male termination Impedance TI795-1R 2.4 and 5 GHz, IP65, 0...6 GHz; 1 pack=3 units

electrical data	
number of electrical connections	1
type of electrical connection	R-SMA male
transmission frequency	0 6 GHz
impedance	50 Ω
return loss / minimum	25 dB
ambient conditions	
ambient temperature	
 during operation 	-40 +70 °C
 during storage 	-40 +70 °C
 during transport 	-40 +70 °C
protection class IP	IP65
design, dimensions and weights	
diameter	9 mm
length	15 mm
net weight	5 g
standards, specifications, approvals	
certificate of suitability	
 RoHS conformity 	Yes
further information / internet-Links	
Internet-Link	
 to website: TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
 to web page: selection aid TIA Selection Tool 	http://www.siemens.com/snst
 to the website: IWLAN 	http://www.siemens.com/iwlan
 to website: Industrial communication 	http://www.siemens.com/simatic-net
 to website: Industry Mall 	https://mall.industry.siemens.com
 to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
 to website: Image database 	http://automation.siemens.com/bilddb
 to website: CAx-Download-Manager 	http://www.siemens.com/cax
 to website: Industry Online Support 	https://support.industry.siemens.com
last modified:	12/18/2020 🖸