




| | | | | | | | |
|---|---|---|---|---|---|---|---|
| 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 |
|---|---|---|---|---|---|---|---|

| | | | | |
|------|-------------|--------|----------|------|
| REV. | DESCRIPTION | DESIGN | APPROVAL | DATE |
|------|-------------|--------|----------|------|

广东济德精密电子有限公司
受控文件
 日期: 2023年7月25日



NOTES:

1. Contacts surface should not have burrs; - Other areas burr 0.05mm Max.
2. Never off the black, white fog, crushed phenomenon.
3. The dimension marked "*" shall be checked.
4. Harmful material please follow RoHS.
5. Pulling force between pin and welding body 100N Min.

| NO | P/N | Material | Plating |
|----|--------|--------------------|---------------------------|
| 1 | Pin | CuFe2P 0.63*0.63mm | 镀锡0.8~3.0μm, 镍底1.27~3.0μm |
| 2 | Body | CuNiSi T=0.2mm | 镀锡0.8~6.0μm |
| 3 | Spring | SUS301 T=0.15mm | |

| | | |
|-----------|----------|--|
| X± 0.15 | X*± 1* | Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司 |
| X± 0.10 | X*± 0.5* | |
| XX± 0.05 | XX*± / | |
| XXX± 0.02 | XXX*± / | |
| UNITS: | mm | |

| | | | | | | | | |
|---|--------------------------------|--|-------|-------|------|-----|-----|----|
| The information in this document is property of JIDCON company and should not be copied or reproduced in any other way, without written permission. | TITLE: 0.63 mm male contact | PART NO. 932-063-100X | | | | | | |
| | APPD: HJ 2022.09.25 | DWG NO: 932-063-100X | | | | | | |
| | CHKD: Jack 2022.09.25 | <table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td>SCALE</td> <td>SHEET</td> <td>REV.</td> </tr> <tr> <td>1:1</td> <td>1/1</td> <td>A2</td> </tr> </table> | SCALE | SHEET | REV. | 1:1 | 1/1 | A2 |
| | SCALE | | SHEET | REV. | | | | |
| 1:1 | 1/1 | A2 | | | | | | |
| DRAW: Jun 2022.09.25 | | | | | | | | |

| P/N | E | F | G | H | Wire Size Range |
|--------------|------|------|------|------|--------------------------|
| 932-063-1001 | 2.0 | 2.0 | 1.50 | 1.50 | 0.08~0.22mm ² |
| 932-063-1002 | 2.30 | 2.30 | 1.80 | 1.80 | 0.25~0.35mm ² |
| 932-063-1003 | 2.70 | 2.90 | 2.00 | 2.10 | 0.50~0.75mm ² |

| | | | | | | | |
|---|---|---|---|---|---|---|---|
| 8 | 7 | 6 | 5 | 4 | 3 | 2 | 1 |
|---|---|---|---|---|---|---|---|